

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P575398

Luminaire Tested: **FLD6C-120-D010 FEU6C-X-90-30 F6X-N-X-LI**

Issue Date: 3/1/2023



Test Information

Test Method: LM-79-08
Report Number: P575398
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P205310)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/1/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD6C-120-D010 FEU6C-X-90-30 F6X-N-X-LI
Description: 6 INCH FAIL-SAFE LED DOWNLIGHT WITH 3000K, 90 CRI LEDS, 6LBNLI TRIM

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 10242.0 lumens
Efficiency: N/A
Efficacy: 72.0 lumens/watt
Spacing Criteria (0/90/45): 0.53 / 0.53 / 0.58
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 142.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P575398

CATALOG NUMBER: FLD6C-120-D010 FEU6C-X-90-30 F6X-N-X-LI

Luminous Intensity Polar Plot





TEST NUMBER: P575398

CATALOG NUMBER: FLD6C-120-D010 FEU6C-X-90-30 F6X-N-X-LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	114	112	109	107	112	109	107	106	105	104	102	102	101	99	98	97	96	95			
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	93	91	89			
3	105	99	94	91	103	97	93	90	95	91	89	93	90	87	90	88	86	85			
4	100	93	88	85	98	92	88	84	90	86	83	88	85	82	86	84	81	80			
5	96	88	83	79	94	87	83	79	86	82	78	84	81	78	83	80	77	76			
6	92	84	79	75	90	83	78	75	82	77	74	80	76	74	79	76	73	72			
7	88	80	74	71	87	79	74	71	78	73	70	77	73	70	76	72	69	68			
8	84	76	71	67	83	75	70	67	74	70	67	73	69	66	73	69	66	65			
9	81	73	67	64	80	72	67	64	71	67	63	70	66	63	70	66	63	62			
10	78	69	64	61	77	69	64	61	68	64	61	67	63	60	67	63	60	59			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1278330
5°	1195457
10°	974988
15°	717462
20°	494517
25°	367128
30°	275770
35°	171966
40°	83478
45°	28639
50°	3753
55°	2839
60°	1634
65°	1933
70°	2388
75°	0
80°	0
85°	0



TEST NUMBER: P575398

CATALOG NUMBER: FLD6C-120-D010 FEU6C-X-90-30 F6X-N-X-LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1938.8	18.9
10°-20°	3480.0	34.0
20°-30°	2813.6	27.5
30°-40°	1620.8	15.8
40°-50°	342.6	3.3
50°-60°	29.5	0.3
60°-70°	14.8	0.1
70°-80°	1.9	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	8232.3	80.4
0°-40°	9853.1	96.2
0°-60°	10225.3	99.8
0°-90°	10242.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	10242.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	23319	
5°	21724	###
15°	12642	3480
25°	6070	2814
35°	2570	1621
45°	369	343
55°	30	30
65°	15	15
75°	0	2
85°	0	0
90°	0	



TEST NUMBER: P575398

CATALOG NUMBER: FLD6C-120-D010 FEU6C-X-90-30 F6X-N-X-LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	23318.6
2.5°	23038.4
5°	21723.9
7.5°	19833.6
10°	17515.0
12.5°	15137.5
15°	12641.6
17.5°	10234.4
20°	8476.7
22.5°	7133.0
25°	6069.5
27.5°	5168.9
30°	4356.5
32.5°	3455.9
35°	2569.6
37.5°	1786.8
40°	1166.5
42.5°	709.0
45°	369.4
47.5°	147.5
50°	44.0
52.5°	44.0
55°	29.7
57.5°	29.7
60°	14.9
62.5°	14.9
65°	14.9
67.5°	14.9
70°	14.9
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-MV3F9LC





— 0°-180°







(END OF REPORT)