

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P575538

Luminaire Tested: **FLD6C-120-D010 FEU6C-X-90-40 F6X-W-X-LI**

Issue Date: 3/1/2023



**Test Information**

Test Method: LM-79-08  
Report Number: P575538  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P205209)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/1/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: FAIL-SAFE  
Catalog Number: FLD6C-120-D010 FEU6C-X-90-40 F6X-W-X-LI  
Description: 6 INCH FAIL-SAFE LED DOWNLIGHT WITH 4000K, 90 CRI LEDS, 6LBWLI TRIM

Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 13221.0 lumens  
Efficiency: N/A  
Efficacy: 92.9 lumens/watt  
Spacing Criteria (0/90/45): 1.24 / 1.24 / 1.18  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct

Input Watts (W): 142.3  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P575538

CATALOG NUMBER: FLD6C-120-D010 FEU6C-X-90-40 F6X-W-X-LI

### Luminous Intensity Polar Plot





TEST NUMBER: P575538

CATALOG NUMBER: FLD6C-120-D010 FEU6C-X-90-40 F6X-W-X-LI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	113	110	107	104	110	107	105	103	103	101	99	100	98	97	96	95	94	92			92
2	106	101	96	92	104	99	95	91	95	92	89	92	90	87	90	87	85	83			83
3	100	92	87	82	97	91	86	81	88	84	80	86	82	79	83	80	77	76			76
4	93	85	78	73	92	84	78	73	81	76	72	79	75	71	77	74	70	69			69
5	88	78	71	66	86	77	71	66	75	70	65	73	69	65	72	68	64	63			63
6	82	72	65	60	81	71	65	60	70	64	59	68	63	59	67	62	59	57			57
7	77	67	60	55	76	66	59	55	65	59	54	63	58	54	62	57	54	52			52
8	73	62	55	50	71	61	55	50	60	54	50	59	54	50	58	53	49	48			48
9	69	57	51	46	67	57	50	46	56	50	46	55	50	46	54	49	46	44			44
10	65	54	47	43	64	53	47	42	52	46	42	51	46	42	51	46	42	41			41

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	452787
5°	456977
10°	469764
15°	481518
20°	488829
25°	478727
30°	448829
35°	401277
40°	325023
45°	215007
50°	108679
55°	45848
60°	14780
65°	5798
70°	4841
75°	3198
80°	0
85°	0



TEST NUMBER: P575538

CATALOG NUMBER: FLD6C-120-D010 FEU6C-X-90-40 F6X-W-X-LI

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	796.8	6.0
10°-20°	2394.9	18.1
20°-30°	3610.2	27.3
30°-40°	3695.2	27.9
40°-50°	2152.7	16.3
50°-60°	494.7	3.7
60°-70°	60.7	0.5
70°-80°	15.9	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	6801.9	51.4
0°-40°	10497.0	79.4
0°-60°	13144.4	99.4
0°-90°	13221.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	13221.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	8260	
5°	8304	797
15°	8484	2395
25°	7914	3610
35°	5996	3695
45°	2773	2153
55°	480	495
65°	45	61
75°	15	16
85°	0	0
90°	0	



TEST NUMBER: P575538

CATALOG NUMBER: FLD6C-120-D010 FEU6C-X-90-40 F6X-W-X-LI

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	8259.5
2.5°	8244.4
5°	8304.2
7.5°	8364.1
10°	8439.0
12.5°	8454.1
15°	8484.3
17.5°	8454.1
20°	8379.2
22.5°	8139.3
25°	7914.5
27.5°	7555.0
30°	7090.4
32.5°	6610.6
35°	5996.1
37.5°	5306.2
40°	4541.8
42.5°	3687.5
45°	2773.3
47.5°	1933.5
50°	1274.3
52.5°	809.6
55°	479.7
57.5°	255.0
60°	134.8
62.5°	74.9
65°	44.7
67.5°	44.7
70°	30.2
72.5°	15.1
75°	15.1
77.5°	15.1
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-MV3F9LC







— 0°-180°







(END OF REPORT)