

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P575598

Luminaire Tested: **FLD6C-120-D010 FEU6C-X-90-50 F6X-W-X-LI**

Issue Date: 3/1/2023



Test Information

Test Method: LM-79-08
Report Number: P575598
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P205209)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/1/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD6C-120-D010 FEU6C-X-90-50 F6X-W-X-LI
Description: 6 INCH FAIL-SAFE LED DOWNLIGHT WITH 5000K, 90 CRI LEDS, 6LBWLI TRIM

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 13493.0 lumens
Efficiency: N/A
Efficacy: 94.8 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.24 / 1.18
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 142.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P575598

CATALOG NUMBER: FLD6C-120-D010 FEU6C-X-90-50 F6X-W-X-LI

Luminous Intensity Polar Plot





TEST NUMBER: P575598

CATALOG NUMBER: FLD6C-120-D010 FEU6C-X-90-50 F6X-W-X-LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	113	110	107	104	110	107	105	103	103	101	99	100	98	97	96	95	94	92				92
2	106	101	96	92	104	99	95	91	95	92	89	92	90	87	90	87	85	83				83
3	100	92	87	82	97	91	86	81	88	84	80	86	82	79	83	80	77	76				76
4	93	85	78	73	92	84	78	73	81	76	72	79	75	71	77	74	70	69				69
5	88	78	71	66	86	77	71	66	75	70	65	73	69	65	72	68	64	63				63
6	82	72	65	60	81	71	65	60	70	64	59	68	63	59	67	62	59	57				57
7	77	67	60	55	76	66	59	55	65	59	54	63	58	54	62	57	54	52				52
8	73	62	55	50	71	61	55	50	60	54	50	59	54	50	58	53	49	48				48
9	69	57	51	46	67	57	50	46	56	50	46	55	50	46	54	49	46	44				44
10	65	54	47	43	64	53	47	42	52	46	42	51	46	42	51	46	42	41				41

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	462101
5°	466381
10°	479428
15°	491422
20°	498887
25°	488581
30°	458058
35°	409536
40°	331714
45°	219426
50°	110913
55°	46794
60°	15076
65°	5928
70°	4937
75°	3262
80°	0
85°	0



TEST NUMBER: P575598

CATALOG NUMBER: FLD6C-120-D010 FEU6C-X-90-50 F6X-W-X-LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	813.2	6.0
10°-20°	2444.2	18.1
20°-30°	3684.5	27.3
30°-40°	3771.2	27.9
40°-50°	2197.0	16.3
50°-60°	504.9	3.7
60°-70°	62.0	0.5
70°-80°	16.2	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	6941.8	51.4
0°-40°	10713.0	79.4
0°-60°	13414.8	99.4
0°-90°	13493.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	13493.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	8429	
5°	8475	813
15°	8659	2444
25°	8077	3684
35°	6120	3771
45°	2830	2197
55°	490	505
65°	46	62
75°	15	16
85°	0	0
90°	0	



TEST NUMBER: P575598

CATALOG NUMBER: FLD6C-120-D010 FEU6C-X-90-50 F6X-W-X-LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	8429.4
2.5°	8414.0
5°	8475.1
7.5°	8536.1
10°	8612.6
12.5°	8628.0
15°	8658.8
17.5°	8628.0
20°	8551.6
22.5°	8306.8
25°	8077.4
27.5°	7710.4
30°	7236.2
32.5°	6746.6
35°	6119.5
37.5°	5415.3
40°	4635.3
42.5°	3763.3
45°	2830.3
47.5°	1973.3
50°	1300.5
52.5°	826.3
55°	489.6
57.5°	260.2
60°	137.5
62.5°	76.5
65°	45.7
67.5°	45.7
70°	30.8
72.5°	15.4
75°	15.4
77.5°	15.4
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-MV3F9LC





— 0°-180°







(END OF REPORT)