

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P575698

Luminaire Tested: **FLD6C-15-D010 FEU6C-X-90-30 F6X-N-X-LI**

Issue Date: 3/1/2023



**Test Information**

Test Method: LM-79-08  
Report Number: P575698  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P205310)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/1/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: FAIL-SAFE  
Catalog Number: FLD6C-15-D010 FEU6C-X-90-30 F6X-N-X-LI  
Description: 6 INCH FAIL-SAFE LED DOWNLIGHT WITH 3000K, 90 CRI LEDS, 6LBNLI TRIM

Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1255.0 lumens  
Efficiency: N/A  
Efficacy: 79.4 lumens/watt  
Spacing Criteria (0/90/45): 0.53 / 0.53 / 0.58  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct

Input Watts (W): 15.8  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P575698

CATALOG NUMBER: FLD6C-15-D010 FEU6C-X-90-30 F6X-N-X-LI

### Luminous Intensity Polar Plot





TEST NUMBER: P575698

CATALOG NUMBER: FLD6C-15-D010 FEU6C-X-90-30 F6X-N-X-LI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	114	112	109	107	112	109	107	106	105	104	102	102	101	99	98	97	96	95			
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	93	91	89			
3	105	99	94	91	103	97	93	90	95	91	89	93	90	87	90	88	86	85			
4	100	93	88	85	98	92	88	84	90	86	83	88	85	82	86	84	81	80			
5	96	88	83	79	94	87	83	79	86	82	78	84	81	78	83	80	77	76			
6	92	84	79	75	90	83	78	75	82	77	74	80	76	74	79	76	73	72			
7	88	80	74	71	87	79	74	71	78	73	70	77	73	70	76	72	69	68			
8	84	76	71	67	83	75	70	67	74	70	67	73	69	66	73	69	66	65			
9	81	73	67	64	80	72	67	64	71	67	63	70	66	63	70	66	63	62			
10	78	69	64	61	77	69	64	61	68	64	61	67	63	60	67	63	60	59			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	156638
5°	146483
10°	119470
15°	87912
20°	60596
25°	44984
30°	33790
35°	21074
40°	10226
45°	3512
50°	461
55°	344
60°	197
65°	233
70°	289
75°	0
80°	0
85°	0



TEST NUMBER: P575698

CATALOG NUMBER: FLD6C-15-D010 FEU6C-X-90-30 F6X-N-X-LI

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	237.6	18.9
10°-20°	426.4	34.0
20°-30°	344.8	27.5
30°-40°	198.6	15.8
40°-50°	42.0	3.3
50°-60°	3.6	0.3
60°-70°	1.8	0.1
70°-80°	0.2	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1008.7	80.4
0°-40°	1207.3	96.2
0°-60°	1252.9	99.8
0°-90°	1255.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1255.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2857	
5°	2662	238
15°	1549	426
25°	744	345
35°	315	199
45°	45	42
55°	4	4
65°	2	2
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P575698

CATALOG NUMBER: FLD6C-15-D010 FEU6C-X-90-30 F6X-N-X-LI

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	2857.3
2.5°	2823.0
5°	2661.9
7.5°	2430.3
10°	2146.2
12.5°	1854.9
15°	1549.0
17.5°	1254.1
20°	1038.7
22.5°	874.0
25°	743.7
27.5°	633.4
30°	533.8
32.5°	423.5
35°	314.9
37.5°	218.9
40°	142.9
42.5°	86.9
45°	45.3
47.5°	18.1
50°	5.4
52.5°	5.4
55°	3.6
57.5°	3.6
60°	1.8
62.5°	1.8
65°	1.8
67.5°	1.8
70°	1.8
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-MV3F9LC







— 0°-180°







(END OF REPORT)