

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P573958

Luminaire Tested: **FLD6C-02-D010 FEU6C-X-90-35 F6X-N-X-LI**

Issue Date: 3/1/2023



**Test Information**

Test Method: LM-79-08  
Report Number: P573958  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P205310)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/1/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: FAIL-SAFE  
Catalog Number: FLD6C-02-D010 FEU6C-X-90-35 F6X-N-X-LI  
Description: 6 INCH FAIL-SAFE LED DOWNLIGHT WITH 3500K, 90 CRI LEDS, 6LBNLI TRIM

Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 271.0 lumens  
Efficiency: N/A  
Efficacy: 77.4 lumens/watt  
Spacing Criteria (0/90/45): 0.53 / 0.53 / 0.57  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct

Input Watts (W): 3.5  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P573958

CATALOG NUMBER: FLD6C-02-D010 FEU6C-X-90-35 F6X-N-X-LI

### Luminous Intensity Polar Plot





TEST NUMBER: P573958

CATALOG NUMBER: FLD6C-02-D010 FEU6C-X-90-35 F6X-N-X-LI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	114	112	109	107	112	109	107	106	105	104	102	102	101	99	98	97	96	95			
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	93	91	89			
3	105	99	94	91	103	97	93	90	95	91	89	93	90	87	90	88	86	85			
4	100	93	88	85	98	92	88	84	90	86	83	88	85	82	86	84	81	80			
5	96	88	83	79	94	87	83	79	86	82	78	84	81	78	83	80	77	76			
6	92	84	79	75	90	83	78	75	82	77	74	80	76	74	79	76	73	72			
7	88	80	74	71	87	79	74	71	78	73	70	77	73	70	76	72	69	68			
8	84	76	71	67	83	75	70	67	74	70	67	73	69	66	73	69	66	65			
9	81	73	67	64	80	72	67	64	71	67	63	70	66	63	70	66	63	62			
10	78	69	64	61	77	69	64	61	68	64	61	67	63	60	67	63	60	59			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	33824
5°	31631
10°	25796
15°	18984
20°	13085
25°	9714
30°	7299
35°	4551
40°	2211
45°	760
50°	102
55°	76
60°	44
65°	52
70°	64
75°	0
80°	0
85°	0



TEST NUMBER: P573958

CATALOG NUMBER: FLD6C-02-D010 FEU6C-X-90-35 F6X-N-X-LI

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	51.3	18.9
10°-20°	92.1	34.0
20°-30°	74.4	27.5
30°-40°	42.9	15.8
40°-50°	9.1	3.4
50°-60°	0.8	0.3
60°-70°	0.4	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	217.8	80.4
0°-40°	260.7	96.2
0°-60°	270.6	99.8
0°-90°	271.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	271.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	617	
5°	575	51
15°	334	92
25°	161	74
35°	68	43
45°	10	9
55°	1	1
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P573958

CATALOG NUMBER: FLD6C-02-D010 FEU6C-X-90-35 F6X-N-X-LI

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	617.0
2.5°	609.6
5°	574.8
7.5°	524.8
10°	463.4
12.5°	400.5
15°	334.5
17.5°	270.8
20°	224.3
22.5°	188.7
25°	160.6
27.5°	136.8
30°	115.3
32.5°	91.4
35°	68.0
37.5°	47.3
40°	30.9
42.5°	18.8
45°	9.8
47.5°	3.9
50°	1.2
52.5°	1.2
55°	0.8
57.5°	0.8
60°	0.4
62.5°	0.4
65°	0.4
67.5°	0.4
70°	0.4
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-MV3F9LC







— 0°-180°







(END OF REPORT)