

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P574008

Luminaire Tested: **FLD6C-02-D010 FEU6C-X-90-40 F6X-N-X-H**

Issue Date: 3/1/2023



Test Information

Test Method: LM-79-08
Report Number: P574008
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P203666)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/1/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD6C-02-D010 FEU6C-X-90-40 F6X-N-X-H
Description: 6 INCH FAIL-SAFE LED DOWNLIGHT WITH 4000K, 90 CRI LEDS, 6LBNH TRIM

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 215.0 lumens
Efficiency: N/A
Efficacy: 61.4 lumens/watt
Spacing Criteria (0/90/45): 0.78 / 0.78 / 0.84
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 3.5
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P574008

CATALOG NUMBER: FLD6C-02-D010 FEU6C-X-90-40 F6X-N-X-H

Luminous Intensity Polar Plot





TEST NUMBER: P574008

CATALOG NUMBER: FLD6C-02-D010 FEU6C-X-90-40 F6X-N-X-H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	113	111	108	106	111	109	106	104	104	103	101	101	99	98	97	96	95	93
2	108	103	99	96	106	101	98	94	98	95	92	95	93	90	92	90	89	87
3	102	96	91	87	100	95	90	86	92	88	85	90	86	84	87	85	82	81
4	97	90	84	80	95	89	83	79	86	82	78	84	81	78	83	79	77	75
5	92	84	78	74	91	83	78	73	81	76	73	80	75	72	78	74	72	70
6	88	79	73	69	86	78	72	68	77	72	68	75	71	67	74	70	67	65
7	83	74	68	64	82	73	68	64	72	67	63	71	66	63	70	66	63	61
8	79	70	64	60	78	69	64	60	68	63	59	67	63	59	66	62	59	58
9	76	66	60	56	75	66	60	56	65	59	56	64	59	56	63	59	55	54
10	72	62	57	53	71	62	56	53	61	56	53	60	56	52	60	55	52	51

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	15108
5°	14737
10°	13594
15°	12038
20°	10454
25°	8940
30°	7368
35°	4852
40°	2612
45°	1155
50°	469
55°	335
60°	219
65°	156
70°	128
75°	85
80°	126
85°	0



TEST NUMBER: P574008

CATALOG NUMBER: FLD6C-02-D010 FEU6C-X-90-40 F6X-N-X-H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	24.8	11.5
10°-20°	59.1	27.5
20°-30°	67.7	31.5
30°-40°	45.5	21.2
40°-50°	13.0	6.0
50°-60°	3.2	1.5
60°-70°	1.2	0.6
70°-80°	0.5	0.2
80°-90°	0.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	151.6	70.5
0°-40°	197.1	91.7
0°-60°	213.3	99.2
0°-90°	215.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	215.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	276	
5°	268	25
15°	212	59
25°	148	68
35°	72	45
45°	15	13
55°	4	3
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P574008

CATALOG NUMBER: FLD6C-02-D010 FEU6C-X-90-40 F6X-N-X-H

CANDELA DISTRIBUTION (FULL):

	0°
0°	275.6
2.5°	273.7
5°	267.8
7.5°	257.2
10°	244.2
12.5°	227.8
15°	212.1
17.5°	195.6
20°	179.2
22.5°	163.5
25°	147.8
27.5°	133.3
30°	116.4
32.5°	94.1
35°	72.5
37.5°	52.9
40°	36.5
42.5°	23.9
45°	14.9
47.5°	9.0
50°	5.5
52.5°	4.3
55°	3.5
57.5°	2.7
60°	2.0
62.5°	1.6
65°	1.2
67.5°	0.8
70°	0.8
72.5°	0.4
75°	0.4
77.5°	0.4
80°	0.4
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-MV3F9LC





— 0°-180°







(END OF REPORT)