

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P578378

Luminaire Tested: **FLD6C-60-D010 FEU6C-X-90-30 F6X-M-X-LI**

Issue Date: 3/1/2023



Test Information

Test Method: LM-79-08
Report Number: P578378
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P205108)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/1/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD6C-60-D010 FEU6C-X-90-30 F6X-M-X-LI
Description: 6 INCH FAIL-SAFE LED DOWNLIGHT WITH 3000K, 90 CRI LEDS, 6LBMLI TRIM

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5831.9 lumens
Efficiency: N/A
Efficacy: 81.0 lumens/watt
Spacing Criteria (0/90/45): 0.85 / 0.85 / 0.85
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 72
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P578378

CATALOG NUMBER: FLD6C-60-D010 FEU6C-X-90-30 F6X-M-X-LI

Luminous Intensity Polar Plot





TEST NUMBER: P578378

CATALOG NUMBER: FLD6C-60-D010 FEU6C-X-90-30 F6X-M-X-LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	114	111	109	106	111	109	107	105	105	103	101	101	100	98	98	97	96	94			
2	108	103	100	96	106	102	98	95	99	96	93	96	93	91	93	91	89	88			
3	103	97	92	88	101	95	91	87	93	89	86	90	87	85	88	85	83	82			
4	98	91	85	81	96	89	84	81	87	83	80	85	82	79	83	80	78	76			
5	93	85	79	75	91	84	79	75	82	78	74	81	77	73	79	76	73	71			
6	89	80	74	70	87	79	74	70	78	73	69	76	72	69	75	71	68	67			
7	84	75	69	65	83	75	69	65	73	68	65	72	68	64	71	67	64	63			
8	80	71	65	61	79	70	65	61	69	64	61	68	64	60	67	63	60	59			
9	77	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55			
10	73	64	58	54	72	63	58	54	62	57	54	62	57	54	61	57	54	52			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	400105
5°	396295
10°	375527
15°	340944
20°	301271
25°	260459
30°	203601
35°	124858
40°	64084
45°	25460
50°	8264
55°	2848
60°	2445
65°	1946
70°	1202
75°	1589
80°	0
85°	0



TEST NUMBER: P578378

CATALOG NUMBER: FLD6C-60-D010 FEU6C-X-90-30 F6X-M-X-LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	672.3	11.5
10°-20°	1673.9	28.7
20°-30°	1945.8	33.4
30°-40°	1191.6	20.4
40°-50°	295.9	5.1
50°-60°	34.6	0.6
60°-70°	12.9	0.2
70°-80°	4.9	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4292.1	73.6
0°-40°	5483.7	94.0
0°-60°	5814.1	99.7
0°-90°	5831.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5831.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	7298	
5°	7202	672
15°	6007	1674
25°	4306	1946
35°	1866	1192
45°	328	296
55°	30	35
65°	15	13
75°	8	5
85°	0	0
90°	0	



TEST NUMBER: P578378

CATALOG NUMBER: FLD6C-60-D010 FEU6C-X-90-30 F6X-M-X-LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	7298.5
2.5°	7290.9
5°	7201.5
7.5°	7007.4
10°	6746.1
12.5°	6402.9
15°	6007.4
17.5°	5582.1
20°	5164.2
22.5°	4746.2
25°	4306.0
27.5°	3798.5
30°	3216.4
32.5°	2537.3
35°	1865.7
37.5°	1313.3
40°	895.5
42.5°	559.6
45°	328.4
47.5°	186.6
50°	96.9
52.5°	44.8
55°	29.8
57.5°	22.3
60°	22.3
62.5°	15.0
65°	15.0
67.5°	7.5
70°	7.5
72.5°	7.5
75°	7.5
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-MV3F9LC





— 0°-180°







(END OF REPORT)