

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P576658

Luminaire Tested: **FLD6C-30-D010 FEU6C-X-90-35 F6X-N-X-LI**

Issue Date: 3/1/2023



Test Information

Test Method: LM-79-08
Report Number: P576658
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P205310)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/1/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD6C-30-D010 FEU6C-X-90-35 F6X-N-X-LI
Description: 6 INCH FAIL-SAFE LED DOWNLIGHT WITH 3500K, 90 CRI LEDS, 6LBNLI TRIM

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2421.0 lumens
Efficiency: N/A
Efficacy: 76.6 lumens/watt
Spacing Criteria (0/90/45): 0.53 / 0.53 / 0.58
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 31.6
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P576658

CATALOG NUMBER: FLD6C-30-D010 FEU6C-X-90-35 F6X-N-X-LI

Luminous Intensity Polar Plot





TEST NUMBER: P576658

CATALOG NUMBER: FLD6C-30-D010 FEU6C-X-90-35 F6X-N-X-LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20									20
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR	0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100	100	100	100	100	100	100	100																	
	1	114	112	109	107	112	109	107	106	105	104	102	102	101	99	98	97	96	95	95	95	95	95	95	95	95	95	95	95																	
	2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	93	91	89	89	89	89	89	89	89	89	89	89	89																	
	3	105	99	94	91	103	97	93	90	95	91	89	93	90	87	90	88	86	85	85	85	85	85	85	85	85	85	85	85																	
	4	100	93	88	85	98	92	88	84	90	86	83	88	85	82	86	84	81	80	80	80	80	80	80	80	80	80	80	80																	
	5	96	88	83	79	94	87	83	79	86	82	78	84	81	78	83	80	77	76	76	76	76	76	76	76	76	76	76	76																	
	6	92	84	79	75	90	83	78	75	82	77	74	80	76	74	79	76	73	72	72	72	72	72	72	72	72	72	72	72																	
	7	88	80	74	71	87	79	74	71	78	73	70	77	73	70	76	72	69	68	68	68	68	68	68	68	68	68	68	68																	
	8	84	76	71	67	83	75	70	67	74	70	67	73	69	66	73	69	66	65	65	65	65	65	65	65	65	65	65	65																	
	9	81	73	67	64	80	72	67	64	71	67	63	70	66	63	70	66	63	62	62	62	62	62	62	62	62	62	62	62																	
	10	78	69	64	61	77	69	64	61	68	64	61	67	63	60	67	63	60	59	59	59	59	59	59	59	59	59	59	59																	

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	302169
5°	282582
10°	230468
15°	169592
20°	116893
25°	86781
30°	65187
35°	40649
40°	19730
45°	6768
50°	887
55°	669
60°	384
65°	454
70°	561
75°	0
80°	0
85°	0



TEST NUMBER: P576658

CATALOG NUMBER: FLD6C-30-D010 FEU6C-X-90-35 F6X-N-X-LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	458.3	18.9
10°-20°	822.6	34.0
20°-30°	665.1	27.5
30°-40°	383.1	15.8
40°-50°	81.0	3.3
50°-60°	7.0	0.3
60°-70°	3.5	0.1
70°-80°	0.5	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1945.9	80.4
0°-40°	2329.1	96.2
0°-60°	2417.0	99.8
0°-90°	2421.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2421.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5512	
5°	5135	458
15°	2988	823
25°	1435	665
35°	607	383
45°	87	81
55°	7	7
65°	4	3
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P576658

CATALOG NUMBER: FLD6C-30-D010 FEU6C-X-90-35 F6X-N-X-LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	5512.0
2.5°	5445.8
5°	5135.1
7.5°	4688.2
10°	4140.2
12.5°	3578.2
15°	2988.2
17.5°	2419.2
20°	2003.7
22.5°	1686.1
25°	1434.7
27.5°	1221.8
30°	1029.8
32.5°	816.9
35°	607.4
37.5°	422.4
40°	275.7
42.5°	167.6
45°	87.3
47.5°	34.9
50°	10.4
52.5°	10.4
55°	7.0
57.5°	7.0
60°	3.5
62.5°	3.5
65°	3.5
67.5°	3.5
70°	3.5
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-MV3F9LC





— 0°-180°







(END OF REPORT)