

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P578648

Luminaire Tested: **FLD6C-65-D010 FEU6C-X-90-27 F6X-W-X-H**

Issue Date: 3/1/2023



Test Information

Test Method: LM-79-08
Report Number: P578648
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P202739)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/1/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD6C-65-D010 FEU6C-X-90-27 F6X-W-X-H
Description: 6 INCH FAIL-SAFE LED DOWNLIGHT WITH 2700K, 90 CRI LEDS, 6LBWH TRIM

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5801.0 lumens
Efficiency: N/A
Efficacy: 80.1 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.16
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 72.4
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P578648

CATALOG NUMBER: FLD6C-65-D010 FEU6C-X-90-27 F6X-W-X-H

Luminous Intensity Polar Plot





TEST NUMBER: P578648

CATALOG NUMBER: FLD6C-65-D010 FEU6C-X-90-27 F6X-W-X-H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	112	109	106	103	110	107	104	101	103	100	98	99	97	95	95	94	93	91			91
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	85	83	81			81
3	98	90	84	79	96	89	83	78	86	81	77	83	79	76	81	78	75	73			73
4	92	82	75	70	90	81	75	70	79	73	69	77	72	68	75	71	67	65			65
5	86	75	68	63	84	74	68	63	72	66	62	71	65	61	69	64	61	59			59
6	80	69	62	57	78	68	61	56	67	61	56	65	60	56	64	59	55	53			53
7	75	64	56	51	73	63	56	51	62	55	51	60	55	51	59	54	50	49			49
8	70	59	52	47	69	58	51	47	57	51	46	56	50	46	55	50	46	44			44
9	66	55	48	43	65	54	47	43	53	47	43	52	47	42	51	46	42	41			41
10	62	51	44	40	61	50	44	39	50	43	39	49	43	39	48	43	39	38			38

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	196136
5°	196070
10°	194563
15°	193259
20°	190312
25°	185962
30°	175097
35°	158460
40°	132319
45°	101390
50°	71810
55°	45274
60°	25535
65°	16578
70°	10835
75°	7964
80°	4767
85°	4780



TEST NUMBER: P578648

CATALOG NUMBER: FLD6C-65-D010 FEU6C-X-90-27 F6X-W-X-H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	337.9	5.8
10°-20°	958.9	16.5
20°-30°	1405.9	24.2
30°-40°	1463.2	25.2
40°-50°	1012.4	17.5
50°-60°	440.8	7.6
60°-70°	135.2	2.3
70°-80°	40.5	0.7
80°-90°	6.2	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2702.8	46.6
0°-40°	4166.0	71.8
0°-60°	5619.1	96.9
0°-90°	5801.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5801.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3578	
5°	3563	338
15°	3405	959
25°	3074	1406
35°	2368	1463
45°	1308	1012
55°	474	441
65°	128	135
75°	38	41
85°	8	6
90°	0	



TEST NUMBER: P578648

CATALOG NUMBER: FLD6C-65-D010 FEU6C-X-90-27 F6X-W-X-H

CANDELA DISTRIBUTION (FULL):

	0°
0°	3577.8
2.5°	3585.4
5°	3563.0
7.5°	3533.0
10°	3495.2
12.5°	3457.6
15°	3405.2
17.5°	3337.4
20°	3262.2
22.5°	3179.6
25°	3074.4
27.5°	2939.1
30°	2766.1
32.5°	2585.6
35°	2367.8
37.5°	2127.4
40°	1849.0
42.5°	1571.0
45°	1307.8
47.5°	1059.8
50°	842.0
52.5°	639.0
55°	473.7
57.5°	338.3
60°	232.9
62.5°	172.9
65°	127.8
67.5°	97.8
70°	67.6
72.5°	52.7
75°	37.6
77.5°	22.4
80°	15.1
82.5°	7.6
85°	7.6
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-MV3F9LC





— 0°-180°







(END OF REPORT)