

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P578778

Luminaire Tested: **FLD6C-65-D010 FEU6C-X-90-35 F6X-W-X-LI**

Issue Date: 3/1/2023



Test Information

Test Method: LM-79-08
Report Number: P578778
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P205209)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/1/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD6C-65-D010 FEU6C-X-90-35 F6X-W-X-LI
Description: 6 INCH FAIL-SAFE LED DOWNLIGHT WITH 3500K, 90 CRI LEDS, 6LBWLI TRIM

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6987.0 lumens
Efficiency: N/A
Efficacy: 96.5 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.24 / 1.18
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 72.4
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P578778

CATALOG NUMBER: FLD6C-65-D010 FEU6C-X-90-35 F6X-W-X-LI

Luminous Intensity Polar Plot





TEST NUMBER: P578778

CATALOG NUMBER: FLD6C-65-D010 FEU6C-X-90-35 F6X-W-X-LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	110	107	104	110	107	105	103	103	101	99	100	98	97	96	95	94	92																			
2	106	101	96	92	104	99	95	91	95	92	89	92	90	87	90	87	85	83																			
3	100	92	87	82	97	91	86	81	88	84	80	86	82	79	83	80	77	76																			
4	93	85	78	73	92	84	78	73	81	76	72	79	75	71	77	74	70	69																			
5	88	78	71	66	86	77	71	66	75	70	65	73	69	65	72	68	64	63																			
6	82	72	65	60	81	71	65	60	70	64	59	68	63	59	67	62	59	57																			
7	77	67	60	55	76	66	59	55	65	59	54	63	58	54	62	57	54	52																			
8	73	62	55	50	71	61	55	50	60	54	50	59	54	50	58	53	49	48																			
9	69	57	51	46	67	57	50	46	56	50	46	55	50	46	54	49	46	44																			
10	65	54	47	43	64	53	47	42	52	46	42	51	46	42	51	46	42	41																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	239290
5°	241503
10°	248259
15°	254468
20°	258334
25°	252994
30°	237195
35°	212066
40°	171772
45°	113624
50°	57431
55°	24229
60°	7806
65°	3061
70°	2565
75°	1694
80°	0
85°	0



TEST NUMBER: P578778

CATALOG NUMBER: FLD6C-65-D010 FEU6C-X-90-35 F6X-W-X-LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	421.1	6.0
10°-20°	1265.6	18.1
20°-30°	1907.9	27.3
30°-40°	1952.8	27.9
40°-50°	1137.6	16.3
50°-60°	261.4	3.7
60°-70°	32.1	0.5
70°-80°	8.4	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3594.6	51.4
0°-40°	5547.4	79.4
0°-60°	6946.5	99.4
0°-90°	6987.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6987.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4365	
5°	4389	421
15°	4484	1266
25°	4183	1908
35°	3169	1953
45°	1466	1138
55°	254	261
65°	24	32
75°	8	8
85°	0	0
90°	0	



TEST NUMBER: P578778

CATALOG NUMBER: FLD6C-65-D010 FEU6C-X-90-35 F6X-W-X-LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	4365.0
2.5°	4357.0
5°	4388.6
7.5°	4420.2
10°	4459.8
12.5°	4467.8
15°	4483.7
17.5°	4467.8
20°	4428.2
22.5°	4301.4
25°	4182.6
27.5°	3992.6
30°	3747.1
32.5°	3493.6
35°	3168.8
37.5°	2804.2
40°	2400.3
42.5°	1948.7
45°	1465.6
47.5°	1021.8
50°	673.4
52.5°	427.9
55°	253.5
57.5°	134.7
60°	71.2
62.5°	39.6
65°	23.6
67.5°	23.6
70°	16.0
72.5°	8.0
75°	8.0
77.5°	8.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-MV3F9LC





— 0°-180°







(END OF REPORT)