

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P574218

Luminaire Tested: **FLD6C-05-D010 FEU6C-X-90-30 F6X-W-X-LI**

Issue Date: 3/1/2023



Test Information

Test Method: LM-79-08
Report Number: P574218
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P205209)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/1/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD6C-05-D010 FEU6C-X-90-30 F6X-W-X-LI
Description: 6 INCH FAIL-SAFE LED DOWNLIGHT WITH 3000K, 90 CRI LEDS, 6LBWLI TRIM

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 675.0 lumens
Efficiency: N/A
Efficacy: 93.8 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.24 / 1.18
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P574218

CATALOG NUMBER: FLD6C-05-D010 FEU6C-X-90-30 F6X-W-X-LI

Luminous Intensity Polar Plot





TEST NUMBER: P574218

CATALOG NUMBER: FLD6C-05-D010 FEU6C-X-90-30 F6X-W-X-LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	113	110	107	104	110	107	105	103	103	101	99	100	98	97	96	95	94	92			92
2	106	101	96	92	104	99	95	91	95	92	89	92	90	87	90	87	85	83			83
3	100	92	87	82	97	91	86	81	88	84	80	86	82	79	83	80	77	76			76
4	93	85	78	73	92	84	78	73	81	76	72	79	75	71	77	74	70	69			69
5	88	78	71	66	86	77	71	66	75	70	65	73	69	65	72	68	64	63			63
6	82	72	65	60	81	71	65	60	70	64	59	68	63	59	67	62	59	57			57
7	77	67	60	55	76	66	59	55	65	59	54	63	58	54	62	57	54	52			52
8	73	62	55	50	71	61	55	50	60	54	50	59	54	50	58	53	49	48			48
9	69	57	51	46	67	57	50	46	56	50	46	55	50	46	54	49	46	44			44
10	65	54	47	43	64	53	47	42	52	46	42	51	46	42	51	46	42	41			41

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	23118
5°	23333
10°	23986
15°	24586
20°	24957
25°	24443
30°	22915
35°	20485
40°	16595
45°	10978
50°	5552
55°	2342
60°	757
65°	298
70°	240
75°	169
80°	0
85°	0



TEST NUMBER: P574218

CATALOG NUMBER: FLD6C-05-D010 FEU6C-X-90-30 F6X-W-X-LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	40.7	6.0
10°-20°	122.3	18.1
20°-30°	184.3	27.3
30°-40°	188.7	27.9
40°-50°	109.9	16.3
50°-60°	25.3	3.7
60°-70°	3.1	0.5
70°-80°	0.8	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	347.3	51.4
0°-40°	535.9	79.4
0°-60°	671.1	99.4
0°-90°	675.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	675.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	422	
5°	424	41
15°	433	122
25°	404	184
35°	306	189
45°	142	110
55°	24	25
65°	2	3
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P574218

CATALOG NUMBER: FLD6C-05-D010 FEU6C-X-90-30 F6X-W-X-LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	421.7
2.5°	420.9
5°	424.0
7.5°	427.0
10°	430.9
12.5°	431.6
15°	433.2
17.5°	431.6
20°	427.8
22.5°	415.6
25°	404.1
27.5°	385.7
30°	362.0
32.5°	337.5
35°	306.1
37.5°	270.9
40°	231.9
42.5°	188.3
45°	141.6
47.5°	98.7
50°	65.1
52.5°	41.3
55°	24.5
57.5°	13.0
60°	6.9
62.5°	3.8
65°	2.3
67.5°	2.3
70°	1.5
72.5°	0.8
75°	0.8
77.5°	0.8
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-MV3F9LC





— 0°-180°







(END OF REPORT)