

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P578818

Luminaire Tested: **FLD6C-65-D010 FEU6C-X-90-40 F6X-N-X-LI**

Issue Date: 3/1/2023



Test Information

Test Method: LM-79-08
Report Number: P578818
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P205310)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/1/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD6C-65-D010 FEU6C-X-90-40 F6X-N-X-LI
Description: 6 INCH FAIL-SAFE LED DOWNLIGHT WITH 4000K, 90 CRI LEDS, 6LBNLI TRIM

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5505.0 lumens
Efficiency: N/A
Efficacy: 76.0 lumens/watt
Spacing Criteria (0/90/45): 0.53 / 0.53 / 0.58
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 72.4
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P578818

CATALOG NUMBER: FLD6C-65-D010 FEU6C-X-90-40 F6X-N-X-LI

Luminous Intensity Polar Plot





TEST NUMBER: P578818

CATALOG NUMBER: FLD6C-65-D010 FEU6C-X-90-40 F6X-N-X-LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	114	112	109	107	112	109	107	106	105	104	102	102	101	99	98	97	96	95			
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	93	91	89			
3	105	99	94	91	103	97	93	90	95	91	89	93	90	87	90	88	86	85			
4	100	93	88	85	98	92	88	84	90	86	83	88	85	82	86	84	81	80			
5	96	88	83	79	94	87	83	79	86	82	78	84	81	78	83	80	77	76			
6	92	84	79	75	90	83	78	75	82	77	74	80	76	74	79	76	73	72			
7	88	80	74	71	87	79	74	71	78	73	70	77	73	70	76	72	69	68			
8	84	76	71	67	83	75	70	67	74	70	67	73	69	66	73	69	66	65			
9	81	73	67	64	80	72	67	64	71	67	63	70	66	63	70	66	63	62			
10	78	69	64	61	77	69	64	61	68	64	61	67	63	60	67	63	60	59			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	687094
5°	642547
10°	524050
15°	385632
20°	265801
25°	197328
30°	148225
35°	92427
40°	44870
45°	15389
50°	2021
55°	1529
60°	877
65°	1038
70°	1282
75°	0
80°	0
85°	0



TEST NUMBER: P578818

CATALOG NUMBER: FLD6C-65-D010 FEU6C-X-90-40 F6X-N-X-LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1042.1	18.9
10°-20°	1870.5	34.0
20°-30°	1512.3	27.5
30°-40°	871.2	15.8
40°-50°	184.2	3.3
50°-60°	15.9	0.3
60°-70°	7.9	0.1
70°-80°	1.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4424.8	80.4
0°-40°	5296.0	96.2
0°-60°	5496.1	99.8
0°-90°	5505.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5505.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	12534	
5°	11676	###
15°	6795	1870
25°	3262	1512
35°	1381	871
45°	198	184
55°	16	16
65°	8	8
75°	0	1
85°	0	0
90°	0	



TEST NUMBER: P578818

CATALOG NUMBER: FLD6C-65-D010 FEU6C-X-90-40 F6X-N-X-LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	12533.6
2.5°	12383.0
5°	11676.4
7.5°	10660.4
10°	9414.2
12.5°	8136.3
15°	6794.8
17.5°	5500.9
20°	4556.2
22.5°	3834.0
25°	3262.3
27.5°	2778.3
30°	2341.6
32.5°	1857.5
35°	1381.1
37.5°	960.4
40°	627.0
42.5°	381.1
45°	198.5
47.5°	79.3
50°	23.7
52.5°	23.7
55°	16.0
57.5°	16.0
60°	8.0
62.5°	8.0
65°	8.0
67.5°	8.0
70°	8.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-MV3F9LC





— 0°-180°







(END OF REPORT)