

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P578828

Luminaire Tested: **FLD6C-65-D010 FEU6C-X-90-40 F6X-W-X-H**

Issue Date: 3/1/2023



**Test Information**

Test Method: LM-79-08  
Report Number: P578828  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P202739)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/1/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: FAIL-SAFE  
Catalog Number: FLD6C-65-D010 FEU6C-X-90-40 F6X-W-X-H  
Description: 6 INCH FAIL-SAFE LED DOWNLIGHT WITH 4000K, 90 CRI LEDS, 6LBWH TRIM

Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 6125.0 lumens  
Efficiency: N/A  
Efficacy: 84.6 lumens/watt  
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.16  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct

Input Watts (W): 72.4  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P578828

CATALOG NUMBER: FLD6C-65-D010 FEU6C-X-90-40 F6X-W-X-H

### Luminous Intensity Polar Plot





TEST NUMBER: P578828

CATALOG NUMBER: FLD6C-65-D010 FEU6C-X-90-40 F6X-W-X-H

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	112	109	106	103	110	107	104	101	103	100	98	99	97	95	95	94	93	91			91
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	85	83	81			81
3	98	90	84	79	96	89	83	78	86	81	77	83	79	76	81	78	75	73			73
4	92	82	75	70	90	81	75	70	79	73	69	77	72	68	75	71	67	65			65
5	86	75	68	63	84	74	68	63	72	66	62	71	65	61	69	64	61	59			59
6	80	69	62	57	78	68	61	56	67	61	56	65	60	56	64	59	55	53			53
7	75	64	56	51	73	63	56	51	62	55	51	60	55	51	59	54	50	49			49
8	70	59	52	47	69	58	51	47	57	51	46	56	50	46	55	50	46	44			44
9	66	55	48	43	65	54	47	43	53	47	43	52	47	42	51	46	42	41			41
10	62	51	44	40	61	50	44	39	50	43	39	49	43	39	48	43	39	38			38

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	207094
5°	207021
10°	205429
15°	204053
20°	200941
25°	196354
30°	184877
35°	167314
40°	139712
45°	107058
50°	75818
55°	47798
60°	26961
65°	17499
70°	11428
75°	8409
80°	5051
85°	5032



TEST NUMBER: P578828

CATALOG NUMBER: FLD6C-65-D010 FEU6C-X-90-40 F6X-W-X-H

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	356.8	5.8
10°-20°	1012.4	16.5
20°-30°	1484.5	24.2
30°-40°	1545.0	25.2
40°-50°	1068.9	17.5
50°-60°	465.4	7.6
60°-70°	142.7	2.3
70°-80°	42.8	0.7
80°-90°	6.5	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2853.7	46.6
0°-40°	4398.7	71.8
0°-60°	5933.0	96.9
0°-90°	6125.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6125.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	3778	
5°	3762	357
15°	3595	1012
25°	3246	1484
35°	2500	1545
45°	1381	1069
55°	500	465
65°	135	143
75°	40	43
85°	8	7
90°	0	



TEST NUMBER: P578828

CATALOG NUMBER: FLD6C-65-D010 FEU6C-X-90-40 F6X-W-X-H

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	3777.7
2.5°	3785.7
5°	3762.0
7.5°	3730.3
10°	3690.4
12.5°	3650.7
15°	3595.4
17.5°	3523.8
20°	3444.4
22.5°	3357.1
25°	3246.2
27.5°	3103.2
30°	2920.6
32.5°	2730.0
35°	2500.1
37.5°	2246.2
40°	1952.3
42.5°	1658.7
45°	1380.9
47.5°	1119.0
50°	889.0
52.5°	674.7
55°	500.1
57.5°	357.2
60°	245.9
62.5°	182.6
65°	134.9
67.5°	103.3
70°	71.3
72.5°	55.6
75°	39.7
77.5°	23.7
80°	16.0
82.5°	8.0
85°	8.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-MV3F9LC







— 0°-180°







(END OF REPORT)