

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P578848

Luminaire Tested: **FLD6C-65-D010 FEU6C-X-90-50 F6X-M-X-H**

Issue Date: 3/1/2023



**Test Information**

Test Method: LM-79-08  
Report Number: P578848  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P203254)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/1/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: FAIL-SAFE  
Catalog Number: FLD6C-65-D010 FEU6C-X-90-50 F6X-M-X-H  
Description: 6 INCH FAIL-SAFE LED DOWNLIGHT WITH 5000K, 90 CRI LEDS, 6LBMH TRIM

Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 5166.0 lumens  
Efficiency: N/A  
Efficacy: 71.4 lumens/watt  
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.93  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct

Input Watts (W): 72.4  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P578848

CATALOG NUMBER: FLD6C-65-D010 FEU6C-X-90-50 F6X-M-X-H

### Luminous Intensity Polar Plot





TEST NUMBER: P578848

CATALOG NUMBER: FLD6C-65-D010 FEU6C-X-90-50 F6X-M-X-H

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	92			92
2	107	102	97	93	105	100	96	92	97	93	90	94	91	88	91	89	87	85			85
3	101	94	88	84	99	92	87	84	90	86	82	87	84	81	85	82	80	78			78
4	95	87	81	76	93	86	80	76	84	79	75	82	78	74	80	76	73	72			72
5	90	81	75	70	88	80	74	70	78	73	69	76	72	68	75	71	68	66			66
6	85	75	69	64	83	75	69	64	73	68	64	72	67	63	70	66	63	61			61
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57			57
8	76	66	60	55	75	65	59	55	64	59	55	63	58	55	62	58	54	53			53
9	72	62	56	51	71	61	55	51	60	55	51	60	55	51	59	54	51	49			49
10	69	58	52	48	68	58	52	48	57	52	48	56	51	48	55	51	48	46			46

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	280274
5°	275252
10°	261190
15°	244928
20°	228103
25°	210175
30°	175122
35°	123426
40°	78662
45°	46912
50°	27692
55°	17615
60°	12126
65°	8613
70°	5930
75°	4681
80°	2305
85°	0



TEST NUMBER: P578848

CATALOG NUMBER: FLD6C-65-D010 FEU6C-X-90-50 F6X-M-X-H

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	467.5	9.0
10°-20°	1209.3	23.4
20°-30°	1566.9	30.3
30°-40°	1163.3	22.5
40°-50°	491.1	9.5
50°-60°	174.4	3.4
60°-70°	67.3	1.3
70°-80°	23.3	0.5
80°-90°	3.0	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3243.7	62.8
0°-40°	4407.0	85.3
0°-60°	5072.4	98.2
0°-90°	5166.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5166.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	5113	
5°	5002	467
15°	4316	1209
25°	3475	1567
35°	1844	1163
45°	605	491
55°	184	174
65°	66	67
75°	22	23
85°	0	3
90°	0	



TEST NUMBER: P578848

CATALOG NUMBER: FLD6C-65-D010 FEU6C-X-90-50 F6X-M-X-H

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	5112.6
2.5°	5097.7
5°	5001.9
7.5°	4861.6
10°	4692.1
12.5°	4507.5
15°	4315.6
17.5°	4101.9
20°	3910.0
22.5°	3710.8
25°	3474.7
27.5°	3150.0
30°	2766.5
32.5°	2316.3
35°	1844.3
37.5°	1446.0
40°	1099.2
42.5°	818.8
45°	605.1
47.5°	442.6
50°	324.7
52.5°	243.4
55°	184.3
57.5°	140.1
60°	110.6
62.5°	81.2
65°	66.4
67.5°	51.5
70°	37.0
72.5°	29.4
75°	22.1
77.5°	14.9
80°	7.3
82.5°	7.3
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-MV3F9LC







— 0°-180°







(END OF REPORT)