

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P577728

Luminaire Tested: **FLD6C-50-D010 FEU6C-X-90-27 F6X-N-X-H**

Issue Date: 3/1/2023



Test Information

Test Method: LM-79-08
Report Number: P577728
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P203666)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/1/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD6C-50-D010 FEU6C-X-90-27 F6X-N-X-H
Description: 6 INCH FAIL-SAFE LED DOWNLIGHT WITH 2700K, 90 CRI LEDS, 6LBNH TRIM

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3263.0 lumens
Efficiency: N/A
Efficacy: 55.9 lumens/watt
Spacing Criteria (0/90/45): 0.78 / 0.78 / 0.84
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 58.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P577728

CATALOG NUMBER: FLD6C-50-D010 FEU6C-X-90-27 F6X-N-X-H

Luminous Intensity Polar Plot





TEST NUMBER: P577728

CATALOG NUMBER: FLD6C-50-D010 FEU6C-X-90-27 F6X-N-X-H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	113	111	108	106	111	109	106	104	104	103	101	101	99	98	97	96	95	93
2	108	103	99	96	106	101	98	94	98	95	92	95	93	90	92	90	89	87
3	102	96	91	87	100	95	90	86	92	88	85	90	86	84	87	85	82	81
4	97	90	84	80	95	89	83	79	86	82	78	84	81	78	83	79	77	75
5	92	84	78	74	91	83	78	73	81	76	73	80	75	72	78	74	72	70
6	88	79	73	69	86	78	72	68	77	72	68	75	71	67	74	70	67	65
7	83	74	68	64	82	73	68	64	72	67	63	71	66	63	70	66	63	61
8	79	70	64	60	78	69	64	60	68	63	59	67	63	59	66	62	59	58
9	76	66	60	56	75	66	60	56	65	59	56	64	59	56	63	59	55	54
10	72	62	57	53	71	62	57	53	61	56	53	60	56	52	60	55	52	51

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	229302
5°	223629
10°	206348
15°	182686
20°	158622
25°	135679
30°	111859
35°	73662
40°	39596
45°	17529
50°	7113
55°	5123
60°	3256
65°	2335
70°	1923
75°	1271
80°	1894
85°	0



TEST NUMBER: P577728

CATALOG NUMBER: FLD6C-50-D010 FEU6C-X-90-27 F6X-N-X-H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	376.1	11.5
10°-20°	897.0	27.5
20°-30°	1027.6	31.5
30°-40°	690.4	21.2
40°-50°	197.3	6.0
50°-60°	48.3	1.5
60°-70°	18.4	0.6
70°-80°	7.1	0.2
80°-90°	0.8	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2300.8	70.5
0°-40°	2991.2	91.7
0°-60°	3236.7	99.2
0°-90°	3263.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3263.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4183	
5°	4064	376
15°	3219	897
25°	2243	1028
35°	1101	690
45°	226	197
55°	54	48
65°	18	18
75°	6	7
85°	0	1
90°	0	



TEST NUMBER: P577728

CATALOG NUMBER: FLD6C-50-D010 FEU6C-X-90-27 F6X-N-X-H

CANDELA DISTRIBUTION (FULL):

	0°
0°	4182.8
2.5°	4153.1
5°	4063.8
7.5°	3903.1
10°	3706.9
12.5°	3456.8
15°	3218.9
17.5°	2969.1
20°	2719.0
22.5°	2481.1
25°	2243.1
27.5°	2022.9
30°	1767.1
32.5°	1427.9
35°	1100.7
37.5°	803.2
40°	553.3
42.5°	362.9
45°	226.1
47.5°	136.8
50°	83.4
52.5°	65.4
55°	53.6
57.5°	41.7
60°	29.7
62.5°	23.7
65°	18.0
67.5°	12.0
70°	12.0
72.5°	6.0
75°	6.0
77.5°	6.0
80°	6.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-MV3F9LC





— 0°-180°







(END OF REPORT)