

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P579278

Luminaire Tested: **FLD6C-75-D010 FEU6C-X-90-30 F6X-M-X-LI**

Issue Date: 3/1/2023



**Test Information**

Test Method: LM-79-08  
Report Number: P579278  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P205108)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/1/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: FAIL-SAFE  
Catalog Number: FLD6C-75-D010 FEU6C-X-90-30 F6X-M-X-LI  
Description: 6 INCH FAIL-SAFE LED DOWNLIGHT WITH 3000K, 90 CRI LEDS, 6LBMLI TRIM

Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 7533.0 lumens  
Efficiency: N/A  
Efficacy: 92.4 lumens/watt  
Spacing Criteria (0/90/45): 0.85 / 0.85 / 0.85  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct

Input Watts (W): 81.5  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P579278

CATALOG NUMBER: FLD6C-75-D010 FEU6C-X-90-30 F6X-M-X-LI

### Luminous Intensity Polar Plot





TEST NUMBER: P579278

CATALOG NUMBER: FLD6C-75-D010 FEU6C-X-90-30 F6X-M-X-LI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	114	111	109	106	111	109	107	105	105	103	101	101	100	98	98	97	96	94				94
2	108	103	100	96	106	102	98	95	99	96	93	96	93	91	93	91	89	88				88
3	103	97	92	88	101	95	91	87	93	89	86	90	87	85	88	85	83	82				82
4	98	91	85	81	96	89	84	81	87	83	80	85	82	79	83	80	78	76				76
5	93	85	79	75	91	84	79	75	82	78	74	81	77	73	79	76	73	71				71
6	89	80	74	70	87	79	74	70	78	73	69	76	72	69	75	71	68	67				67
7	84	75	69	65	83	75	69	65	73	68	65	72	68	64	71	67	64	63				63
8	80	71	65	61	79	70	65	61	69	64	61	68	64	60	67	63	60	59				59
9	77	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55				55
10	73	64	58	54	72	63	58	54	62	57	54	62	57	54	61	57	54	52				52

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	516801
5°	511885
10°	485056
15°	440388
20°	389146
25°	336431
30°	262984
35°	161278
40°	82777
45°	32887
50°	10678
55°	3680
60°	3158
65°	2516
70°	1555
75°	2055
80°	0
85°	0



TEST NUMBER: P579278

CATALOG NUMBER: FLD6C-75-D010 FEU6C-X-90-30 F6X-M-X-LI

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	868.4	11.5
10°-20°	2162.1	28.7
20°-30°	2513.4	33.4
30°-40°	1539.1	20.4
40°-50°	382.2	5.1
50°-60°	44.6	0.6
60°-70°	16.7	0.2
70°-80°	6.4	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5544.0	73.6
0°-40°	7083.1	94.0
0°-60°	7509.9	99.7
0°-90°	7533.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7533.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	9427	
5°	9302	868
15°	7760	2162
25°	5562	2513
35°	2410	1539
45°	424	382
55°	38	45
65°	19	17
75°	10	6
85°	0	0
90°	0	



TEST NUMBER: P579278

CATALOG NUMBER: FLD6C-75-D010 FEU6C-X-90-30 F6X-M-X-LI

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	9427.2
2.5°	9417.5
5°	9302.0
7.5°	9051.2
10°	8713.7
12.5°	8270.5
15°	7759.6
17.5°	7210.2
20°	6670.5
22.5°	6130.4
25°	5562.0
27.5°	4906.4
30°	4154.5
32.5°	3277.3
35°	2409.9
37.5°	1696.4
40°	1156.7
42.5°	722.8
45°	424.2
47.5°	241.1
50°	125.2
52.5°	57.9
55°	38.5
57.5°	28.8
60°	28.8
62.5°	19.4
65°	19.4
67.5°	9.7
70°	9.7
72.5°	9.7
75°	9.7
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-MV3F9LC







— 0°-180°







(END OF REPORT)