

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P577788

Luminaire Tested: **FLD6C-50-D010 FEU6C-X-90-30 F6X-N-X-H**

Issue Date: 3/1/2023



Test Information

Test Method: LM-79-08
Report Number: P577788
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P203666)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/1/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD6C-50-D010 FEU6C-X-90-30 F6X-N-X-H
Description: 6 INCH FAIL-SAFE LED DOWNLIGHT WITH 3000K, 90 CRI LEDS, 6LBNH TRIM

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3392.0 lumens
Efficiency: N/A
Efficacy: 58.1 lumens/watt
Spacing Criteria (0/90/45): 0.78 / 0.78 / 0.84
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 58.4
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P577788

CATALOG NUMBER: FLD6C-50-D010 FEU6C-X-90-30 F6X-N-X-H

Luminous Intensity Polar Plot





TEST NUMBER: P577788

CATALOG NUMBER: FLD6C-50-D010 FEU6C-X-90-30 F6X-N-X-H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	111	108	106	111	109	106	104	104	103	101	101	99	98	97	96	95	93			
2	108	103	99	96	106	101	98	94	98	95	92	95	93	90	92	90	89	87			
3	102	96	91	87	100	95	90	86	92	88	85	90	86	84	87	85	82	81			
4	97	90	84	80	95	89	83	79	86	82	78	84	81	78	83	79	77	75			
5	92	84	78	74	91	83	78	73	81	76	73	80	75	72	78	74	72	70			
6	88	79	73	69	86	78	72	68	77	72	68	75	71	67	74	70	67	65			
7	83	74	68	64	82	73	68	64	72	67	63	71	66	63	70	66	63	61			
8	79	70	64	60	78	69	64	60	68	63	59	67	63	59	66	62	59	58			
9	76	66	60	56	75	66	60	56	65	59	56	64	59	56	63	59	55	54			
10	72	62	57	53	71	62	57	53	61	56	53	60	56	52	60	55	52	51			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	238369
5°	232467
10°	214503
15°	189910
20°	164894
25°	141038
30°	116277
35°	76573
40°	41163
45°	18227
50°	7386
55°	5333
60°	3388
65°	2426
70°	1988
75°	1313
80°	1957
85°	0



TEST NUMBER: P577788

CATALOG NUMBER: FLD6C-50-D010 FEU6C-X-90-30 F6X-N-X-H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	391.0	11.5
10°-20°	932.5	27.5
20°-30°	1068.2	31.5
30°-40°	717.7	21.2
40°-50°	205.1	6.0
50°-60°	50.2	1.5
60°-70°	19.1	0.6
70°-80°	7.4	0.2
80°-90°	0.8	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2391.7	70.5
0°-40°	3109.4	91.7
0°-60°	3364.7	99.2
0°-90°	3392.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3392.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4348	
5°	4224	391
15°	3346	932
25°	2332	1068
35°	1144	718
45°	235	205
55°	56	50
65°	19	19
75°	6	7
85°	0	1
90°	0	



TEST NUMBER: P577788

CATALOG NUMBER: FLD6C-50-D010 FEU6C-X-90-30 F6X-N-X-H

CANDELA DISTRIBUTION (FULL):

	0°
0°	4348.2
2.5°	4317.3
5°	4224.4
7.5°	4057.4
10°	3853.4
12.5°	3593.5
15°	3346.2
17.5°	3086.5
20°	2826.5
22.5°	2579.2
25°	2331.7
27.5°	2102.9
30°	1836.9
32.5°	1484.4
35°	1144.2
37.5°	834.9
40°	575.2
42.5°	377.3
45°	235.1
47.5°	142.2
50°	86.6
52.5°	68.0
55°	55.8
57.5°	43.3
60°	30.9
62.5°	24.7
65°	18.7
67.5°	12.4
70°	12.4
72.5°	6.2
75°	6.2
77.5°	6.2
80°	6.2
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-MV3F9LC





— 0°-180°







(END OF REPORT)