

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P579338

Luminaire Tested: **FLD6C-75-D010 FEU6C-X-90-35 F6X-M-X-LI**

Issue Date: 3/1/2023



**Test Information**

Test Method: LM-79-08  
Report Number: P579338  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P205108)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/1/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: FAIL-SAFE  
Catalog Number: FLD6C-75-D010 FEU6C-X-90-35 F6X-M-X-LI  
Description: 6 INCH FAIL-SAFE LED DOWNLIGHT WITH 3500K, 90 CRI LEDS, 6LBMLI TRIM

Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 7638.9 lumens  
Efficiency: N/A  
Efficacy: 93.7 lumens/watt  
Spacing Criteria (0/90/45): 0.85 / 0.85 / 0.85  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct

Input Watts (W): 81.5  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P579338

CATALOG NUMBER: FLD6C-75-D010 FEU6C-X-90-35 F6X-M-X-LI

### Luminous Intensity Polar Plot





TEST NUMBER: P579338

CATALOG NUMBER: FLD6C-75-D010 FEU6C-X-90-35 F6X-M-X-LI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	114	111	109	106	111	109	107	105	105	103	101	101	100	98	98	97	96	94			
2	108	103	100	96	106	102	98	95	99	96	93	96	93	91	93	91	89	88			
3	103	97	92	88	101	95	91	87	93	89	86	90	87	85	88	85	83	82			
4	98	91	85	81	96	89	84	81	87	83	80	85	82	79	83	80	78	76			
5	93	85	79	75	91	84	79	75	82	78	74	81	77	73	79	76	73	71			
6	89	80	74	70	87	79	74	70	78	73	69	76	72	69	75	71	68	67			
7	84	75	69	65	83	75	69	65	73	68	65	72	68	64	71	67	64	63			
8	80	71	65	61	79	70	65	61	69	64	61	68	64	60	67	63	60	59			
9	77	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55			
10	73	64	58	54	72	63	58	54	62	57	54	62	57	54	61	57	54	52			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	524070
5°	519088
10°	491880
15°	446586
20°	394618
25°	341161
30°	266680
35°	163547
40°	83943
45°	33352
50°	10831
55°	3727
60°	3201
65°	2555
70°	1571
75°	2076
80°	0
85°	0



TEST NUMBER: P579338

CATALOG NUMBER: FLD6C-75-D010 FEU6C-X-90-35 F6X-M-X-LI

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	880.7	11.5
10°-20°	2192.6	28.7
20°-30°	2548.7	33.4
30°-40°	1560.8	20.4
40°-50°	387.6	5.1
50°-60°	45.3	0.6
60°-70°	16.9	0.2
70°-80°	6.4	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5622.0	73.6
0°-40°	7182.7	94.0
0°-60°	7615.6	99.7
0°-90°	7638.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7638.9	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	9560	
5°	9433	881
15°	7869	2193
25°	5640	2549
35°	2444	1561
45°	430	388
55°	39	45
65°	20	17
75°	10	6
85°	0	0
90°	0	



TEST NUMBER: P579338

CATALOG NUMBER: FLD6C-75-D010 FEU6C-X-90-35 F6X-M-X-LI

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	9559.8
2.5°	9550.0
5°	9432.9
7.5°	9178.6
10°	8836.3
12.5°	8386.8
15°	7868.8
17.5°	7311.6
20°	6764.3
22.5°	6216.7
25°	5640.2
27.5°	4975.5
30°	4212.9
32.5°	3323.4
35°	2443.8
37.5°	1720.3
40°	1173.0
42.5°	733.0
45°	430.2
47.5°	244.4
50°	127.0
52.5°	58.7
55°	39.0
57.5°	29.2
60°	29.2
62.5°	19.7
65°	19.7
67.5°	9.8
70°	9.8
72.5°	9.8
75°	9.8
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-MV3F9LC







— 0°-180°







(END OF REPORT)