

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P578148

Luminaire Tested: **FLD6C-55-D010 FEU6C-X-90-35 F6X-N-X-H**

Issue Date: 3/1/2023



Test Information

Test Method: LM-79-08
Report Number: P578148
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P203666)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/1/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD6C-55-D010 FEU6C-X-90-35 F6X-N-X-H
Description: 6 INCH FAIL-SAFE LED DOWNLIGHT WITH 3500K, 90 CRI LEDS, 6LBNH TRIM

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3845.1 lumens
Efficiency: N/A
Efficacy: 60.2 lumens/watt
Spacing Criteria (0/90/45): 0.78 / 0.78 / 0.84
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 63.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P578148

CATALOG NUMBER: FLD6C-55-D010 FEU6C-X-90-35 F6X-N-X-H

Luminous Intensity Polar Plot





TEST NUMBER: P578148

CATALOG NUMBER: FLD6C-55-D010 FEU6C-X-90-35 F6X-N-X-H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	111	108	106	111	109	106	104	104	103	101	101	99	98	97	96	95	93			
2	108	103	99	96	106	101	98	94	98	95	92	95	93	90	92	90	89	87			
3	102	96	91	87	100	95	90	86	92	88	85	90	86	84	87	85	82	81			
4	97	90	84	80	95	89	83	79	86	82	78	84	81	78	83	79	77	75			
5	92	84	78	74	91	83	78	73	81	76	73	80	75	72	78	74	72	70			
6	88	79	73	69	86	78	72	68	77	72	68	75	71	67	74	70	67	65			
7	83	74	68	64	82	73	68	64	72	67	63	71	66	63	70	66	63	61			
8	79	70	64	60	78	69	64	60	68	63	59	67	63	59	66	62	59	58			
9	76	66	60	56	75	66	60	56	65	59	56	64	59	56	63	59	55	54			
10	72	62	57	53	71	62	57	53	61	56	53	60	56	52	60	55	52	51			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	270203
5°	263515
10°	243148
15°	215274
20°	186916
25°	159874
30°	131811
35°	86799
40°	46659
45°	20661
50°	8375
55°	6040
60°	3837
65°	2750
70°	2260
75°	1504
80°	2241
85°	0



TEST NUMBER: P578148

CATALOG NUMBER: FLD6C-55-D010 FEU6C-X-90-35 F6X-N-X-H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	443.2	11.5
10°-20°	1057.0	27.5
20°-30°	1210.9	31.5
30°-40°	813.6	21.2
40°-50°	232.4	6.0
50°-60°	56.9	1.5
60°-70°	21.7	0.6
70°-80°	8.4	0.2
80°-90°	1.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2711.1	70.5
0°-40°	3524.7	91.7
0°-60°	3814.0	99.2
0°-90°	3845.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3845.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4929	
5°	4789	443
15°	3793	1057
25°	2643	1211
35°	1297	814
45°	266	232
55°	63	57
65°	21	22
75°	7	8
85°	0	1
90°	0	



TEST NUMBER: P578148

CATALOG NUMBER: FLD6C-55-D010 FEU6C-X-90-35 F6X-N-X-H

CANDELA DISTRIBUTION (FULL):

	0°
0°	4928.9
2.5°	4893.9
5°	4788.6
7.5°	4599.2
10°	4368.0
12.5°	4073.4
15°	3793.1
17.5°	3498.7
20°	3204.0
22.5°	2923.7
25°	2643.1
27.5°	2383.7
30°	2082.3
32.5°	1682.6
35°	1297.0
37.5°	946.4
40°	652.0
42.5°	427.6
45°	266.5
47.5°	161.2
50°	98.2
52.5°	77.1
55°	63.2
57.5°	49.1
60°	35.0
62.5°	28.0
65°	21.2
67.5°	14.1
70°	14.1
72.5°	7.1
75°	7.1
77.5°	7.1
80°	7.1
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-MV3F9LC





— 0°-180°







(END OF REPORT)