

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P578168

Luminaire Tested: **FLD6C-55-D010 FEU6C-X-90-35 F6X-W-X-H**

Issue Date: 3/1/2023



Test Information

Test Method: LM-79-08
Report Number: P578168
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P202739)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/1/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD6C-55-D010 FEU6C-X-90-35 F6X-W-X-H
Description: 6 INCH FAIL-SAFE LED DOWNLIGHT WITH 3500K, 90 CRI LEDS, 6LBWH TRIM

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5409.0 lumens
Efficiency: N/A
Efficacy: 84.6 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.16
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 63.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P578168

CATALOG NUMBER: FLD6C-55-D010 FEU6C-X-90-35 F6X-W-X-H

Luminous Intensity Polar Plot





TEST NUMBER: P578168

CATALOG NUMBER: FLD6C-55-D010 FEU6C-X-90-35 F6X-W-X-H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	112	109	106	103	110	107	104	101	103	100	98	99	97	95	95	94	93	91				91
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	85	83	81				81
3	98	90	84	79	96	89	83	78	86	81	77	83	79	76	81	78	75	73				73
4	92	82	75	70	90	81	75	70	79	73	69	77	72	68	75	71	67	65				65
5	86	75	68	63	84	74	68	63	72	66	62	71	65	61	69	64	61	59				59
6	80	69	62	57	78	68	61	56	67	61	56	65	60	56	64	59	55	53				53
7	75	64	56	51	73	63	56	51	62	55	51	60	55	51	59	54	50	49				49
8	70	59	52	47	69	58	51	47	57	51	46	56	50	46	55	50	46	44				44
9	66	55	48	43	65	54	47	43	53	47	43	52	47	42	51	46	42	41				41
10	62	51	44	40	61	50	44	39	50	43	39	49	43	39	48	43	39	38				38

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	182886
5°	182819
10°	181415
15°	180200
20°	177454
25°	173399
30°	163266
35°	147753
40°	123381
45°	94537
50°	66957
55°	42216
60°	23814
65°	15462
70°	10098
75°	7413
80°	4451
85°	4466



TEST NUMBER: P578168

CATALOG NUMBER: FLD6C-55-D010 FEU6C-X-90-35 F6X-W-X-H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	315.1	5.8
10°-20°	894.1	16.5
20°-30°	1310.9	24.2
30°-40°	1364.4	25.2
40°-50°	943.9	17.5
50°-60°	411.0	7.6
60°-70°	126.0	2.3
70°-80°	37.8	0.7
80°-90°	5.8	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2520.1	46.6
0°-40°	3884.5	71.8
0°-60°	5239.4	96.9
0°-90°	5409.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5409.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3336	
5°	3322	315
15°	3175	894
25°	2867	1311
35°	2208	1364
45°	1219	944
55°	442	411
65°	119	126
75°	35	38
85°	7	6
90°	0	



TEST NUMBER: P578168

CATALOG NUMBER: FLD6C-55-D010 FEU6C-X-90-35 F6X-W-X-H

CANDELA DISTRIBUTION (FULL):

0°	
0°	3336.1
2.5°	3343.1
5°	3322.2
7.5°	3294.3
10°	3259.0
12.5°	3224.0
15°	3175.1
17.5°	3111.8
20°	3041.8
22.5°	2964.7
25°	2866.7
27.5°	2740.5
30°	2579.2
32.5°	2410.9
35°	2207.8
37.5°	1983.6
40°	1724.1
42.5°	1464.8
45°	1219.4
47.5°	988.1
50°	785.1
52.5°	595.9
55°	441.7
57.5°	315.4
60°	217.2
62.5°	161.2
65°	119.2
67.5°	91.2
70°	63.0
72.5°	49.1
75°	35.0
77.5°	20.9
80°	14.1
82.5°	7.1
85°	7.1
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-MV3F9LC





— 0°-180°







(END OF REPORT)