

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P578278

Luminaire Tested: **FLD6C-55-D010 FEU6C-X-90-50 F6X-N-X-LI**

Issue Date: 3/1/2023



**Test Information**

Test Method: LM-79-08  
Report Number: P578278  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P205310)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/1/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: FAIL-SAFE  
Catalog Number: FLD6C-55-D010 FEU6C-X-90-50 F6X-N-X-LI  
Description: 6 INCH FAIL-SAFE LED DOWNLIGHT WITH 5000K, 90 CRI LEDS, 6LBNLI TRIM

Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 4969.0 lumens  
Efficiency: N/A  
Efficacy: 77.8 lumens/watt  
Spacing Criteria (0/90/45): 0.53 / 0.53 / 0.58  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct

Input Watts (W): 63.9  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P578278

CATALOG NUMBER: FLD6C-55-D010 FEU6C-X-90-50 F6X-N-X-LI

### Luminous Intensity Polar Plot





TEST NUMBER: P578278

CATALOG NUMBER: FLD6C-55-D010 FEU6C-X-90-50 F6X-N-X-LI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	114	112	109	107	112	109	107	106	105	104	102	102	101	99	98	97	96	95			
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	93	91	89			
3	105	99	94	91	103	97	93	90	95	91	89	93	90	87	90	88	86	85			
4	100	93	88	85	98	92	88	84	90	86	83	88	85	82	86	84	81	80			
5	96	88	83	79	94	87	83	79	86	82	78	84	81	78	83	80	77	76			
6	92	84	79	75	90	83	78	75	82	77	74	80	76	74	79	76	73	72			
7	88	80	74	71	87	79	74	71	78	73	70	77	73	70	76	72	69	68			
8	84	76	71	67	83	75	70	67	74	70	67	73	69	66	73	69	66	65			
9	81	73	67	64	80	72	67	64	71	67	63	70	66	63	70	66	63	62			
10	78	69	64	61	77	69	64	61	68	64	61	67	63	60	67	63	60	59			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	620192
5°	579984
10°	473021
15°	348084
20°	239923
25°	178117
30°	133793
35°	83433
40°	40497
45°	13893
50°	1825
55°	1376
60°	789
65°	934
70°	1154
75°	0
80°	0
85°	0



TEST NUMBER: P578278

CATALOG NUMBER: FLD6C-55-D010 FEU6C-X-90-50 F6X-N-X-LI

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	940.6	18.9
10°-20°	1688.3	34.0
20°-30°	1365.1	27.5
30°-40°	786.3	15.8
40°-50°	166.2	3.3
50°-60°	14.3	0.3
60°-70°	7.1	0.1
70°-80°	0.9	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3994.0	80.4
0°-40°	4780.3	96.2
0°-60°	4960.9	99.8
0°-90°	4969.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4969.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	11313	
5°	10540	941
15°	6133	1688
25°	2945	1365
35°	1247	786
45°	179	166
55°	14	14
65°	7	7
75°	0	1
85°	0	0
90°	0	



TEST NUMBER: P578278

CATALOG NUMBER: FLD6C-55-D010 FEU6C-X-90-50 F6X-N-X-LI

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	11313.2
2.5°	11177.3
5°	10539.5
7.5°	9622.4
10°	8497.5
12.5°	7344.1
15°	6133.2
17.5°	4965.3
20°	4112.6
22.5°	3460.7
25°	2944.7
27.5°	2507.8
30°	2113.6
32.5°	1676.6
35°	1246.7
37.5°	866.9
40°	565.9
42.5°	344.0
45°	179.2
47.5°	71.6
50°	21.4
52.5°	21.4
55°	14.4
57.5°	14.4
60°	7.2
62.5°	7.2
65°	7.2
67.5°	7.2
70°	7.2
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-MV3F9LC







— 0°-180°







(END OF REPORT)