

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P574428

Luminaire Tested: **FLD6C-08-D010 FEU6C-X-90-27 F6X-N-X-H**

Issue Date: 3/1/2023



**Test Information**

Test Method: LM-79-08  
Report Number: P574428  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P203666)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/1/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: FAIL-SAFE  
Catalog Number: FLD6C-08-D010 FEU6C-X-90-27 F6X-N-X-H  
Description: 6 INCH FAIL-SAFE LED DOWNLIGHT WITH 2700K, 90 CRI LEDS, 6LBNH TRIM

Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 544.0 lumens  
Efficiency: N/A  
Efficacy: 55.1 lumens/watt  
Spacing Criteria (0/90/45): 0.78 / 0.78 / 0.84  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct

Input Watts (W): 9.87  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P574428

CATALOG NUMBER: FLD6C-08-D010 FEU6C-X-90-27 F6X-N-X-H

### Luminous Intensity Polar Plot





TEST NUMBER: P574428

CATALOG NUMBER: FLD6C-08-D010 FEU6C-X-90-27 F6X-N-X-H

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	111	108	106	111	109	106	104	104	103	101	101	99	98	97	96	95	93			
2	108	103	99	96	106	101	98	94	98	95	92	95	93	90	92	90	89	87			
3	102	96	91	87	100	95	90	86	92	88	85	90	86	84	87	85	82	81			
4	97	90	84	80	95	89	83	79	86	82	78	84	81	78	83	79	77	75			
5	92	84	78	74	91	83	78	73	81	76	73	80	75	72	78	74	72	70			
6	88	79	73	69	86	78	72	68	77	72	68	75	71	67	74	70	67	65			
7	83	74	68	64	82	73	68	64	72	67	63	71	66	63	70	66	63	61			
8	79	70	64	60	78	69	64	60	68	63	59	67	63	59	66	62	59	58			
9	76	66	60	56	75	66	60	56	65	59	56	64	59	56	63	59	55	54			
10	72	62	57	53	71	62	57	53	61	56	53	60	56	52	60	55	52	51			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	38232
5°	37283
10°	34402
15°	30460
20°	26445
25°	22622
30°	18648
35°	12280
40°	6605
45°	2923
50°	1185
55°	851
60°	548
65°	389
70°	321
75°	212
80°	316
85°	0



TEST NUMBER: P574428

CATALOG NUMBER: FLD6C-08-D010 FEU6C-X-90-27 F6X-N-X-H

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	62.7	11.5
10°-20°	149.5	27.5
20°-30°	171.3	31.5
30°-40°	115.1	21.2
40°-50°	32.9	6.0
50°-60°	8.0	1.5
60°-70°	3.1	0.6
70°-80°	1.2	0.2
80°-90°	0.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	383.6	70.5
0°-40°	498.7	91.7
0°-60°	539.6	99.2
0°-90°	544.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	544.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	697	
5°	678	63
15°	537	150
25°	374	171
35°	184	115
45°	38	33
55°	9	8
65°	3	3
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P574428

CATALOG NUMBER: FLD6C-08-D010 FEU6C-X-90-27 F6X-N-X-H

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	697.4
2.5°	692.4
5°	677.5
7.5°	650.7
10°	618.0
12.5°	576.3
15°	536.7
17.5°	495.0
20°	453.3
22.5°	413.7
25°	374.0
27.5°	337.3
30°	294.6
32.5°	238.1
35°	183.5
37.5°	133.9
40°	92.3
42.5°	60.5
45°	37.7
47.5°	22.8
50°	13.9
52.5°	10.9
55°	8.9
57.5°	6.9
60°	5.0
62.5°	4.0
65°	3.0
67.5°	2.0
70°	2.0
72.5°	1.0
75°	1.0
77.5°	1.0
80°	1.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-MV3F9LC







— 0°-180°







(END OF REPORT)