

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P578308

Luminaire Tested: **FLD6C-60-D010 FEU6C-X-90-27 F6X-M-X-H**

Issue Date: 3/1/2023



Test Information

Test Method: LM-79-08
Report Number: P578308
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P203254)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/1/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD6C-60-D010 FEU6C-X-90-27 F6X-M-X-H
Description: 6 INCH FAIL-SAFE LED DOWNLIGHT WITH 2700K, 90 CRI LEDS, 6LBMH TRIM

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4583.0 lumens
Efficiency: N/A
Efficacy: 63.7 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.93
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 72
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P578308

CATALOG NUMBER: FLD6C-60-D010 FEU6C-X-90-27 F6X-M-X-H

Luminous Intensity Polar Plot





TEST NUMBER: P578308

CATALOG NUMBER: FLD6C-60-D010 FEU6C-X-90-27 F6X-M-X-H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	92																			
2	107	102	97	93	105	100	96	92	97	93	90	94	91	88	91	89	87	85																			
3	101	94	88	84	99	92	87	84	90	86	82	87	84	81	85	82	80	78																			
4	95	87	81	76	93	86	80	76	84	79	75	82	78	74	80	76	73	72																			
5	90	81	75	70	88	80	74	70	78	73	69	76	72	68	75	71	68	66																			
6	85	75	69	64	83	75	69	64	73	68	64	72	67	63	70	66	63	61																			
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57																			
8	76	66	60	55	75	65	59	55	64	59	55	63	58	55	62	58	54	53																			
9	72	62	56	51	71	61	55	51	60	55	51	60	55	51	59	54	51	49																			
10	69	58	52	48	68	58	52	48	57	52	48	56	51	48	55	51	48	46																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	248642
5°	244188
10°	231715
15°	217288
20°	202358
25°	186452
30°	155359
35°	109500
40°	69788
45°	41617
50°	24562
55°	15627
60°	10767
65°	7640
70°	5257
75°	4151
80°	2052
85°	0



TEST NUMBER: P578308

CATALOG NUMBER: FLD6C-60-D010 FEU6C-X-90-27 F6X-M-X-H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	414.7	9.0
10°-20°	1072.8	23.4
20°-30°	1390.1	30.3
30°-40°	1032.0	22.5
40°-50°	435.7	9.5
50°-60°	154.7	3.4
60°-70°	59.7	1.3
70°-80°	20.7	0.5
80°-90°	2.6	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2877.6	62.8
0°-40°	3909.6	85.3
0°-60°	4500.0	98.2
0°-90°	4583.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4583.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4536	
5°	4437	415
15°	3829	1073
25°	3082	1390
35°	1636	1032
45°	537	436
55°	164	155
65°	59	60
75°	20	21
85°	0	3
90°	0	



TEST NUMBER: P578308

CATALOG NUMBER: FLD6C-60-D010 FEU6C-X-90-27 F6X-M-X-H

CANDELA DISTRIBUTION (FULL):

0°	
0°	4535.6
2.5°	4522.4
5°	4437.4
7.5°	4312.9
10°	4162.6
12.5°	3998.8
15°	3828.6
17.5°	3639.0
20°	3468.7
22.5°	3292.0
25°	3082.5
27.5°	2794.5
30°	2454.3
32.5°	2054.9
35°	1636.2
37.5°	1282.8
40°	975.2
42.5°	726.4
45°	536.8
47.5°	392.6
50°	288.0
52.5°	216.0
55°	163.5
57.5°	124.3
60°	98.2
62.5°	72.1
65°	58.9
67.5°	45.7
70°	32.8
72.5°	26.1
75°	19.6
77.5°	13.2
80°	6.5
82.5°	6.5
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-MV3F9LC





— 0°-180°







(END OF REPORT)