

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P578348

Luminaire Tested: **FLD6C-60-D010 FEU6C-X-90-27 F6X-W-X-H**

Issue Date: 3/1/2023



Test Information

Test Method: LM-79-08
Report Number: P578348
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P202739)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/1/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD6C-60-D010 FEU6C-X-90-27 F6X-W-X-H
Description: 6 INCH FAIL-SAFE LED DOWNLIGHT WITH 2700K, 90 CRI LEDS, 6LBWH TRIM

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5547.0 lumens
Efficiency: N/A
Efficacy: 77.0 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.16
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 72
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P578348

CATALOG NUMBER: FLD6C-60-D010 FEU6C-X-90-27 F6X-W-X-H

Luminous Intensity Polar Plot





TEST NUMBER: P578348

CATALOG NUMBER: FLD6C-60-D010 FEU6C-X-90-27 F6X-W-X-H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20																	
RC	80									70									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																								
RCR																																																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																																				
1	112	109	106	103	110	107	104	101	103	100	98	99	97	95	95	94	93	91																																				
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	85	83	81																																				
3	98	90	84	79	96	89	83	78	86	81	77	83	79	76	81	78	75	73																																				
4	92	82	75	70	90	81	75	70	79	73	69	77	72	68	75	71	67	65																																				
5	86	75	68	63	84	74	68	63	72	66	62	71	65	61	69	64	61	59																																				
6	80	69	62	57	78	68	61	56	67	61	56	65	60	56	64	59	55	53																																				
7	75	64	56	51	73	63	56	51	62	55	51	60	55	51	59	54	50	49																																				
8	70	59	52	47	69	58	51	47	57	51	46	56	50	46	55	50	46	44																																				
9	66	55	48	43	65	54	47	43	53	47	43	52	47	42	51	46	42	41																																				
10	62	51	44	40	61	50	44	39	50	43	39	49	43	39	48	43	39	38																																				

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	187551
5°	187486
10°	186041
15°	184797
20°	181981
25°	177821
30°	167431
35°	151527
40°	126530
45°	96956
50°	68663
55°	43286
60°	24417
65°	15851
70°	10354
75°	7604
80°	4578
85°	4529



TEST NUMBER: P578348

CATALOG NUMBER: FLD6C-60-D010 FEU6C-X-90-27 F6X-W-X-H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	323.1	5.8
10°-20°	916.9	16.5
20°-30°	1344.4	24.2
30°-40°	1399.2	25.2
40°-50°	968.0	17.5
50°-60°	421.5	7.6
60°-70°	129.3	2.3
70°-80°	38.7	0.7
80°-90°	5.9	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2584.4	46.6
0°-40°	3983.6	71.8
0°-60°	5373.1	96.9
0°-90°	5547.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5547.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3421	
5°	3407	323
15°	3256	917
25°	2940	1344
35°	2264	1399
45°	1251	968
55°	453	421
65°	122	129
75°	36	39
85°	7	6
90°	0	



TEST NUMBER: P578348

CATALOG NUMBER: FLD6C-60-D010 FEU6C-X-90-27 F6X-W-X-H

CANDELA DISTRIBUTION (FULL):

0°	
0°	3421.2
2.5°	3428.4
5°	3407.0
7.5°	3378.3
10°	3342.1
12.5°	3306.2
15°	3256.1
17.5°	3191.2
20°	3119.4
22.5°	3040.3
25°	2939.8
27.5°	2810.4
30°	2645.0
32.5°	2472.4
35°	2264.2
37.5°	2034.2
40°	1768.1
42.5°	1502.2
45°	1250.6
47.5°	1013.4
50°	805.1
52.5°	611.1
55°	452.9
57.5°	323.5
60°	222.7
62.5°	165.4
65°	122.2
67.5°	93.5
70°	64.6
72.5°	50.4
75°	35.9
77.5°	21.4
80°	14.5
82.5°	7.2
85°	7.2
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-MV3F9LC





— 0°-180°







(END OF REPORT)