

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P574528

Luminaire Tested: **FLD6C-08-D010 FEU6C-X-90-35 F6X-M-X-H**

Issue Date: 3/1/2023



**Test Information**

Test Method: LM-79-08  
Report Number: P574528  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P203254)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/1/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: FAIL-SAFE  
Catalog Number: FLD6C-08-D010 FEU6C-X-90-35 F6X-M-X-H  
Description: 6 INCH FAIL-SAFE LED DOWNLIGHT WITH 3500K, 90 CRI LEDS, 6LBMH TRIM

Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 666.1 lumens  
Efficiency: N/A  
Efficacy: 67.5 lumens/watt  
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.93  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct

Input Watts (W): 9.87  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P574528

CATALOG NUMBER: FLD6C-08-D010 FEU6C-X-90-35 F6X-M-X-H

### Luminous Intensity Polar Plot





TEST NUMBER: P574528

CATALOG NUMBER: FLD6C-08-D010 FEU6C-X-90-35 F6X-M-X-H

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	92	92	92	92
2	107	102	97	93	105	100	96	92	97	93	90	94	91	88	91	89	87	85	85	85	85
3	101	94	88	84	99	92	87	83	90	86	82	87	84	81	85	82	80	78	78	78	78
4	95	87	81	76	93	86	80	76	84	79	75	82	78	74	80	76	73	72	72	72	72
5	90	81	75	70	88	80	74	70	78	73	69	76	72	68	75	71	68	66	66	66	66
6	85	75	69	64	83	75	69	64	73	68	64	72	67	63	70	66	63	61	61	61	61
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57	57	57	57
8	76	66	60	55	75	65	59	55	64	59	55	63	58	55	62	58	54	53	53	53	53
9	72	62	56	51	71	61	55	51	60	55	51	60	55	51	59	54	51	49	49	49	49
10	69	58	52	48	68	58	52	48	57	52	48	56	51	48	55	51	48	46	46	46	46

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	36132
5°	35483
10°	33672
15°	31578
20°	29408
25°	27098
30°	22579
35°	15914
40°	10140
45°	6047
50°	3573
55°	2275
60°	1568
65°	1116
70°	769
75°	614
80°	284
85°	0



TEST NUMBER: P574528

CATALOG NUMBER: FLD6C-08-D010 FEU6C-X-90-35 F6X-M-X-H

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	60.3	9.0
10°-20°	155.9	23.4
20°-30°	202.0	30.3
30°-40°	150.0	22.5
40°-50°	63.3	9.5
50°-60°	22.5	3.4
60°-70°	8.7	1.3
70°-80°	3.0	0.5
80°-90°	0.4	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	418.2	62.8
0°-40°	568.2	85.3
0°-60°	654.0	98.2
0°-90°	666.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	666.1	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	659	
5°	645	60
15°	556	156
25°	448	202
35°	238	150
45°	78	63
55°	24	23
65°	9	9
75°	3	3
85°	0	0
90°	0	



TEST NUMBER: P574528

CATALOG NUMBER: FLD6C-08-D010 FEU6C-X-90-35 F6X-M-X-H

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	659.1
2.5°	657.2
5°	644.8
7.5°	626.8
10°	604.9
12.5°	581.1
15°	556.4
17.5°	528.8
20°	504.1
22.5°	478.4
25°	448.0
27.5°	406.1
30°	356.7
32.5°	298.6
35°	237.8
37.5°	186.4
40°	141.7
42.5°	105.6
45°	78.0
47.5°	57.1
50°	41.9
52.5°	31.4
55°	23.8
57.5°	18.1
60°	14.3
62.5°	10.5
65°	8.6
67.5°	6.6
70°	4.8
72.5°	3.8
75°	2.9
77.5°	1.9
80°	0.9
82.5°	0.9
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-MV3F9LC







— 0°-180°







(END OF REPORT)