

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P578528

Luminaire Tested: **FLD6C-60-D010 FEU6C-X-90-40 F6X-W-X-H**

Issue Date: 3/1/2023



**Test Information**

Test Method: LM-79-08  
Report Number: P578528  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P202739)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/1/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: FAIL-SAFE  
Catalog Number: FLD6C-60-D010 FEU6C-X-90-40 F6X-W-X-H  
Description: 6 INCH FAIL-SAFE LED DOWNLIGHT WITH 4000K, 90 CRI LEDS, 6LBWH TRIM

Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 5856.0 lumens  
Efficiency: N/A  
Efficacy: 81.3 lumens/watt  
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.16  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct

Input Watts (W): 72  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P578528

CATALOG NUMBER: FLD6C-60-D010 FEU6C-X-90-40 F6X-W-X-H

### Luminous Intensity Polar Plot





TEST NUMBER: P578528

CATALOG NUMBER: FLD6C-60-D010 FEU6C-X-90-40 F6X-W-X-H

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |    |    |   |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|---|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     | 20  |     |    |    |   |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |     | 30  |     |     |     | 10  |     |    | 0  |   |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30 | 10 | 0 |
| RCR |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |    |    |   |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 |    |    |   |
| 1   | 112 | 109 | 106 | 103 | 110 | 107 | 104 | 101 | 103 | 100 | 98  | 99  | 97  | 95  | 95  | 94  | 93  | 91  |    |    |   |
| 2   | 105 | 99  | 94  | 90  | 103 | 97  | 93  | 89  | 94  | 90  | 87  | 91  | 88  | 85  | 88  | 85  | 83  | 81  |    |    |   |
| 3   | 98  | 90  | 84  | 79  | 96  | 89  | 83  | 78  | 86  | 81  | 77  | 83  | 79  | 76  | 81  | 78  | 75  | 73  |    |    |   |
| 4   | 92  | 82  | 75  | 70  | 90  | 81  | 75  | 70  | 79  | 73  | 69  | 77  | 72  | 68  | 75  | 71  | 67  | 65  |    |    |   |
| 5   | 86  | 75  | 68  | 63  | 84  | 74  | 68  | 63  | 72  | 66  | 62  | 71  | 65  | 61  | 69  | 64  | 61  | 59  |    |    |   |
| 6   | 80  | 69  | 62  | 57  | 78  | 68  | 61  | 56  | 67  | 61  | 56  | 65  | 60  | 56  | 64  | 59  | 55  | 53  |    |    |   |
| 7   | 75  | 64  | 56  | 51  | 73  | 63  | 56  | 51  | 62  | 55  | 51  | 60  | 55  | 51  | 59  | 54  | 50  | 49  |    |    |   |
| 8   | 70  | 59  | 52  | 47  | 69  | 58  | 51  | 47  | 57  | 51  | 46  | 56  | 50  | 46  | 55  | 50  | 46  | 44  |    |    |   |
| 9   | 66  | 55  | 48  | 43  | 65  | 54  | 47  | 43  | 53  | 47  | 43  | 52  | 47  | 42  | 51  | 46  | 42  | 41  |    |    |   |
| 10  | 62  | 51  | 44  | 40  | 61  | 50  | 44  | 39  | 50  | 43  | 39  | 49  | 43  | 39  | 48  | 43  | 39  | 38  |    |    |   |

**AVERAGE LUMINANCE (cd/sqm):**

|     |        |
|-----|--------|
|     | 0°     |
| 0°  | 197999 |
| 5°  | 197930 |
| 10° | 196406 |
| 15° | 195092 |
| 20° | 192120 |
| 25° | 187729 |
| 30° | 176761 |
| 35° | 159966 |
| 40° | 133579 |
| 45° | 102352 |
| 50° | 72492  |
| 55° | 45704  |
| 60° | 25776  |
| 65° | 16733  |
| 70° | 10931  |
| 75° | 8028   |
| 80° | 4830   |
| 85° | 4780   |



TEST NUMBER: P578528

CATALOG NUMBER: FLD6C-60-D010 FEU6C-X-90-40 F6X-W-X-H

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 341.1  | 5.8       |
| 10°-20°   | 968.0  | 16.5      |
| 20°-30°   | 1419.3 | 24.2      |
| 30°-40°   | 1477.1 | 25.2      |
| 40°-50°   | 1021.9 | 17.5      |
| 50°-60°   | 445.0  | 7.6       |
| 60°-70°   | 136.4  | 2.3       |
| 70°-80°   | 40.9   | 0.7       |
| 80°-90°   | 6.2    | 0.1       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 2728.4 | 46.6      |
| 0°-40°    | 4205.5 | 71.8      |
| 0°-60°    | 5672.4 | 96.9      |
| 0°-90°    | 5856.0 | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 5856.0 | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°   | Flux |
|-----|------|------|
| 0°  | 3612 |      |
| 5°  | 3597 | 341  |
| 15° | 3438 | 968  |
| 25° | 3104 | 1419 |
| 35° | 2390 | 1477 |
| 45° | 1320 | 1022 |
| 55° | 478  | 445  |
| 65° | 129  | 136  |
| 75° | 38   | 41   |
| 85° | 8    | 6    |
| 90° | 0    |      |



TEST NUMBER: P578528

CATALOG NUMBER: FLD6C-60-D010 FEU6C-X-90-40 F6X-W-X-H

**CANDELA DISTRIBUTION (FULL):**

|       | 0°     |
|-------|--------|
| 0°    | 3611.8 |
| 2.5°  | 3619.4 |
| 5°    | 3596.8 |
| 7.5°  | 3566.5 |
| 10°   | 3528.3 |
| 12.5° | 3490.4 |
| 15°   | 3437.5 |
| 17.5° | 3369.0 |
| 20°   | 3293.2 |
| 22.5° | 3209.7 |
| 25°   | 3103.6 |
| 27.5° | 2966.9 |
| 30°   | 2792.4 |
| 32.5° | 2610.2 |
| 35°   | 2390.3 |
| 37.5° | 2147.5 |
| 40°   | 1866.6 |
| 42.5° | 1585.9 |
| 45°   | 1320.2 |
| 47.5° | 1069.8 |
| 50°   | 850.0  |
| 52.5° | 645.1  |
| 55°   | 478.2  |
| 57.5° | 341.5  |
| 60°   | 235.1  |
| 62.5° | 174.6  |
| 65°   | 129.0  |
| 67.5° | 98.7   |
| 70°   | 68.2   |
| 72.5° | 53.2   |
| 75°   | 37.9   |
| 77.5° | 22.6   |
| 80°   | 15.3   |
| 82.5° | 7.6    |
| 85°   | 7.6    |
| 87.5° | 0.0    |
| 90°   | 0.0    |



Report Generated By 670246072 / DESKTOP-MV3F9LC







— 0°-180°







(END OF REPORT)