

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P578618

Luminaire Tested: **FLD6C-65-D010 FEU6C-X-90-27 F6X-M-X-LI**

Issue Date: 3/1/2023



**Test Information**

Test Method: LM-79-08  
Report Number: P578618  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P205108)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/1/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: FAIL-SAFE  
Catalog Number: FLD6C-65-D010 FEU6C-X-90-27 F6X-M-X-LI  
Description: 6 INCH FAIL-SAFE LED DOWNLIGHT WITH 2700K, 90 CRI LEDS, 6LBMLI TRIM

Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 5867.0 lumens  
Efficiency: N/A  
Efficacy: 81.0 lumens/watt  
Spacing Criteria (0/90/45): 0.85 / 0.85 / 0.85  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct

Input Watts (W): 72.4  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P578618

CATALOG NUMBER: FLD6C-65-D010 FEU6C-X-90-27 F6X-M-X-LI

### Luminous Intensity Polar Plot





TEST NUMBER: P578618

CATALOG NUMBER: FLD6C-65-D010 FEU6C-X-90-27 F6X-M-X-LI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	114	111	109	106	111	109	107	105	105	103	101	101	100	98	98	97	96	94			
2	108	103	100	96	106	102	98	95	99	96	93	96	93	91	93	91	89	88			
3	103	97	92	88	101	95	91	87	93	89	86	90	87	85	88	85	83	82			
4	98	91	85	81	96	89	84	81	87	83	80	85	82	79	83	80	78	76			
5	93	85	79	75	91	84	79	75	82	78	74	81	77	73	79	76	73	71			
6	89	80	74	70	87	79	74	70	78	73	69	76	72	69	75	71	68	67			
7	84	75	69	65	83	75	69	65	73	68	65	72	68	64	71	67	64	63			
8	80	71	65	61	79	70	65	61	69	64	61	68	64	60	67	63	60	59			
9	77	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55			
10	73	64	58	54	72	63	58	54	62	57	54	62	57	54	61	57	54	52			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	402506
5°	398673
10°	377782
15°	342993
20°	303080
25°	262025
30°	204823
35°	125608
40°	64471
45°	25615
50°	8315
55°	2867
60°	2456
65°	1959
70°	1218
75°	1610
80°	0
85°	0



TEST NUMBER: P578618

CATALOG NUMBER: FLD6C-65-D010 FEU6C-X-90-27 F6X-M-X-LI

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	676.4	11.5
10°-20°	1684.0	28.7
20°-30°	1957.5	33.4
30°-40°	1198.7	20.4
40°-50°	297.7	5.1
50°-60°	34.8	0.6
60°-70°	13.0	0.2
70°-80°	5.0	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4317.9	73.6
0°-40°	5516.6	94.0
0°-60°	5849.0	99.7
0°-90°	5867.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5867.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	7342	
5°	7245	676
15°	6044	1684
25°	4332	1958
35°	1877	1199
45°	330	298
55°	30	35
65°	15	13
75°	8	5
85°	0	0
90°	0	



TEST NUMBER: P578618

CATALOG NUMBER: FLD6C-65-D010 FEU6C-X-90-27 F6X-M-X-LI

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	7342.3
2.5°	7334.7
5°	7244.7
7.5°	7049.4
10°	6786.6
12.5°	6441.4
15°	6043.5
17.5°	5615.6
20°	5195.2
22.5°	4774.6
25°	4331.9
27.5°	3821.3
30°	3235.7
32.5°	2552.5
35°	1876.9
37.5°	1321.2
40°	900.9
42.5°	563.0
45°	330.4
47.5°	187.7
50°	97.5
52.5°	45.1
55°	30.0
57.5°	22.4
60°	22.4
62.5°	15.1
65°	15.1
67.5°	7.6
70°	7.6
72.5°	7.6
75°	7.6
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-MV3F9LC







— 0°-180°







(END OF REPORT)