

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P578638

Luminaire Tested: **FLD6C-65-D010 FEU6C-X-90-27 F6X-N-X-LI**

Issue Date: 3/1/2023



Test Information

Test Method: LM-79-08
Report Number: P578638
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P205310)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/1/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD6C-65-D010 FEU6C-X-90-27 F6X-N-X-LI
Description: 6 INCH FAIL-SAFE LED DOWNLIGHT WITH 2700K, 90 CRI LEDS, 6LBNLI TRIM

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5214.0 lumens
Efficiency: N/A
Efficacy: 72.0 lumens/watt
Spacing Criteria (0/90/45): 0.53 / 0.53 / 0.58
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 72.4
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P578638

CATALOG NUMBER: FLD6C-65-D010 FEU6C-X-90-27 F6X-N-X-LI

Luminous Intensity Polar Plot





TEST NUMBER: P578638

CATALOG NUMBER: FLD6C-65-D010 FEU6C-X-90-27 F6X-N-X-LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	114	112	109	107	112	109	107	106	105	104	102	102	101	99	98	97	96	95				95
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	93	91	89				89
3	105	99	94	91	103	97	93	90	95	91	89	93	90	87	90	88	86	85				85
4	100	93	88	85	98	92	88	84	90	86	83	88	85	82	86	84	81	80				80
5	96	88	83	79	94	87	83	79	86	82	78	84	81	78	83	80	77	76				76
6	92	84	79	75	90	83	78	75	82	77	74	80	76	74	79	76	73	72				72
7	88	80	74	71	87	79	74	71	78	73	70	77	73	70	76	72	69	68				68
8	84	76	71	67	83	75	70	67	74	70	67	73	69	66	73	69	66	65				65
9	81	73	67	64	80	72	67	64	71	67	63	70	66	63	70	66	63	62				62
10	78	69	64	61	77	69	64	61	68	64	61	67	63	60	67	63	60	59				59

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	650770
5°	608583
10°	496345
15°	365246
20°	251748
25°	186900
30°	140389
35°	87542
40°	42494
45°	14575
50°	1910
55°	1443
60°	833
65°	986
70°	1218
75°	0
80°	0
85°	0



TEST NUMBER: P578638

CATALOG NUMBER: FLD6C-65-D010 FEU6C-X-90-27 F6X-N-X-LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	987.0	18.9
10°-20°	1771.6	34.0
20°-30°	1432.3	27.5
30°-40°	825.1	15.8
40°-50°	174.4	3.3
50°-60°	15.0	0.3
60°-70°	7.5	0.1
70°-80°	1.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4190.9	80.4
0°-40°	5016.0	96.2
0°-60°	5205.5	99.8
0°-90°	5214.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5214.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	11871	
5°	11059	987
15°	6436	1772
25°	3090	1432
35°	1308	825
45°	188	174
55°	15	15
65°	8	8
75°	0	1
85°	0	0
90°	0	



TEST NUMBER: P578638

CATALOG NUMBER: FLD6C-65-D010 FEU6C-X-90-27 F6X-N-X-LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	11871.0
2.5°	11728.4
5°	11059.2
7.5°	10096.9
10°	8916.5
12.5°	7706.2
15°	6435.6
17.5°	5210.1
20°	4315.3
22.5°	3631.3
25°	3089.9
27.5°	2631.4
30°	2217.8
32.5°	1759.3
35°	1308.1
37.5°	909.6
40°	593.8
42.5°	360.9
45°	188.0
47.5°	75.1
50°	22.4
52.5°	22.4
55°	15.1
57.5°	15.1
60°	7.6
62.5°	7.6
65°	7.6
67.5°	7.6
70°	7.6
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-MV3F9LC





— 0°-180°







(END OF REPORT)