

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P579588

Luminaire Tested: **FLD6C-80-D010 FEU6C-X-90-30 F6X-N-X-H**

Issue Date: 3/1/2023



Test Information

Test Method: LM-79-08
Report Number: P579588
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P203666)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/1/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD6C-80-D010 FEU6C-X-90-30 F6X-N-X-H
Description: 6 INCH FAIL-SAFE LED DOWNLIGHT WITH 3000K, 90 CRI LEDS, 6LBNH TRIM

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5720.0 lumens
Efficiency: N/A
Efficacy: 63.9 lumens/watt
Spacing Criteria (0/90/45): 0.78 / 0.78 / 0.84
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 89.5
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P579588

CATALOG NUMBER: FLD6C-80-D010 FEU6C-X-90-30 F6X-N-X-H

Luminous Intensity Polar Plot





TEST NUMBER: P579588

CATALOG NUMBER: FLD6C-80-D010 FEU6C-X-90-30 F6X-N-X-H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	111	108	106	111	109	106	104	104	103	101	101	99	98	97	96	95	93			
2	108	103	99	96	106	101	98	94	98	95	92	95	93	90	92	90	89	87			
3	102	96	91	87	100	95	90	86	92	88	85	90	86	84	87	85	82	81			
4	97	90	84	80	95	89	83	79	86	82	78	84	81	78	83	79	77	75			
5	92	84	78	74	91	83	78	73	81	76	73	80	75	72	78	74	72	70			
6	88	79	73	69	86	78	72	68	77	72	68	75	71	67	74	70	67	65			
7	83	74	68	64	82	73	68	64	72	67	63	71	66	63	70	66	63	61			
8	79	70	64	60	78	69	64	60	68	63	59	67	63	59	66	62	59	58			
9	76	66	60	56	75	66	60	56	65	59	56	64	59	56	63	59	55	54			
10	72	62	57	53	71	62	57	53	61	56	53	60	56	52	60	55	52	51			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	401969
5°	392020
10°	361722
15°	320246
20°	278064
25°	237842
30°	196087
35°	129128
40°	69416
45°	30732
50°	12460
55°	8984
60°	5712
65°	4086
70°	3366
75°	2224
80°	3315
85°	0



TEST NUMBER: P579588

CATALOG NUMBER: FLD6C-80-D010 FEU6C-X-90-30 F6X-N-X-H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	659.4	11.5
10°-20°	1572.4	27.5
20°-30°	1801.4	31.5
30°-40°	1210.3	21.2
40°-50°	345.8	6.0
50°-60°	84.6	1.5
60°-70°	32.2	0.6
70°-80°	12.5	0.2
80°-90°	1.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4033.2	70.5
0°-40°	5243.5	91.7
0°-60°	5674.0	99.2
0°-90°	5720.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5720.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	7332	
5°	7124	659
15°	5643	1572
25°	3932	1801
35°	1930	1210
45°	396	346
55°	94	85
65°	32	32
75°	10	12
85°	0	1
90°	0	



TEST NUMBER: P579588

CATALOG NUMBER: FLD6C-80-D010 FEU6C-X-90-30 F6X-N-X-H

CANDELA DISTRIBUTION (FULL):

	0°
0°	7332.5
2.5°	7280.4
5°	7123.8
7.5°	6842.0
10°	6498.1
12.5°	6059.7
15°	5642.7
17.5°	5204.8
20°	4766.4
22.5°	4349.4
25°	3932.1
27.5°	3546.2
30°	3097.7
32.5°	2503.1
35°	1929.5
37.5°	1408.0
40°	970.0
42.5°	636.2
45°	396.4
47.5°	239.8
50°	146.1
52.5°	114.6
55°	94.0
57.5°	73.1
60°	52.1
62.5°	41.6
65°	31.5
67.5°	21.0
70°	21.0
72.5°	10.5
75°	10.5
77.5°	10.5
80°	10.5
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-MV3F9LC





— 0°-180°







(END OF REPORT)