

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P578788

Luminaire Tested: **FLD6C-65-D010 FEU6C-X-90-40 F6X-M-X-H**

Issue Date: 3/1/2023



Test Information

Test Method: LM-79-08
Report Number: P578788
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P203254)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/1/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD6C-65-D010 FEU6C-X-90-40 F6X-M-X-H
Description: 6 INCH FAIL-SAFE LED DOWNLIGHT WITH 4000K, 90 CRI LEDS, 6LBMH TRIM

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5062.0 lumens
Efficiency: N/A
Efficacy: 69.9 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.93
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 72.4
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P578788

CATALOG NUMBER: FLD6C-65-D010 FEU6C-X-90-40 F6X-M-X-H

Luminous Intensity Polar Plot





TEST NUMBER: P578788

CATALOG NUMBER: FLD6C-65-D010 FEU6C-X-90-40 F6X-M-X-H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	92	92	92	92
2	107	102	97	93	105	100	96	92	97	93	90	94	91	88	91	89	87	85	85	85	85
3	101	94	88	84	99	92	88	84	90	86	82	87	84	81	85	82	80	78	78	78	78
4	95	87	81	76	93	86	80	76	84	79	75	82	78	74	80	76	73	72	72	72	72
5	90	81	75	70	88	80	74	70	78	73	69	76	72	68	75	71	68	66	66	66	66
6	85	75	69	64	83	75	69	64	73	68	64	72	67	63	70	66	63	61	61	61	61
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57	57	57	57
8	76	66	60	55	75	65	59	55	64	59	55	63	58	55	62	58	54	53	53	53	53
9	72	62	56	51	71	61	55	51	60	55	51	60	55	51	59	54	51	49	49	49	49
10	69	58	52	48	68	58	52	48	57	52	48	56	51	48	55	51	48	46	46	46	46

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	274627
5°	269711
10°	255929
15°	239996
20°	223512
25°	205941
30°	171596
35°	120943
40°	77080
45°	45966
50°	27129
55°	17261
60°	11885
65°	8444
70°	5802
75°	4596
80°	2241
85°	0



TEST NUMBER: P578788

CATALOG NUMBER: FLD6C-65-D010 FEU6C-X-90-40 F6X-M-X-H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	458.0	9.0
10°-20°	1184.9	23.4
20°-30°	1535.4	30.3
30°-40°	1139.9	22.5
40°-50°	481.2	9.5
50°-60°	170.8	3.4
60°-70°	66.0	1.3
70°-80°	22.8	0.5
80°-90°	2.9	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3178.4	62.8
0°-40°	4318.2	85.3
0°-60°	4970.3	98.2
0°-90°	5062.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5062.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5010	
5°	4901	458
15°	4229	1185
25°	3405	1535
35°	1807	1140
45°	593	481
55°	181	171
65°	65	66
75°	22	23
85°	0	3
90°	0	



TEST NUMBER: P578788

CATALOG NUMBER: FLD6C-65-D010 FEU6C-X-90-40 F6X-M-X-H

CANDELA DISTRIBUTION (FULL):

0°	
0°	5009.6
2.5°	4995.1
5°	4901.2
7.5°	4763.7
10°	4597.6
12.5°	4416.7
15°	4228.7
17.5°	4019.3
20°	3831.3
22.5°	3636.1
25°	3404.7
27.5°	3086.6
30°	2710.8
32.5°	2269.7
35°	1807.2
37.5°	1416.9
40°	1077.1
42.5°	802.3
45°	592.9
47.5°	433.7
50°	318.1
52.5°	238.5
55°	180.6
57.5°	137.2
60°	108.4
62.5°	79.6
65°	65.1
67.5°	50.5
70°	36.2
72.5°	28.8
75°	21.7
77.5°	14.6
80°	7.1
82.5°	7.1
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-MV3F9LC





— 0°-180°







(END OF REPORT)