

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P578798

Luminaire Tested: **FLD6C-65-D010 FEU6C-X-90-40 F6X-M-X-LI**

Issue Date: 3/1/2023



Test Information

Test Method: LM-79-08
Report Number: P578798
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P205108)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/1/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD6C-65-D010 FEU6C-X-90-40 F6X-M-X-LI
Description: 6 INCH FAIL-SAFE LED DOWNLIGHT WITH 4000K, 90 CRI LEDS, 6LBMLI TRIM

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6195.0 lumens
Efficiency: N/A
Efficacy: 85.6 lumens/watt
Spacing Criteria (0/90/45): 0.85 / 0.85 / 0.85
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 72.4
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P578798

CATALOG NUMBER: FLD6C-65-D010 FEU6C-X-90-40 F6X-M-X-LI

Luminous Intensity Polar Plot





TEST NUMBER: P578798

CATALOG NUMBER: FLD6C-65-D010 FEU6C-X-90-40 F6X-M-X-LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	114	111	109	106	111	109	107	105	105	103	101	101	100	98	98	97	96	94		
2	108	103	100	96	106	102	98	95	99	96	93	96	93	91	93	91	89	88		
3	103	97	92	88	101	95	91	87	93	89	86	90	87	85	88	85	83	82		
4	98	91	85	81	96	89	84	81	87	83	80	85	82	79	83	80	78	76		
5	93	85	79	75	91	84	79	75	82	78	74	81	77	73	79	76	73	71		
6	89	80	74	70	87	79	74	70	78	73	69	76	72	69	75	71	68	67		
7	84	75	69	65	83	75	69	65	73	68	65	72	68	64	71	67	64	63		
8	80	71	65	61	79	70	65	61	69	64	61	68	64	60	67	63	60	59		
9	77	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55		
10	73	64	58	54	72	63	58	54	62	57	54	62	57	54	61	57	54	52		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	425004
5°	420965
10°	398902
15°	362164
20°	320027
25°	276675
30°	216274
35°	132628
40°	68078
45°	27042
50°	8784
55°	3030
60°	2598
65°	2075
70°	1282
75°	1694
80°	0
85°	0



TEST NUMBER: P578798

CATALOG NUMBER: FLD6C-65-D010 FEU6C-X-90-40 F6X-M-X-LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	714.2	11.5
10°-20°	1778.1	28.7
20°-30°	2067.0	33.4
30°-40°	1265.7	20.4
40°-50°	314.3	5.1
50°-60°	36.7	0.6
60°-70°	13.8	0.2
70°-80°	5.2	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4559.3	73.6
0°-40°	5825.0	94.0
0°-60°	6176.0	99.7
0°-90°	6195.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6195.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	7753	
5°	7650	714
15°	6381	1778
25°	4574	2067
35°	1982	1266
45°	349	314
55°	32	37
65°	16	14
75°	8	5
85°	0	0
90°	0	



TEST NUMBER: P578798

CATALOG NUMBER: FLD6C-65-D010 FEU6C-X-90-40 F6X-M-X-LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	7752.7
2.5°	7744.8
5°	7649.8
7.5°	7443.5
10°	7166.0
12.5°	6801.5
15°	6381.3
17.5°	5929.5
20°	5485.7
22.5°	5041.6
25°	4574.1
27.5°	4035.0
30°	3416.6
32.5°	2695.2
35°	1981.8
37.5°	1395.1
40°	951.3
42.5°	594.4
45°	348.8
47.5°	198.2
50°	103.0
52.5°	47.6
55°	31.7
57.5°	23.7
60°	23.7
62.5°	16.0
65°	16.0
67.5°	8.0
70°	8.0
72.5°	8.0
75°	8.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-MV3F9LC





— 0°-180°







(END OF REPORT)