

LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P#

Luminaire Tested: **FLDSQ4C100D010 FEU4C1009050 F4LC-DFSSQ-MW**

Issue Date: 12/13/2022

Tested By:

Approved By:



Cooper Lighting Solutions laboratories have been accredited by National Voluntary Laboratory Accreditation Program (NVLAP) that it adheres to the requirements of ISO/IEC 17025:2005 and appropriate IESNA test methods. This report must not be used to claim product certification, approval or endorsement by NVLAP, NIST or any agency of the Federal Government. Results contained in this report are valid for luminaire sample tested, as supplied by requestor. Information related to the luminaire tested has been supplied by requestor and can affect the validity of the test results. Report shall not be reproduced except in full without approval of Cooper Lighting Solutions Lighting Laboratory. Test performed at address noted above.

Test Information

Test Method: LM-79-08
 Report Number: P#
 Test Lab: INNOVATION CENTER
 Issue Date: 12/13/2022
 Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
 Product Line: FAIL-SAFE
 Catalog Number: FLDSQ4C100D010 FEU4C1009050 F4LC-DFSSQ-MW
 Description: 4 INCH 10000 LUMEN FAIL-SAFE LED DOWNLIGHT WITH, 5000K, 90CRI LEDS AND F4LC-DFSSQ TRIM WITH MW FINISH
 Light Source: -
 Ballast/Driver: -

Summary


Lumens per Lamp: N/A
 Luminaire Lumens: 10306.0 lumens
 Efficiency: N/A
 Efficacy: 90.1 lumens/watt
 Spacing Criteria (0/90/45): 1.19 / 1.2 / 1.29
 Luminous Opening: Rectangular (W 0.33' x L: 0.33' x H: 0')
 CIE Type: Direct

Input Watts (W): 114.4
 Input Voltage (V):
 Input Current (Ain): NR
 Voltage Rise (V): NR
 Power Factor: NR
 Total Harmonic Distortion (THDi): NR
 Frequency (hertz): 60
 Stabilization Time: NR
 Operation Time: NR
 Ambient Temperature (°C): NR
 Test Distance: 25 FT

Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	GONIO 1 IN0055	4/22/2021	10/22/2021
Power Meter	XITRON 2801 IN0197	12/1/2020	12/1/2021
AC Power Source	CHROMA 61505 IN0196	12/1/2020	12/1/2021
DC Power Supply	AGILENT E3634A IN0198	11/30/2020	11/30/2021
Room Thermometer	ONSET IN0143	12/1/2020	12/1/2021

TEST NUMBER: P#
CATALOG NUMBER: FLDSQ4C100D010 FEU4C1009050 F4LC-DFSSQ-MW

Luminous Intensity Polar Plot



TEST NUMBER: P#
 CATALOG NUMBER: FLDSQ4C100D010 FEU4C1009050 F4LC-DFSSQ-MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	111	108	104	101	109	105	102	100	101	99	96		97	95	94		94	92	91	89
2	103	96	91	86	100	94	89	85	91	87	83		88	84	81		85	82	79	77
3	95	86	79	74	93	85	78	73	82	76	72		79	74	71		77	73	69	67
4	88	77	70	64	86	76	69	63	74	67	63		71	66	62		69	65	61	59
5	81	70	62	56	79	69	61	56	67	60	55		65	59	54		63	58	54	52
6	75	63	55	49	73	62	55	49	61	54	49		59	53	48		57	52	48	46
7	70	58	50	44	68	57	49	44	55	49	44		54	48	43		53	47	43	41
8	65	53	45	40	64	52	45	39	51	44	39		50	44	39		49	43	39	37
9	61	49	41	36	60	48	41	36	47	40	36		46	40	35		45	39	35	33
10	57	45	38	33	56	44	37	33	44	37	32		43	37	32		42	36	32	31

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	465520	465520	465520
5°	458010	463967	465294
10°	461963	460621	462620
15°	453872	454542	455910
20°	443316	450350	448245
25°	441399	441399	444316
30°	429096	432148	432928
35°	415709	419749	412481
40°	396199	403958	400506
45°	374967	383400	371228
50°	330227	359018	328171
55°	267441	328540	268619
60°	195699	272427	191762
65°	118928	193997	115800
70°	46380	104439	44489
75°	5107	28147	5107
80°	3890	3890	3890
85°	0	0	0

TEST NUMBER: P#
 CATALOG NUMBER: FLDSQ4C100D010 FEU4C1009050 F4LC-DFSSQ-MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	455.4	4.4
10°-20°	1288.7	12.5
20°-30°	1912.1	18.6
30°-40°	2215.5	21.5
40°-50°	2124.2	20.6
50°-60°	1561.8	15.2
60°-70°	674.6	6.5
70°-80°	72.8	0.7
80°-90°	0.9	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3656.1	35.5
0°-40°	5871.7	57.0
0°-60°	9557.6	92.7
0°-90°	10306.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	10306.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	4825	4825	4825	4825	4825	
5°	4729	4776	4790	4797	4804	451
15°	4544	4571	4550	4557	4564	1281
25°	4146	4139	4146	4153	4173	1898
35°	3529	3550	3564	3557	3502	2207
45°	2748	2755	2810	2769	2720	2089
55°	1590	1754	1953	1748	1597	1431
65°	521	651	850	644	507	535
75°	14	21	76	14	14	42
85°	0	0	0	0	0	1
90°	0	0	0	0	0	

TEST NUMBER: P#
 CATALOG NUMBER: FLDSQ4C100D010 FEU4C1009050 F4LC-DFSSQ-MW

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	4824.6	4824.6	4824.6	4824.6	4824.6	4824.6	4824.6	4824.6	4824.6	4824.6	4824.6
2.5°	4790.2	4845.0	4852.0	4817.6	4803.9	4783.5	4831.3	4797.2	4810.9	4797.2	4790.2
5°	4728.7	4790.2	4797.2	4797.2	4783.5	4776.5	4797.2	4790.2	4783.5	4769.8	4790.2
7.5°	4701.3	4735.4	4769.8	4728.7	4749.1	4742.4	4790.2	4769.8	4762.8	4762.8	4749.1
10°	4715.0	4708.0	4735.4	4694.3	4708.0	4694.3	4735.4	4735.4	4721.7	4708.0	4701.3
12.5°	4605.1	4659.9	4659.9	4653.2	4639.5	4618.8	4659.9	4687.5	4646.2	4646.2	4639.5
15°	4543.6	4557.3	4564.0	4564.0	4557.3	4571.0	4591.4	4564.0	4571.0	4536.6	4550.3
17.5°	4475.1	4447.7	4468.1	4454.4	4461.4	4475.1	4502.5	4502.5	4461.4	4454.4	4468.1
20°	4317.4	4399.6	4406.5	4365.4	4372.2	4372.2	4420.2	4379.1	4406.5	4372.2	4385.9
22.5°	4241.9	4296.7	4303.7	4248.9	4283.0	4241.9	4290.0	4228.2	4296.7	4248.9	4269.3
25°	4146.0	4139.2	4159.7	4132.3	4139.2	4139.2	4173.4	4146.0	4166.7	4139.2	4146.0
27.5°	3988.5	4043.3	4036.4	4009.0	4022.7	4015.9	4084.4	4009.0	4050.1	4015.9	4029.6
30°	3851.3	3899.4	3885.7	3858.2	3858.2	3837.6	3913.1	3892.4	3885.7	3885.7	3878.7
32.5°	3714.3	3721.2	3707.5	3714.3	3721.2	3693.8	3755.4	3728.0	3721.2	3728.0	3734.9
35°	3529.2	3529.2	3542.9	3522.4	3549.8	3549.8	3604.6	3570.3	3563.5	3542.9	3563.5
37.5°	3364.8	3344.3	3351.1	3351.1	3364.8	3378.5	3405.9	3392.2	3392.2	3371.7	3385.4
40°	3145.5	3131.8	3152.3	3152.3	3172.9	3172.9	3200.3	3186.6	3207.1	3207.1	3207.1
42.5°	2953.7	2953.7	2940.0	2960.4	2967.4	2960.4	3008.5	3001.5	3008.5	2994.8	3001.5
45°	2747.9	2747.9	2734.2	2727.5	2761.6	2754.9	2809.7	2789.1	2816.5	2802.8	2809.7
47.5°	2466.9	2501.3	2480.6	2501.3	2542.4	2549.4	2583.5	2569.8	2597.2	2576.8	2604.2
50°	2199.9	2199.9	2220.3	2247.7	2288.8	2295.8	2336.9	2364.3	2378.0	2384.7	2391.7
52.5°	1918.9	1911.9	1932.6	1966.7	2001.1	2028.5	2069.6	2110.7	2138.1	2179.2	2158.5
55°	1589.8	1603.5	1624.2	1665.3	1720.1	1754.2	1788.6	1843.4	1891.5	1911.9	1953.0
57.5°	1308.8	1295.1	1308.8	1363.6	1425.4	1452.8	1500.9	1555.7	1624.2	1665.3	1679.0
60°	1014.1	1021.1	1034.8	1082.9	1130.7	1171.8	1192.5	1281.4	1343.2	1384.3	1411.7
62.5°	747.1	760.8	774.5	815.6	863.4	897.8	931.9	1007.4	1062.2	1103.3	1130.7
65°	520.9	527.6	548.3	568.7	616.8	650.9	678.3	740.1	794.9	829.3	849.7
67.5°	322.1	328.8	342.5	370.2	404.3	431.7	459.1	500.2	548.3	582.4	589.4
70°	164.4	171.4	178.1	198.8	226.2	239.9	260.3	294.7	328.8	356.2	370.2
72.5°	54.8	54.8	61.8	75.5	89.2	102.9	109.6	144.0	171.4	185.1	191.8
75°	13.7	13.7	13.7	13.7	13.7	20.7	20.7	41.1	54.8	68.5	75.5
77.5°	7.0	7.0	7.0	7.0	7.0	7.0	7.0	7.0	7.0	13.7	13.7
80°	7.0	7.0	7.0	7.0	7.0	7.0	7.0	7.0	7.0	7.0	7.0
82.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P#
 CATALOG NUMBER: FLDSQ4C100D010 FEU4C1009050 F4LC-DFSSQ-MW

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°
0°	4824.6	4824.6	4824.6	4824.6	4824.6	4824.6	4824.6	4824.6	4824.6	4824.6
2.5°	4824.6	4810.9	4803.9	4810.9	4810.9	4803.9	4824.6	4852.0	4886.1	4797.2
5°	4817.6	4803.9	4817.6	4776.5	4797.2	4783.5	4810.9	4803.9	4831.3	4803.9
7.5°	4797.2	4769.8	4776.5	4756.1	4783.5	4749.1	4769.8	4810.9	4783.5	4742.4
10°	4728.7	4715.0	4762.8	4694.3	4680.6	4708.0	4762.8	4721.7	4708.0	4721.7
12.5°	4659.9	4659.9	4680.6	4625.8	4632.5	4646.2	4673.6	4646.2	4659.9	4694.3
15°	4584.7	4571.0	4605.1	4564.0	4557.3	4543.6	4571.0	4571.0	4584.7	4564.0
17.5°	4495.5	4475.1	4475.1	4461.4	4454.4	4488.8	4502.5	4509.2	4516.2	4488.8
20°	4385.9	4379.1	4399.6	4379.1	4385.9	4392.8	4392.8	4379.1	4440.7	4365.4
22.5°	4269.3	4290.0	4262.6	4248.9	4262.6	4276.3	4276.3	4283.0	4269.3	4255.6
25°	4153.0	4166.7	4173.4	4132.3	4153.0	4132.3	4180.4	4187.1	4159.7	4173.4
27.5°	4050.1	4029.6	4022.7	3995.3	4009.0	4002.2	4009.0	4009.0	4050.1	3995.3
30°	3892.4	3871.9	3878.7	3858.2	3865.0	3858.2	3865.0	3865.0	3892.4	3885.7
32.5°	3741.7	3721.2	3728.0	3707.5	3707.5	3714.3	3700.6	3700.6	3721.2	3707.5
35°	3597.7	3549.8	3556.6	3549.8	3556.6	3529.2	3529.2	3522.4	3536.1	3501.8
37.5°	3392.2	3371.7	3364.8	3358.0	3364.8	3351.1	3364.8	3344.3	3364.8	3337.4
40°	3207.1	3193.4	3200.3	3159.2	3159.2	3166.0	3152.3	3145.5	3152.3	3179.7
42.5°	3022.2	2994.8	2981.1	2967.4	2974.1	2953.7	2946.7	2933.0	2946.7	2919.3
45°	2802.8	2802.8	2796.0	2761.6	2768.6	2768.6	2741.2	2713.8	2720.5	2720.5
47.5°	2604.2	2590.5	2583.5	2549.4	2542.4	2535.7	2508.0	2487.6	2487.6	2466.9
50°	2384.7	2371.0	2350.6	2316.2	2302.5	2261.4	2241.0	2213.6	2186.2	2186.2
52.5°	2179.2	2131.1	2103.7	2048.9	2028.5	2007.8	1953.0	1932.6	1911.9	1891.5
55°	1932.6	1891.5	1836.7	1774.9	1747.5	1713.1	1658.3	1617.2	1589.8	1596.8
57.5°	1692.7	1624.2	1569.4	1487.2	1452.8	1432.1	1377.3	1322.5	1295.1	1295.1
60°	1398.0	1343.2	1274.7	1199.2	1171.8	1137.7	1068.9	1034.8	1014.1	993.7
62.5°	1117.0	1075.9	1014.1	918.2	897.8	863.4	815.6	774.5	753.8	753.8
65°	836.0	794.9	740.1	671.6	644.2	616.8	575.7	534.6	513.9	507.2
67.5°	589.4	541.3	493.5	438.7	418.0	404.3	363.2	335.8	322.1	315.1
70°	356.2	328.8	294.7	253.6	232.9	219.2	191.8	171.4	164.4	157.7
72.5°	185.1	164.4	137.0	109.6	95.9	82.2	68.5	54.8	48.1	48.1
75°	68.5	54.8	34.4	20.7	13.7	13.7	13.7	13.7	13.7	13.7
77.5°	13.7	7.0	7.0	7.0	7.0	7.0	7.0	7.0	7.0	7.0
80°	7.0	7.0	7.0	7.0	7.0	7.0	7.0	7.0	7.0	7.0
82.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)