

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P579008

Luminaire Tested: **FLD6C-70-D010 FEU6C-X-90-30 F6X-W-X-H**

Issue Date: 3/1/2023



Test Information

Test Method: LM-79-08
Report Number: P579008
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P202739)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/1/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD6C-70-D010 FEU6C-X-90-30 F6X-W-X-H
Description: 6 INCH FAIL-SAFE LED DOWNLIGHT WITH 3000K, 90 CRI LEDS, 6LBWH TRIM

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6335.0 lumens
Efficiency: N/A
Efficacy: 81.2 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.16
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 78
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P579008

CATALOG NUMBER: FLD6C-70-D010 FEU6C-X-90-30 F6X-W-X-H

Luminous Intensity Polar Plot





TEST NUMBER: P579008

CATALOG NUMBER: FLD6C-70-D010 FEU6C-X-90-30 F6X-W-X-H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	112	109	106	103	110	107	104	101	103	100	98	99	97	95	95	94	93	91			
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	85	83	81			
3	98	90	84	79	96	89	83	78	86	81	77	83	79	76	81	78	75	73			
4	92	82	75	70	90	81	75	70	79	73	69	77	72	68	75	71	67	65			
5	86	75	68	63	84	74	68	63	72	66	62	71	65	61	69	64	61	59			
6	80	69	62	57	78	68	61	56	67	61	56	65	60	56	64	59	55	53			
7	75	64	56	51	73	63	56	51	62	55	51	60	55	51	59	54	50	49			
8	70	59	52	47	69	58	51	47	57	51	46	56	50	46	55	50	46	44			
9	66	55	48	43	65	54	47	43	53	47	43	52	47	42	51	46	42	41			
10	62	51	44	40	61	50	44	39	50	43	39	49	43	39	48	43	39	38			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	214193
5°	214120
10°	212471
15°	211045
20°	207831
25°	203086
30°	191219
35°	173050
40°	144506
45°	110725
50°	78420
55°	49441
60°	27893
65°	18108
70°	11829
75°	8684
80°	5209
85°	5221



TEST NUMBER: P579008

CATALOG NUMBER: FLD6C-70-D010 FEU6C-X-90-30 F6X-W-X-H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	369.0	5.8
10°-20°	1047.2	16.5
20°-30°	1535.4	24.2
30°-40°	1597.9	25.2
40°-50°	1105.5	17.5
50°-60°	481.4	7.6
60°-70°	147.6	2.3
70°-80°	44.2	0.7
80°-90°	6.8	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2951.6	46.6
0°-40°	4549.5	71.8
0°-60°	6136.4	96.9
0°-90°	6335.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6335.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3907	
5°	3891	369
15°	3719	1047
25°	3358	1535
35°	2586	1598
45°	1428	1106
55°	517	481
65°	140	148
75°	41	44
85°	8	7
90°	0	



TEST NUMBER: P579008

CATALOG NUMBER: FLD6C-70-D010 FEU6C-X-90-30 F6X-W-X-H

CANDELA DISTRIBUTION (FULL):

	0°
0°	3907.2
2.5°	3915.5
5°	3891.0
7.5°	3858.2
10°	3816.9
12.5°	3775.9
15°	3718.6
17.5°	3644.6
20°	3562.5
22.5°	3472.2
25°	3357.5
27.5°	3209.6
30°	3020.8
32.5°	2823.7
35°	2585.8
37.5°	2323.2
40°	2019.3
42.5°	1715.6
45°	1428.2
47.5°	1157.3
50°	919.5
52.5°	697.9
55°	517.3
57.5°	369.4
60°	254.4
62.5°	188.9
65°	139.6
67.5°	106.8
70°	73.8
72.5°	57.5
75°	41.0
77.5°	24.5
80°	16.5
82.5°	8.3
85°	8.3
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-MV3F9LC





— 0°-180°







(END OF REPORT)