

LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P#

Luminaire Tested: **FLDSQ4C10D010 FEU4C109050 F4LC-DFSSQ-MW**

Issue Date: 12/13/2022

Tested By:

Approved By:



Cooper Lighting Solutions laboratories have been accredited by National Voluntary Laboratory Accreditation Program (NVLAP) that it adheres to the requirements of ISO/IEC 17025:2005 and appropriate IESNA test methods. This report must not be used to claim product certification, approval or endorsement by NVLAP, NIST or any agency of the Federal Government. Results contained in this report are valid for luminaire sample tested, as supplied by requestor. Information related to the luminaire tested has been supplied by requestor and can affect the validity of the test results. Report shall not be reproduced except in full without approval of Cooper Lighting Solutions Lighting Laboratory. Test performed at address noted above.



**Test Information**

Test Method: LM-79-08  
 Report Number: P#  
 Test Lab: INNOVATION CENTER  
 Issue Date: 12/13/2022  
 Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
 Product Line: FAIL-SAFE  
 Catalog Number: FLDSQ4C10D010 FEU4C109050 F4LC-DFSSQ-MW  
 Description: 4 INCH 1000 LUMEN FAIL-SAFE LED DOWNLIGHT WITH, 5000K, 90CRI LEDS AND F4LC-DFSSQ TRIM WITH MW FINISH  
 Light Source: -  
 Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
 Luminaire Lumens: 1025.0 lumens  
 Efficiency: N/A  
 Efficacy: 104.6 lumens/watt  
 Spacing Criteria (0/90/45): 1.19 / 1.2 / 1.29  
 Luminous Opening: Rectangular (W 0.33' x L: 0.33' x H: 0')  
 CIE Type: Direct

Input Watts (W): 9.8  
 Input Voltage (V):  
 Input Current (Ain): NR  
 Voltage Rise (V): NR  
 Power Factor: NR  
 Total Harmonic Distortion (THDi): NR  
 Frequency (hertz): 60  
 Stabilization Time: NR  
 Operation Time: NR  
 Ambient Temperature (°C): NR  
 Test Distance: 25 FT

Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	GONIO 1 IN0055	4/22/2021	10/22/2021
Power Meter	XITRON 2801 IN0197	12/1/2020	12/1/2021
AC Power Source	CHROMA 61505 IN0196	12/1/2020	12/1/2021
DC Power Supply	AGILENT E3634A IN0198	11/30/2020	11/30/2021
Room Thermometer	ONSET IN0143	12/1/2020	12/1/2021

TEST NUMBER: P#  
CATALOG NUMBER: FLDSQ4C10D010 FEU4C109050 F4LC-DFSSQ-MW

### Luminous Intensity Polar Plot



TEST NUMBER: P#

CATALOG NUMBER: FLDSQ4C10D010 FEU4C109050 F4LC-DFSSQ-MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	111	108	104	101	109	105	102	100	101	99	96	97	95	94	94	92	91	89				89
2	103	96	91	86	100	94	89	85	91	87	83	88	84	81	85	82	79	77				77
3	95	86	79	74	93	85	78	73	82	76	72	79	74	71	77	73	69	67				67
4	88	77	70	64	86	76	69	63	74	67	63	71	66	62	69	65	61	59				59
5	81	70	62	56	79	69	61	56	67	60	55	65	59	54	63	58	54	52				52
6	75	63	55	49	73	62	55	49	61	54	49	59	53	48	57	52	48	46				46
7	70	58	50	44	68	57	49	44	55	49	44	54	48	43	53	47	43	41				41
8	65	53	45	40	64	52	45	39	51	44	39	50	44	39	49	43	39	37				37
9	61	49	41	36	60	48	41	36	47	40	36	46	40	35	45	39	35	33				33
10	57	45	38	33	56	44	37	33	44	37	32	43	37	32	42	36	32	31				31

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	46295	46295	46295
5°	45552	46143	46278
10°	45942	45814	46010
15°	45141	45211	45341
20°	44091	44790	44584
25°	43895	43895	44193
30°	42672	42984	43062
35°	41345	41745	41027
40°	39399	40180	39828
45°	37293	38126	36925
50°	32844	35711	32634
55°	26596	32669	26714
60°	19471	27094	19066
65°	11827	19292	11507
70°	4627	10382	4429
75°	522	2796	522
80°	389	389	389
85°	0	0	0

TEST NUMBER: P#  
 CATALOG NUMBER: FLDSQ4C10D010 FEU4C109050 F4LC-DFSSQ-MW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	45.3	4.4
10°-20°	128.2	12.5
20°-30°	190.2	18.6
30°-40°	220.3	21.5
40°-50°	211.3	20.6
50°-60°	155.3	15.2
60°-70°	67.1	6.5
70°-80°	7.3	0.7
80°-90°	0.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	363.6	35.5
0°-40°	584.0	57.0
0°-60°	950.6	92.7
0°-90°	1025.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1025.0	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	480	480	480	480	480	
5°	470	475	476	477	478	45
15°	452	455	453	453	454	127
25°	412	412	412	413	415	189
35°	351	353	354	354	348	219
45°	273	274	279	275	271	208
55°	158	174	194	174	159	142
65°	52	65	84	64	50	53
75°	1	2	8	1	1	4
85°	0	0	0	0	0	0
90°	0	0	0	0	0	

TEST NUMBER: P#  
 CATALOG NUMBER: FLDSQ4C10D010 FEU4C109050 F4LC-DFSSQ-MW

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	479.8	479.8	479.8	479.8	479.8	479.8	479.8	479.8	479.8	479.8	479.8
2.5°	476.4	481.9	482.6	479.1	477.8	475.7	480.5	477.1	478.5	477.1	476.4
5°	470.3	476.4	477.1	477.1	475.7	475.1	477.1	476.4	475.7	474.4	476.4
7.5°	467.6	471.0	474.4	470.3	472.3	471.7	476.4	474.4	473.7	473.7	472.3
10°	468.9	468.2	471.0	466.9	468.2	466.9	471.0	471.0	469.6	468.2	467.6
12.5°	458.0	463.5	463.5	462.8	461.4	459.4	463.5	466.2	462.1	462.1	461.4
15°	451.9	453.2	453.9	453.9	453.2	454.6	456.6	453.9	454.6	451.2	452.6
17.5°	445.1	442.3	444.4	443.0	443.7	445.1	447.8	447.8	443.7	443.0	444.4
20°	429.4	437.6	438.3	434.2	434.8	434.8	439.6	435.5	438.3	434.8	436.2
22.5°	421.9	427.3	428.0	422.6	426.0	421.9	426.7	420.5	427.3	422.6	424.6
25°	412.3	411.7	413.7	411.0	411.7	411.7	415.1	412.3	414.4	411.7	412.3
27.5°	396.7	402.1	401.4	398.7	400.1	399.4	406.2	398.7	402.8	399.4	400.8
30°	383.0	387.8	386.5	383.7	383.7	381.7	389.2	387.1	386.5	386.5	385.8
32.5°	369.4	370.1	368.7	369.4	370.1	367.4	373.5	370.8	370.1	370.8	371.5
35°	351.0	351.0	352.4	350.3	353.1	353.1	358.5	355.1	354.4	352.4	354.4
37.5°	334.6	332.6	333.3	333.3	334.6	336.0	338.7	337.4	337.4	335.3	336.7
40°	312.8	311.5	313.5	313.5	315.6	315.6	318.3	316.9	319.0	319.0	319.0
42.5°	293.8	293.8	292.4	294.4	295.1	294.4	299.2	298.5	299.2	297.9	298.5
45°	273.3	273.3	271.9	271.3	274.7	274.0	279.4	277.4	280.1	278.8	279.4
47.5°	245.4	248.8	246.7	248.8	252.9	253.6	257.0	255.6	258.3	256.3	259.0
50°	218.8	218.8	220.8	223.6	227.6	228.3	232.4	235.1	236.5	237.2	237.9
52.5°	190.8	190.2	192.2	195.6	199.0	201.7	205.8	209.9	212.7	216.7	214.7
55°	158.1	159.5	161.5	165.6	171.1	174.5	177.9	183.3	188.1	190.2	194.2
57.5°	130.2	128.8	130.2	135.6	141.8	144.5	149.3	154.7	161.5	165.6	167.0
60°	100.9	101.6	102.9	107.7	112.5	116.5	118.6	127.4	133.6	137.7	140.4
62.5°	74.3	75.7	77.0	81.1	85.9	89.3	92.7	100.2	105.6	109.7	112.5
65°	51.8	52.5	54.5	56.6	61.3	64.7	67.5	73.6	79.1	82.5	84.5
67.5°	32.0	32.7	34.1	36.8	40.2	42.9	45.7	49.7	54.5	57.9	58.6
70°	16.4	17.0	17.7	19.8	22.5	23.9	25.9	29.3	32.7	35.4	36.8
72.5°	5.5	5.5	6.1	7.5	8.9	10.2	10.9	14.3	17.0	18.4	19.1
75°	1.4	1.4	1.4	1.4	1.4	2.1	2.1	4.1	5.5	6.8	7.5
77.5°	0.7	0.7	0.7	0.7	0.7	0.7	0.7	0.7	0.7	1.4	1.4
80°	0.7	0.7	0.7	0.7	0.7	0.7	0.7	0.7	0.7	0.7	0.7
82.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P#  
 CATALOG NUMBER: FLDSQ4C10D010 FEU4C109050 F4LC-DFSSQ-MW

**CANDELA DISTRIBUTION (continued):**

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°
0°	479.8	479.8	479.8	479.8	479.8	479.8	479.8	479.8	479.8	479.8
2.5°	479.8	478.5	477.8	478.5	478.5	477.8	479.8	482.6	486.0	477.1
5°	479.1	477.8	479.1	475.1	477.1	475.7	478.5	477.8	480.5	477.8
7.5°	477.1	474.4	475.1	473.0	475.7	472.3	474.4	478.5	475.7	471.7
10°	470.3	468.9	473.7	466.9	465.5	468.2	473.7	469.6	468.2	469.6
12.5°	463.5	463.5	465.5	460.1	460.7	462.1	464.8	462.1	463.5	466.9
15°	456.0	454.6	458.0	453.9	453.2	451.9	454.6	454.6	456.0	453.9
17.5°	447.1	445.1	445.1	443.7	443.0	446.4	447.8	448.5	449.2	446.4
20°	436.2	435.5	437.6	435.5	436.2	436.9	436.9	435.5	441.7	434.2
22.5°	424.6	426.7	423.9	422.6	423.9	425.3	425.3	426.0	424.6	423.2
25°	413.0	414.4	415.1	411.0	413.0	411.0	415.8	416.4	413.7	415.1
27.5°	402.8	400.8	400.1	397.4	398.7	398.0	398.7	398.7	402.8	397.4
30°	387.1	385.1	385.8	383.7	384.4	383.7	384.4	384.4	387.1	386.5
32.5°	372.1	370.1	370.8	368.7	368.7	369.4	368.0	368.0	370.1	368.7
35°	357.8	353.1	353.7	353.1	353.7	351.0	351.0	350.3	351.7	348.3
37.5°	337.4	335.3	334.6	334.0	334.6	333.3	334.6	332.6	334.6	331.9
40°	319.0	317.6	318.3	314.2	314.2	314.9	313.5	312.8	313.5	316.2
42.5°	300.6	297.9	296.5	295.1	295.8	293.8	293.1	291.7	293.1	290.3
45°	278.8	278.8	278.1	274.7	275.4	275.4	272.6	269.9	270.6	270.6
47.5°	259.0	257.6	257.0	253.6	252.9	252.2	249.4	247.4	247.4	245.4
50°	237.2	235.8	233.8	230.4	229.0	224.9	222.9	220.2	217.4	217.4
52.5°	216.7	212.0	209.2	203.8	201.7	199.7	194.2	192.2	190.2	188.1
55°	192.2	188.1	182.7	176.5	173.8	170.4	164.9	160.8	158.1	158.8
57.5°	168.4	161.5	156.1	147.9	144.5	142.4	137.0	131.5	128.8	128.8
60°	139.0	133.6	126.8	119.3	116.5	113.2	106.3	102.9	100.9	98.8
62.5°	111.1	107.0	100.9	91.3	89.3	85.9	81.1	77.0	75.0	75.0
65°	83.1	79.1	73.6	66.8	64.1	61.3	57.3	53.2	51.1	50.4
67.5°	58.6	53.8	49.1	43.6	41.6	40.2	36.1	33.4	32.0	31.3
70°	35.4	32.7	29.3	25.2	23.2	21.8	19.1	17.0	16.4	15.7
72.5°	18.4	16.4	13.6	10.9	9.5	8.2	6.8	5.5	4.8	4.8
75°	6.8	5.5	3.4	2.1	1.4	1.4	1.4	1.4	1.4	1.4
77.5°	1.4	0.7	0.7	0.7	0.7	0.7	0.7	0.7	0.7	0.7
80°	0.7	0.7	0.7	0.7	0.7	0.7	0.7	0.7	0.7	0.7
82.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)