

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P579148

Luminaire Tested: **FLD6C-70-D010 FEU6C-X-90-50 F6X-M-X-H**

Issue Date: 3/1/2023



Test Information

Test Method: LM-79-08
Report Number: P579148
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P203254)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/1/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD6C-70-D010 FEU6C-X-90-50 F6X-M-X-H
Description: 6 INCH FAIL-SAFE LED DOWNLIGHT WITH 5000K, 90 CRI LEDS, 6LBMH TRIM

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5425.9 lumens
Efficiency: N/A
Efficacy: 69.6 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.93
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 78
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P579148

CATALOG NUMBER: FLD6C-70-D010 FEU6C-X-90-50 F6X-M-X-H

Luminous Intensity Polar Plot





TEST NUMBER: P579148

CATALOG NUMBER: FLD6C-70-D010 FEU6C-X-90-50 F6X-M-X-H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	92			92
2	107	102	97	93	105	100	96	92	97	93	90	94	91	88	91	89	87	85			85
3	101	94	88	84	99	92	88	84	90	86	82	87	84	81	85	82	80	78			78
4	95	87	81	76	93	86	80	76	84	79	75	82	78	74	80	76	73	72			72
5	90	81	75	70	88	80	74	70	78	73	69	76	72	68	75	71	68	66			66
6	85	75	69	64	83	75	69	64	73	68	64	72	67	63	70	66	63	61			61
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57			57
8	76	66	60	55	75	65	59	55	64	59	55	63	58	55	62	58	54	53			53
9	72	62	56	51	71	61	55	51	60	55	51	60	55	51	59	54	51	49			49
10	69	58	52	48	68	58	52	48	57	52	48	56	51	48	55	51	48	46			46

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	294379
5°	289109
10°	274332
15°	257255
20°	239584
25°	220749
30°	183933
35°	129643
40°	82619
45°	49269
50°	29082
55°	18504
60°	12740
65°	9041
70°	6219
75°	4914
80°	2399
85°	0



TEST NUMBER: P579148

CATALOG NUMBER: FLD6C-70-D010 FEU6C-X-90-50 F6X-M-X-H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	491.0	9.0
10°-20°	1270.2	23.4
20°-30°	1645.8	30.3
30°-40°	1221.9	22.5
40°-50°	515.8	9.5
50°-60°	183.1	3.4
60°-70°	70.7	1.3
70°-80°	24.5	0.5
80°-90°	3.1	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3406.9	62.8
0°-40°	4628.8	85.3
0°-60°	5327.7	98.2
0°-90°	5425.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5425.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5370	
5°	5254	491
15°	4533	1270
25°	3650	1646
35°	1937	1222
45°	636	516
55°	194	183
65°	70	71
75°	23	24
85°	0	3
90°	0	



TEST NUMBER: P579148

CATALOG NUMBER: FLD6C-70-D010 FEU6C-X-90-50 F6X-M-X-H

CANDELA DISTRIBUTION (FULL):

	0°
0°	5369.9
2.5°	5354.3
5°	5253.7
7.5°	5106.2
10°	4928.2
12.5°	4734.3
15°	4532.8
17.5°	4308.3
20°	4106.8
22.5°	3897.6
25°	3649.5
27.5°	3308.5
30°	2905.7
32.5°	2432.9
35°	1937.2
37.5°	1518.8
40°	1154.5
42.5°	860.0
45°	635.5
47.5°	464.9
50°	341.0
52.5°	255.7
55°	193.6
57.5°	147.1
60°	116.2
62.5°	85.3
65°	69.7
67.5°	54.1
70°	38.8
72.5°	30.9
75°	23.2
77.5°	15.6
80°	7.6
82.5°	7.6
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-MV3F9LC





— 0°-180°







(END OF REPORT)