

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P579228

Luminaire Tested: **FLD6C-75-D010 FEU6C-X-90-27 F6X-N-X-H**

Issue Date: 3/1/2023



**Test Information**

Test Method: LM-79-08  
Report Number: P579228  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P203666)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/1/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: FAIL-SAFE  
Catalog Number: FLD6C-75-D010 FEU6C-X-90-27 F6X-N-X-H  
Description: 6 INCH FAIL-SAFE LED DOWNLIGHT WITH 2700K, 90 CRI LEDS, 6LBNH TRIM

Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 5092.9 lumens  
Efficiency: N/A  
Efficacy: 62.5 lumens/watt  
Spacing Criteria (0/90/45): 0.78 / 0.78 / 0.84  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct

Input Watts (W): 81.5  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P579228

CATALOG NUMBER: FLD6C-75-D010 FEU6C-X-90-27 F6X-N-X-H

### Luminous Intensity Polar Plot





TEST NUMBER: P579228

CATALOG NUMBER: FLD6C-75-D010 FEU6C-X-90-27 F6X-N-X-H

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	111	108	106	111	109	106	104	104	103	101	101	99	98	97	96	95	93			
2	108	103	99	96	106	101	98	94	98	95	92	95	93	90	92	90	89	87			
3	102	96	91	87	100	95	90	86	92	88	85	90	86	84	87	85	82	81			
4	97	90	84	80	95	89	83	79	86	82	78	84	81	78	83	79	77	75			
5	92	84	78	74	91	83	78	73	81	76	73	80	75	72	78	74	72	70			
6	88	79	73	69	86	78	72	68	77	72	68	75	71	67	74	70	67	65			
7	83	74	68	64	82	73	68	64	72	67	63	71	66	63	70	66	63	61			
8	79	70	64	60	78	69	64	60	68	63	59	67	63	59	66	62	59	58			
9	76	66	60	56	75	66	60	56	65	59	56	64	59	56	63	59	55	54			
10	72	62	57	53	71	62	57	53	61	56	53	60	56	52	60	55	52	51			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	357904
5°	349047
10°	322072
15°	285144
20°	247582
25°	211766
30°	174590
35°	114974
40°	61809
45°	27359
50°	11096
55°	8000
60°	5087
65°	3632
70°	2997
75°	1970
80°	2936
85°	0



TEST NUMBER: P579228

CATALOG NUMBER: FLD6C-75-D010 FEU6C-X-90-27 F6X-N-X-H

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	587.1	11.5
10°-20°	1400.1	27.5
20°-30°	1603.9	31.5
30°-40°	1077.6	21.2
40°-50°	307.9	6.0
50°-60°	75.4	1.5
60°-70°	28.6	0.6
70°-80°	11.1	0.2
80°-90°	1.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3591.1	70.5
0°-40°	4668.7	91.7
0°-60°	5052.0	99.2
0°-90°	5092.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5092.9	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	6529	
5°	6343	587
15°	5024	1400
25°	3501	1604
35°	1718	1078
45°	353	308
55°	84	75
65°	28	29
75°	9	11
85°	0	1
90°	0	



TEST NUMBER: P579228

CATALOG NUMBER: FLD6C-75-D010 FEU6C-X-90-27 F6X-N-X-H

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	6528.7
2.5°	6482.3
5°	6342.9
7.5°	6092.0
10°	5785.8
12.5°	5395.5
15°	5024.2
17.5°	4634.2
20°	4243.9
22.5°	3872.7
25°	3501.0
27.5°	3157.4
30°	2758.1
32.5°	2228.7
35°	1718.0
37.5°	1253.6
40°	863.7
42.5°	566.4
45°	352.9
47.5°	213.5
50°	130.1
52.5°	102.1
55°	83.7
57.5°	65.1
60°	46.4
62.5°	37.0
65°	28.0
67.5°	18.7
70°	18.7
72.5°	9.3
75°	9.3
77.5°	9.3
80°	9.3
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-MV3F9LC







— 0°-180°







(END OF REPORT)