

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P645788

Luminaire Tested: **FLDSQ4C15D010 FEU4C159030 F4LC-SQ-H-D2W**

Issue Date: 12/13/2022

**Test Information**

Test Method: LM-79-08  
Report Number: P645788  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P207151)  
Test Lab: INNOVATION CENTER  
Issue Date: 12/13/2022  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: FAIL-SAFE  
Catalog Number: FLDSQ4C15D010 FEU4C159030 F4LC-SQ-H-D2W  
Description: 4 INCH 1500 LUMEN FAIL-SAFE LED DOWNLIGHT WITH, 3000K, 90CRI LEDS AND F4LC-SQ TRIM WITH H FINISH, DIM TO WARM  
Light Source: -  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1230.1 lumens  
Efficiency: N/A  
Efficacy: 77.9 lumens/watt  
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.93  
Luminous Opening: Rectangular (W 0.33' x L: 0.33' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 15.8  
Input Voltage (V):  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P645788  
CATALOG NUMBER: FLDSQ4C15D010 FEU4C159030 F4LC-SQ-H-D2W

### Luminous Intensity Polar Plot





TEST NUMBER: P645788

CATALOG NUMBER: FLDSQ4C15D010 FEU4C159030 F4LC-SQ-H-D2W

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93
2	107	102	98	94	105	100	96	93	97	94	91	94	91	89	91	89	87	85
3	101	94	89	85	99	93	88	84	90	86	83	88	84	82	86	83	80	79
4	96	88	82	77	94	86	81	77	84	80	76	82	78	75	80	77	74	73
5	90	82	75	71	89	81	75	70	79	74	70	77	73	69	75	72	69	67
6	86	76	70	65	84	75	69	65	74	68	64	72	68	64	71	67	64	62
7	81	71	65	60	80	70	64	60	69	64	60	68	63	59	67	62	59	58
8	77	67	60	56	75	66	60	56	65	59	56	64	59	55	63	58	55	54
9	73	63	56	52	72	62	56	52	61	56	52	60	55	52	59	55	52	50
10	69	59	53	49	68	59	53	49	58	52	49	57	52	48	56	52	48	47

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	117678
5°	115967
10°	111126
15°	104957
20°	97968
25°	88940
30°	74259
35°	53795
40°	33668
45°	19254
50°	10042
55°	5619
60°	3589
65°	2123
70°	1580
75°	708
80°	1056
85°	0



TEST NUMBER: P645788  
 CATALOG NUMBER: FLDSQ4C15D010 FEU4C159030 F4LC-SQ-H-D2W

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	112.2	9.1
10°-20°	294.4	23.9
20°-30°	378.4	30.8
30°-40°	284.7	23.1
40°-50°	114.4	9.3
50°-60°	32.5	2.6
60°-70°	10.3	0.8
70°-80°	3.0	0.2
80°-90°	0.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	785.0	63.8
0°-40°	1069.7	87.0
0°-60°	1216.5	98.9
0°-90°	1230.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1230.1	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1220	
5°	1197	112
15°	1051	294
25°	835	378
35°	457	285
45°	141	114
55°	33	32
65°	9	10
75°	2	3
85°	0	0
90°	0	



TEST NUMBER: P645788  
CATALOG NUMBER: FLDSQ4C15D010 FEU4C159030 F4LC-SQ-H-D2W

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1219.6
2.5°	1212.2
5°	1197.3
7.5°	1169.5
10°	1134.2
12.5°	1091.6
15°	1050.7
17.5°	1004.3
20°	954.1
22.5°	900.4
25°	835.4
27.5°	757.4
30°	666.5
32.5°	564.3
35°	456.7
37.5°	356.4
40°	267.3
42.5°	196.8
45°	141.1
47.5°	96.6
50°	66.9
52.5°	46.4
55°	33.4
57.5°	24.1
60°	18.6
62.5°	13.0
65°	9.3
67.5°	7.4
70°	5.6
72.5°	3.7
75°	1.9
77.5°	1.9
80°	1.9
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)