

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P579298

Luminaire Tested: **FLD6C-75-D010 FEU6C-X-90-30 F6X-N-X-LI**

Issue Date: 3/1/2023



Test Information

Test Method: LM-79-08
Report Number: P579298
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P205310)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/1/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD6C-75-D010 FEU6C-X-90-30 F6X-N-X-LI
Description: 6 INCH FAIL-SAFE LED DOWNLIGHT WITH 3000K, 90 CRI LEDS, 6LBNLI TRIM

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6694.9 lumens
Efficiency: N/A
Efficacy: 82.1 lumens/watt
Spacing Criteria (0/90/45): 0.53 / 0.53 / 0.58
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 81.5
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P579298

CATALOG NUMBER: FLD6C-75-D010 FEU6C-X-90-30 F6X-N-X-LI

Luminous Intensity Polar Plot





TEST NUMBER: P579298

CATALOG NUMBER: FLD6C-75-D010 FEU6C-X-90-30 F6X-N-X-LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	114	112	109	107	112	109	107	106	105	104	102	102	101	99	98	97	96	95				95
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	93	91	89				89
3	105	99	94	91	103	97	93	90	95	91	89	93	90	87	90	88	86	85				85
4	100	93	88	85	98	92	88	84	90	86	83	88	85	82	86	84	81	80				80
5	96	88	83	79	94	87	83	79	86	82	78	84	81	78	83	80	77	76				76
6	92	84	79	75	90	83	78	75	82	77	74	80	76	74	79	76	73	72				72
7	88	80	74	71	87	79	74	71	78	73	70	77	73	70	76	72	69	68				68
8	84	76	71	67	83	75	70	67	74	70	67	73	69	66	73	69	66	65				65
9	81	73	67	64	80	72	67	64	71	67	63	70	66	63	70	66	63	62				62
10	78	69	64	61	77	69	64	61	68	64	61	67	63	60	67	63	60	59				59

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	835618
5°	781447
10°	637330
15°	468992
20°	323259
25°	239984
30°	180262
35°	112411
40°	54567
45°	18715
50°	2456
55°	1854
60°	1064
65°	1258
70°	1555
75°	0
80°	0
85°	0



TEST NUMBER: P579298

CATALOG NUMBER: FLD6C-75-D010 FEU6C-X-90-30 F6X-N-X-LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1267.3	18.9
10°-20°	2274.8	34.0
20°-30°	1839.2	27.5
30°-40°	1059.5	15.8
40°-50°	224.0	3.3
50°-60°	19.3	0.3
60°-70°	9.6	0.1
70°-80°	1.3	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5381.3	80.4
0°-40°	6440.8	96.2
0°-60°	6684.1	99.8
0°-90°	6694.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6694.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	15243	
5°	14200	###
15°	8264	2275
25°	3968	1839
35°	1680	1059
45°	241	224
55°	19	19
65°	10	10
75°	0	1
85°	0	0
90°	0	



TEST NUMBER: P579298

CATALOG NUMBER: FLD6C-75-D010 FEU6C-X-90-30 F6X-N-X-LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	15242.9
2.5°	15059.8
5°	14200.5
7.5°	12964.8
10°	11449.2
12.5°	9895.1
15°	8263.6
17.5°	6690.0
20°	5541.1
22.5°	4662.7
25°	3967.5
27.5°	3378.8
30°	2847.7
32.5°	2259.0
35°	1679.7
37.5°	1168.0
40°	762.5
42.5°	463.5
45°	241.4
47.5°	96.4
50°	28.8
52.5°	28.8
55°	19.4
57.5°	19.4
60°	9.7
62.5°	9.7
65°	9.7
67.5°	9.7
70°	9.7
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-MV3F9LC





— 0°-180°







(END OF REPORT)