

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P579468

Luminaire Tested: **FLD6C-75-D010 FEU6C-X-90-50 F6X-N-X-H**

Issue Date: 3/1/2023



Test Information

Test Method: LM-79-08
Report Number: P579468
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P203666)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/1/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD6C-75-D010 FEU6C-X-90-50 F6X-N-X-H
Description: 6 INCH FAIL-SAFE LED DOWNLIGHT WITH 5000K, 90 CRI LEDS, 6LBNH TRIM

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5488.0 lumens
Efficiency: N/A
Efficacy: 67.3 lumens/watt
Spacing Criteria (0/90/45): 0.78 / 0.78 / 0.84
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 81.5
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P579468

CATALOG NUMBER: FLD6C-75-D010 FEU6C-X-90-50 F6X-N-X-H

Luminous Intensity Polar Plot





TEST NUMBER: P579468

CATALOG NUMBER: FLD6C-75-D010 FEU6C-X-90-50 F6X-N-X-H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	111	108	106	111	109	106	104	104	103	101	101	99	98	97	96	95	93			
2	108	103	99	96	106	101	98	94	98	95	92	95	93	90	92	90	89	87			
3	102	96	91	87	100	95	90	86	92	88	85	90	86	84	87	85	82	81			
4	97	90	84	80	95	89	83	79	86	82	78	84	81	78	83	79	77	75			
5	92	84	78	74	91	83	78	73	81	76	73	80	75	72	78	74	72	70			
6	88	79	73	69	86	78	72	68	77	72	68	75	71	67	74	70	67	65			
7	83	74	68	64	82	73	68	64	72	67	63	71	66	63	70	66	63	61			
8	79	70	64	60	78	69	64	60	68	63	59	67	63	59	66	62	59	58			
9	76	66	60	56	75	66	60	56	65	59	56	64	59	56	63	59	55	54			
10	72	62	57	53	71	62	57	53	61	56	53	60	56	52	60	55	52	51			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	385665
5°	376116
10°	347049
15°	307261
20°	266787
25°	228195
30°	188130
35°	123888
40°	66603
45°	29484
50°	11957
55°	8621
60°	5482
65°	3917
70°	3222
75°	2139
80°	3189
85°	0



TEST NUMBER: P579468

CATALOG NUMBER: FLD6C-75-D010 FEU6C-X-90-50 F6X-N-X-H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	632.6	11.5
10°-20°	1508.7	27.5
20°-30°	1728.3	31.5
30°-40°	1161.2	21.2
40°-50°	331.8	6.0
50°-60°	81.2	1.5
60°-70°	30.9	0.6
70°-80°	12.0	0.2
80°-90°	1.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3869.6	70.5
0°-40°	5030.8	91.7
0°-60°	5443.8	99.2
0°-90°	5488.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5488.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	7035	
5°	6835	633
15°	5414	1509
25°	3773	1728
35°	1851	1161
45°	380	332
55°	90	81
65°	30	31
75°	10	12
85°	0	1
90°	0	



TEST NUMBER: P579468

CATALOG NUMBER: FLD6C-75-D010 FEU6C-X-90-50 F6X-N-X-H

CANDELA DISTRIBUTION (FULL):

0°	
0°	7035.1
2.5°	6985.1
5°	6834.8
7.5°	6564.5
10°	6234.5
12.5°	5814.0
15°	5413.9
17.5°	4993.7
20°	4573.1
22.5°	4173.0
25°	3772.6
27.5°	3402.3
30°	2972.0
32.5°	2401.6
35°	1851.2
37.5°	1350.9
40°	930.7
42.5°	610.4
45°	380.3
47.5°	230.1
50°	140.2
52.5°	110.0
55°	90.2
57.5°	70.1
60°	50.0
62.5°	39.9
65°	30.2
67.5°	20.1
70°	20.1
72.5°	10.1
75°	10.1
77.5°	10.1
80°	10.1
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-MV3F9LC





— 0°-180°







(END OF REPORT)