

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P574488

Luminaire Tested: **FLD6C-08-D010 FEU6C-X-90-30 F6X-N-X-H**

Issue Date: 3/1/2023



Test Information

Test Method: LM-79-08
Report Number: P574488
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P203666)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/1/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD6C-08-D010 FEU6C-X-90-30 F6X-N-X-H
Description: 6 INCH FAIL-SAFE LED DOWNLIGHT WITH 3000K, 90 CRI LEDS, 6LBNH TRIM

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 565.0 lumens
Efficiency: N/A
Efficacy: 57.2 lumens/watt
Spacing Criteria (0/90/45): 0.78 / 0.78 / 0.84
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 9.87
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P574488

CATALOG NUMBER: FLD6C-08-D010 FEU6C-X-90-30 F6X-N-X-H

Luminous Intensity Polar Plot





TEST NUMBER: P574488

CATALOG NUMBER: FLD6C-08-D010 FEU6C-X-90-30 F6X-N-X-H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	111	108	106	111	109	106	104	105	103	101	101	99	98	97	96	95	93			
2	108	103	99	96	106	101	98	94	98	95	92	95	93	90	92	90	89	87			
3	102	96	91	87	100	95	90	86	92	88	85	90	86	84	87	85	82	81			
4	97	90	84	80	95	89	83	79	86	82	78	84	81	78	83	79	77	75			
5	92	84	78	74	91	83	78	73	81	76	73	80	75	72	78	74	72	70			
6	88	79	73	69	86	78	72	68	77	72	68	75	71	67	74	70	67	65			
7	83	74	68	64	82	73	68	64	72	67	63	71	66	63	70	66	63	61			
8	79	70	64	60	78	69	64	60	68	63	59	67	63	59	66	62	59	58			
9	76	66	60	56	75	66	60	56	65	59	56	64	59	56	63	59	55	54			
10	72	62	57	53	71	62	57	53	61	56	53	60	56	52	60	55	52	51			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	39706
5°	38724
10°	35732
15°	31635
20°	27466
25°	23493
30°	19370
35°	12756
40°	6856
45°	3039
50°	1228
55°	889
60°	559
65°	402
70°	337
75°	212
80°	316
85°	0



TEST NUMBER: P574488

CATALOG NUMBER: FLD6C-08-D010 FEU6C-X-90-30 F6X-N-X-H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	65.1	11.5
10°-20°	155.3	27.5
20°-30°	177.9	31.5
30°-40°	119.5	21.2
40°-50°	34.2	6.0
50°-60°	8.3	1.5
60°-70°	3.2	0.6
70°-80°	1.2	0.2
80°-90°	0.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	398.4	70.5
0°-40°	517.9	91.7
0°-60°	560.4	99.2
0°-90°	565.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	565.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	724	
5°	704	65
15°	557	155
25°	388	178
35°	191	120
45°	39	34
55°	9	8
65°	3	3
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P574488

CATALOG NUMBER: FLD6C-08-D010 FEU6C-X-90-30 F6X-N-X-H

CANDELA DISTRIBUTION (FULL):

0°	
0°	724.3
2.5°	719.1
5°	703.7
7.5°	675.8
10°	641.9
12.5°	598.6
15°	557.4
17.5°	514.1
20°	470.8
22.5°	429.6
25°	388.4
27.5°	350.3
30°	306.0
32.5°	247.2
35°	190.6
37.5°	139.1
40°	95.8
42.5°	62.8
45°	39.2
47.5°	23.7
50°	14.4
52.5°	11.3
55°	9.3
57.5°	7.2
60°	5.1
62.5°	4.1
65°	3.1
67.5°	2.1
70°	2.1
72.5°	1.0
75°	1.0
77.5°	1.0
80°	1.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-MV3F9LC





— 0°-180°







(END OF REPORT)