

LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P#

Luminaire Tested: **FLDSQ4C30D010 FEU4C309030 F4LC-DFSSQ-MW**

Issue Date: 12/13/2022

Tested By:

Approved By:



Cooper Lighting Solutions laboratories have been accredited by National Voluntary Laboratory Accreditation Program (NVLAP) that it adheres to the requirements of ISO/IEC 17025:2005 and appropriate IESNA test methods. This report must not be used to claim product certification, approval or endorsement by NVLAP, NIST or any agency of the Federal Government. Results contained in this report are valid for luminaire sample tested, as supplied by requestor. Information related to the luminaire tested has been supplied by requestor and can affect the validity of the test results. Report shall not be reproduced except in full without approval of Cooper Lighting Solutions Lighting Laboratory. Test performed at address noted above.

Test Information

Test Method: LM-79-08
 Report Number: P#
 Test Lab: INNOVATION CENTER
 Issue Date: 12/13/2022
 Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
 Product Line: FAIL-SAFE
 Catalog Number: FLDSQ4C30D010 FEU4C309030 F4LC-DFSSQ-MW
 Description: 4 INCH 3000 LUMEN FAIL-SAFE LED DOWNLIGHT WITH, 3000K, 90CRI LEDS AND F4LC-DFSSQ TRIM WITH MW FINISH
 Light Source: -
 Ballast/Driver: -

Summary


Lumens per Lamp: N/A
 Luminaire Lumens: 2883.0 lumens
 Efficiency: N/A
 Efficacy: 91.2 lumens/watt
 Spacing Criteria (0/90/45): 1.19 / 1.2 / 1.29
 Luminous Opening: Rectangular (W 0.33' x L: 0.33' x H: 0')
 CIE Type: Direct

Input Watts (W): 31.6
 Input Voltage (V):
 Input Current (Ain): NR
 Voltage Rise (V): NR
 Power Factor: NR
 Total Harmonic Distortion (THDi): NR
 Frequency (hertz): 60
 Stabilization Time: NR
 Operation Time: NR
 Ambient Temperature (°C): NR
 Test Distance: 25 FT

Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	GONIO 1 IN0055	4/22/2021	10/22/2021
Power Meter	XITRON 2801 IN0197	12/1/2020	12/1/2021
AC Power Source	CHROMA 61505 IN0196	12/1/2020	12/1/2021
DC Power Supply	AGILENT E3634A IN0198	11/30/2020	11/30/2021
Room Thermometer	ONSET IN0143	12/1/2020	12/1/2021

TEST NUMBER: P#
CATALOG NUMBER: FLDSQ4C30D010 FEU4C309030 F4LC-DFSSQ-MW

Luminous Intensity Polar Plot



TEST NUMBER: P#
 CATALOG NUMBER: FLDSQ4C30D010 FEU4C309030 F4LC-DFSSQ-MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	111	108	104	101	109	105	102	100	101	99	96		97	95	94		94	92	91	89
2	103	96	91	86	100	94	89	85	91	87	83		88	84	81		85	82	79	77
3	95	86	79	74	93	85	78	73	82	76	72		79	74	71		77	73	69	67
4	88	77	70	64	86	76	69	63	74	67	63		71	66	62		69	65	61	59
5	81	70	62	56	79	69	61	56	67	60	55		65	59	54		63	58	54	52
6	75	63	55	49	73	62	55	49	61	54	49		59	53	48		57	52	48	46
7	70	58	50	44	68	57	49	44	55	49	44		54	48	43		53	47	43	41
8	65	53	45	40	64	52	45	39	51	44	39		50	44	39		49	43	39	37
9	61	49	41	36	60	48	41	36	47	40	36		46	40	35		45	39	35	33
10	57	45	38	33	56	44	37	33	44	37	32		43	37	32		42	36	32	31

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	130221	130221	130221
5°	128123	129789	130157
10°	129232	128850	129409
15°	126964	127153	127533
20°	124008	125980	125394
25°	123477	123477	124296
30°	120039	120886	121109
35°	116283	117426	115388
40°	110830	112996	112039
45°	104894	107254	103843
50°	92378	100439	91807
55°	74809	91900	75145
60°	54748	76207	53648
65°	33265	54270	32397
70°	12977	29227	12441
75°	1417	7866	1417
80°	1111	1111	1111
85°	0	0	0

TEST NUMBER: P#
 CATALOG NUMBER: FLDSQ4C30D010 FEU4C309030 F4LC-DFSSQ-MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	127.4	4.4
10°-20°	360.5	12.5
20°-30°	534.9	18.6
30°-40°	619.8	21.5
40°-50°	594.2	20.6
50°-60°	436.9	15.2
60°-70°	188.7	6.5
70°-80°	20.4	0.7
80°-90°	0.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1022.8	35.5
0°-40°	1642.5	57.0
0°-60°	2673.7	92.7
0°-90°	2883.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2883.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1350	1350	1350	1350	1350	
5°	1323	1336	1340	1342	1344	126
15°	1271	1279	1273	1275	1277	358
25°	1160	1158	1160	1162	1168	531
35°	987	993	997	995	980	617
45°	769	771	786	774	761	584
55°	445	491	546	489	447	400
65°	146	182	238	180	142	150
75°	4	6	21	4	4	12
85°	0	0	0	0	0	0
90°	0	0	0	0	0	



TEST NUMBER: P#
 CATALOG NUMBER: FLDSQ4C30D010 FEU4C309030 F4LC-DFSSQ-MW

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1349.6	1349.6	1349.6	1349.6	1349.6	1349.6	1349.6	1349.6	1349.6	1349.6	1349.6
2.5°	1340.0	1355.3	1357.3	1347.7	1343.8	1338.1	1351.5	1342.0	1345.8	1342.0	1340.0
5°	1322.8	1340.0	1342.0	1342.0	1338.1	1336.2	1342.0	1340.0	1338.1	1334.3	1340.0
7.5°	1315.1	1324.7	1334.3	1322.8	1328.5	1326.6	1340.0	1334.3	1332.3	1332.3	1328.5
10°	1319.0	1317.0	1324.7	1313.2	1317.0	1313.2	1324.7	1324.7	1320.8	1317.0	1315.1
12.5°	1288.2	1303.6	1303.6	1301.7	1297.8	1292.1	1303.6	1311.3	1299.7	1299.7	1297.8
15°	1271.0	1274.8	1276.7	1276.7	1274.8	1278.7	1284.4	1276.7	1278.7	1269.1	1272.9
17.5°	1251.9	1244.2	1249.9	1246.1	1248.0	1251.9	1259.5	1259.5	1248.0	1246.1	1249.9
20°	1207.7	1230.7	1232.7	1221.2	1223.1	1223.1	1236.5	1225.0	1232.7	1223.1	1226.9
22.5°	1186.6	1202.0	1203.9	1188.6	1198.1	1186.6	1200.1	1182.8	1202.0	1188.6	1194.3
25°	1159.8	1157.9	1163.6	1156.0	1157.9	1157.9	1167.5	1159.8	1165.6	1157.9	1159.8
27.5°	1115.8	1131.1	1129.1	1121.5	1125.3	1123.4	1142.6	1121.5	1133.0	1123.4	1127.3
30°	1077.4	1090.8	1087.0	1079.3	1079.3	1073.5	1094.6	1088.9	1087.0	1087.0	1085.0
32.5°	1039.0	1041.0	1037.1	1039.0	1041.0	1033.3	1050.5	1042.9	1041.0	1042.9	1044.8
35°	987.2	987.2	991.1	985.4	993.0	993.0	1008.4	998.7	996.9	991.1	996.9
37.5°	941.3	935.5	937.4	937.4	941.3	945.1	952.8	948.9	948.9	943.2	947.0
40°	879.9	876.1	881.8	881.8	887.6	887.6	895.3	891.4	897.1	897.1	897.1
42.5°	826.3	826.3	822.4	828.2	830.1	828.2	841.6	839.7	841.6	837.8	839.7
45°	768.7	768.7	764.9	763.0	772.5	770.7	786.0	780.2	787.9	784.0	786.0
47.5°	690.1	699.7	693.9	699.7	711.2	713.2	722.7	718.9	726.6	720.8	728.5
50°	615.4	615.4	621.1	628.8	640.3	642.2	653.7	661.4	665.2	667.1	669.1
52.5°	536.8	534.8	540.6	550.2	559.8	567.5	579.0	590.5	598.1	609.6	603.8
55°	444.7	448.6	454.4	465.9	481.2	490.7	500.3	515.7	529.1	534.8	546.3
57.5°	366.1	362.3	366.1	381.5	398.7	406.4	419.9	435.2	454.4	465.9	469.7
60°	283.7	285.6	289.5	302.9	316.3	327.8	333.6	358.5	375.8	387.2	394.9
62.5°	209.0	212.8	216.7	228.2	241.5	251.2	260.7	281.8	297.1	308.6	316.3
65°	145.7	147.6	153.4	159.1	172.5	182.1	189.8	207.0	222.4	232.0	237.7
67.5°	90.1	92.0	95.8	103.6	113.1	120.8	128.4	139.9	153.4	162.9	164.9
70°	46.0	47.9	49.8	55.6	63.3	67.1	72.8	82.4	92.0	99.6	103.6
72.5°	15.3	15.3	17.3	21.1	24.9	28.8	30.7	40.3	47.9	51.8	53.7
75°	3.8	3.8	3.8	3.8	3.8	5.8	5.8	11.5	15.3	19.2	21.1
77.5°	2.0	2.0	2.0	2.0	2.0	2.0	2.0	2.0	2.0	3.8	3.8
80°	2.0	2.0	2.0	2.0	2.0	2.0	2.0	2.0	2.0	2.0	2.0
82.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P#
 CATALOG NUMBER: FLDSQ4C30D010 FEU4C309030 F4LC-DFSSQ-MW

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°
0°	1349.6	1349.6	1349.6	1349.6	1349.6	1349.6	1349.6	1349.6	1349.6	1349.6
2.5°	1349.6	1345.8	1343.8	1345.8	1345.8	1343.8	1349.6	1357.3	1366.8	1342.0
5°	1347.7	1343.8	1347.7	1336.2	1342.0	1338.1	1345.8	1343.8	1351.5	1343.8
7.5°	1342.0	1334.3	1336.2	1330.5	1338.1	1328.5	1334.3	1345.8	1338.1	1326.6
10°	1322.8	1319.0	1332.3	1313.2	1309.3	1317.0	1332.3	1320.8	1317.0	1320.8
12.5°	1303.6	1303.6	1309.3	1294.0	1295.9	1299.7	1307.4	1299.7	1303.6	1313.2
15°	1282.5	1278.7	1288.2	1276.7	1274.8	1271.0	1278.7	1278.7	1282.5	1276.7
17.5°	1257.6	1251.9	1251.9	1248.0	1246.1	1255.7	1259.5	1261.4	1263.3	1255.7
20°	1226.9	1225.0	1230.7	1225.0	1226.9	1228.9	1228.9	1225.0	1242.2	1221.2
22.5°	1194.3	1200.1	1192.4	1188.6	1192.4	1196.2	1196.2	1198.1	1194.3	1190.5
25°	1161.7	1165.6	1167.5	1156.0	1161.7	1156.0	1169.4	1171.3	1163.6	1167.5
27.5°	1133.0	1127.3	1125.3	1117.6	1121.5	1119.6	1121.5	1121.5	1133.0	1117.6
30°	1088.9	1083.1	1085.0	1079.3	1081.2	1079.3	1081.2	1081.2	1088.9	1087.0
32.5°	1046.7	1041.0	1042.9	1037.1	1037.1	1039.0	1035.2	1035.2	1041.0	1037.1
35°	1006.4	993.0	994.9	993.0	994.9	987.2	987.2	985.4	989.2	979.6
37.5°	948.9	943.2	941.3	939.4	941.3	937.4	941.3	935.5	941.3	933.6
40°	897.1	893.3	895.3	883.8	883.8	885.6	881.8	879.9	881.8	889.5
42.5°	845.4	837.8	833.9	830.1	832.0	826.3	824.3	820.5	824.3	816.7
45°	784.0	784.0	782.2	772.5	774.5	774.5	766.8	759.2	761.0	761.0
47.5°	728.5	724.7	722.7	713.2	711.2	709.3	701.6	695.9	695.9	690.1
50°	667.1	663.3	657.6	647.9	644.1	632.6	626.9	619.2	611.6	611.6
52.5°	609.6	596.2	588.5	573.2	567.5	561.7	546.3	540.6	534.8	529.1
55°	540.6	529.1	513.8	496.5	488.9	479.2	463.9	452.4	444.7	446.7
57.5°	473.5	454.4	439.0	416.0	406.4	400.6	385.3	370.0	362.3	362.3
60°	391.1	375.8	356.6	335.5	327.8	318.3	299.0	289.5	283.7	278.0
62.5°	312.5	301.0	283.7	256.9	251.2	241.5	228.2	216.7	210.9	210.9
65°	233.9	222.4	207.0	187.9	180.2	172.5	161.0	149.5	143.8	141.9
67.5°	164.9	151.4	138.1	122.7	116.9	113.1	101.6	93.9	90.1	88.2
70°	99.6	92.0	82.4	70.9	65.2	61.3	53.7	47.9	46.0	44.1
72.5°	51.8	46.0	38.3	30.7	26.8	23.0	19.2	15.3	13.5	13.5
75°	19.2	15.3	9.6	5.8	3.8	3.8	3.8	3.8	3.8	3.8
77.5°	3.8	2.0	2.0	2.0	2.0	2.0	2.0	2.0	2.0	2.0
80°	2.0	2.0	2.0	2.0	2.0	2.0	2.0	2.0	2.0	2.0
82.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)