

LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P#

Luminaire Tested: **FLDSQ4C30D010 FEU4C309035 F4LC-CSSQ-MW**

Issue Date: 12/13/2022

Tested By:

Approved By:



Cooper Lighting Solutions laboratories have been accredited by National Voluntary Laboratory Accreditation Program (NVLAP) that it adheres to the requirements of ISO/IEC 17025:2005 and appropriate IESNA test methods. This report must not be used to claim product certification, approval or endorsement by NVLAP, NIST or any agency of the Federal Government. Results contained in this report are valid for luminaire sample tested, as supplied by requestor. Information related to the luminaire tested has been supplied by requestor and can affect the validity of the test results. Report shall not be reproduced except in full without approval of Cooper Lighting Solutions Lighting Laboratory. Test performed at address noted above.

**Test Information**

Test Method: LM-79-08  
 Report Number: P#  
 Test Lab: INNOVATION CENTER  
 Issue Date: 12/13/2022  
 Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
 Product Line: FAIL-SAFE  
 Catalog Number: FLDSQ4C30D010 FEU4C309035 F4LC-CSSQ-MW  
 Description: 4 INCH 3000 LUMEN FAIL-SAFE LED DOWNLIGHT WITH, 3500K, 90CRI LEDS AND F4LC-CSSQ TRIM WITH MW FINISH  
 Light Source: -  
 Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
 Luminaire Lumens: 2923.0 lumens  
 Efficiency: N/A  
 Efficacy: 92.5 lumens/watt  
 Spacing Criteria (0/90/45): 1.19 / 1.2 / 1.29  
 Luminous Opening: Rectangular (W 0.33' x L: 0.33' x H: 0')  
 CIE Type: Direct

Input Watts (W): 31.6  
 Input Voltage (V):  
 Input Current (Ain): NR  
 Voltage Rise (V): NR  
 Power Factor: NR  
 Total Harmonic Distortion (THDi): NR  
 Frequency (hertz): 60  
 Stabilization Time: NR  
 Operation Time: NR  
 Ambient Temperature (°C): NR  
 Test Distance: 25 FT

Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	GONIO 1 IN0055	4/22/2021	10/22/2021
Power Meter	XITRON 2801 IN0197	12/1/2020	12/1/2021
AC Power Source	CHROMA 61505 IN0196	12/1/2020	12/1/2021
DC Power Supply	AGILENT E3634A IN0198	11/30/2020	11/30/2021
Room Thermometer	ONSET IN0143	12/1/2020	12/1/2021

TEST NUMBER: P#  
CATALOG NUMBER: FLDSQ4C30D010 FEU4C309035 F4LC-CSSQ-MW

### Luminous Intensity Polar Plot



TEST NUMBER: P#

CATALOG NUMBER: FLDSQ4C30D010 FEU4C309035 F4LC-CSSQ-MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	111	108	104	101	109	105	102	100	101	99	96	97	95	94	94	92	91	89				89
2	103	96	91	86	100	94	89	85	91	87	83	88	84	81	85	82	79	77				77
3	95	86	79	74	93	85	78	73	82	76	72	79	74	71	77	73	69	67				67
4	88	77	70	64	86	76	69	63	74	67	63	71	66	62	69	65	61	59				59
5	81	70	62	56	79	69	61	56	67	60	55	65	59	54	63	58	54	52				52
6	75	63	55	49	73	62	55	49	61	54	49	59	53	48	57	52	48	46				46
7	70	58	50	44	68	57	49	44	55	49	44	54	48	43	53	47	43	41				41
8	65	53	45	40	64	52	45	39	51	44	39	50	44	39	49	43	39	37				37
9	61	49	41	36	60	48	41	36	47	40	36	46	40	35	45	39	35	33				33
10	57	45	38	33	56	44	37	33	44	37	32	43	37	32	42	36	32	31				31

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	132026	132026	132026
5°	129896	131591	131968
10°	131025	130643	131211
15°	128722	128921	129301
20°	125733	127725	127130
25°	125191	125191	126021
30°	121699	122568	122791
35°	117897	119052	116990
40°	112367	114571	113588
45°	106354	108742	105289
50°	93654	101820	93083
55°	75852	93179	76188
60°	55500	77268	54381
65°	33722	55023	32854
70°	13147	29622	12611
75°	1454	7978	1454
80°	1111	1111	1111
85°	0	0	0

TEST NUMBER: P#  
 CATALOG NUMBER: FLDSQ4C30D010 FEU4C309035 F4LC-CSSQ-MW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	129.2	4.4
10°-20°	365.5	12.5
20°-30°	542.3	18.6
30°-40°	628.4	21.5
40°-50°	602.5	20.6
50°-60°	443.0	15.2
60°-70°	191.3	6.5
70°-80°	20.7	0.7
80°-90°	0.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1037.0	35.5
0°-40°	1665.3	57.0
0°-60°	2710.7	92.7
0°-90°	2923.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2923.0	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1368	1368	1368	1368	1368	
5°	1341	1355	1359	1361	1362	128
15°	1289	1296	1291	1292	1294	363
25°	1176	1174	1176	1178	1184	538
35°	1001	1007	1011	1009	993	626
45°	779	781	797	785	772	592
55°	451	498	554	496	453	406
65°	148	185	241	183	144	152
75°	4	6	21	4	4	12
85°	0	0	0	0	0	0
90°	0	0	0	0	0	



TEST NUMBER: P#  
 CATALOG NUMBER: FLDSQ4C30D010 FEU4C309035 F4LC-CSSQ-MW

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1368.3	1368.3	1368.3	1368.3	1368.3	1368.3	1368.3	1368.3	1368.3	1368.3	1368.3
2.5°	1358.6	1374.1	1376.1	1366.4	1362.5	1356.7	1370.3	1360.6	1364.5	1360.6	1358.6
5°	1341.1	1358.6	1360.6	1360.6	1356.7	1354.7	1360.6	1358.6	1356.7	1352.8	1358.6
7.5°	1333.4	1343.1	1352.8	1341.1	1346.9	1345.0	1358.6	1352.8	1350.8	1350.8	1346.9
10°	1337.3	1335.3	1343.1	1331.4	1335.3	1331.4	1343.1	1343.1	1339.2	1335.3	1333.4
12.5°	1306.1	1321.6	1321.6	1319.7	1315.8	1310.0	1321.6	1329.5	1317.8	1317.8	1315.8
15°	1288.6	1292.5	1294.4	1294.4	1292.5	1296.4	1302.2	1294.4	1296.4	1286.7	1290.6
17.5°	1269.2	1261.4	1267.2	1263.4	1265.3	1269.2	1277.0	1277.0	1265.3	1263.4	1267.2
20°	1224.5	1247.8	1249.8	1238.1	1240.0	1240.0	1253.7	1242.0	1249.8	1240.0	1243.9
22.5°	1203.1	1218.6	1220.6	1205.1	1214.7	1203.1	1216.7	1199.2	1218.6	1205.1	1210.9
25°	1175.9	1174.0	1179.8	1172.0	1174.0	1174.0	1183.7	1175.9	1181.8	1174.0	1175.9
27.5°	1131.2	1146.8	1144.8	1137.0	1140.9	1139.0	1158.4	1137.0	1148.7	1139.0	1142.9
30°	1092.3	1105.9	1102.1	1094.3	1094.3	1088.4	1109.8	1104.0	1102.1	1102.1	1100.1
32.5°	1053.4	1055.4	1051.5	1053.4	1055.4	1047.7	1065.1	1057.3	1055.4	1057.3	1059.3
35°	1000.9	1000.9	1004.8	999.0	1006.8	1006.8	1022.4	1012.6	1010.7	1004.8	1010.7
37.5°	954.3	948.5	950.4	950.4	954.3	958.2	966.0	962.1	962.1	956.3	960.2
40°	892.1	888.3	894.0	894.0	899.9	899.9	907.7	903.8	909.6	909.6	909.6
42.5°	837.7	837.7	833.9	839.6	841.6	839.6	853.3	851.3	853.3	849.4	851.3
45°	779.4	779.4	775.5	773.6	783.3	781.4	796.9	791.0	798.8	794.9	796.9
47.5°	699.7	709.4	703.6	709.4	721.1	723.1	732.7	728.9	736.6	730.8	738.6
50°	623.9	623.9	629.7	637.5	649.2	651.1	662.8	670.6	674.5	676.4	678.3
52.5°	544.2	542.3	548.1	557.8	567.6	575.3	587.0	598.6	606.4	618.1	612.2
55°	450.9	454.8	460.7	472.3	487.9	497.5	507.3	522.8	536.5	542.3	553.9
57.5°	371.2	367.3	371.2	386.8	404.3	412.1	425.7	441.2	460.7	472.3	476.2
60°	287.6	289.6	293.5	307.1	320.7	332.4	338.2	363.4	381.0	392.6	400.4
62.5°	211.9	215.8	219.7	231.3	244.9	254.6	264.3	285.7	301.3	312.9	320.7
65°	147.7	149.6	155.5	161.3	174.9	184.6	192.4	209.9	225.5	235.2	241.0
67.5°	91.4	93.3	97.1	105.0	114.7	122.4	130.2	141.9	155.5	165.2	167.2
70°	46.6	48.6	50.5	56.4	64.2	68.0	73.8	83.6	93.3	101.0	105.0
72.5°	15.5	15.5	17.5	21.4	25.3	29.2	31.1	40.8	48.6	52.5	54.4
75°	3.9	3.9	3.9	3.9	3.9	5.9	5.9	11.7	15.5	19.4	21.4
77.5°	2.0	2.0	2.0	2.0	2.0	2.0	2.0	2.0	2.0	3.9	3.9
80°	2.0	2.0	2.0	2.0	2.0	2.0	2.0	2.0	2.0	2.0	2.0
82.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P#  
 CATALOG NUMBER: FLDSQ4C30D010 FEU4C309035 F4LC-CSSQ-MW

**CANDELA DISTRIBUTION (continued):**

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°
0°	1368.3	1368.3	1368.3	1368.3	1368.3	1368.3	1368.3	1368.3	1368.3	1368.3
2.5°	1368.3	1364.5	1362.5	1364.5	1364.5	1362.5	1368.3	1376.1	1385.8	1360.6
5°	1366.4	1362.5	1366.4	1354.7	1360.6	1356.7	1364.5	1362.5	1370.3	1362.5
7.5°	1360.6	1352.8	1354.7	1348.9	1356.7	1346.9	1352.8	1364.5	1356.7	1345.0
10°	1341.1	1337.3	1350.8	1331.4	1327.5	1335.3	1350.8	1339.2	1335.3	1339.2
12.5°	1321.6	1321.6	1327.5	1312.0	1313.9	1317.8	1325.5	1317.8	1321.6	1331.4
15°	1300.3	1296.4	1306.1	1294.4	1292.5	1288.6	1296.4	1296.4	1300.3	1294.4
17.5°	1275.0	1269.2	1269.2	1265.3	1263.4	1273.1	1277.0	1278.9	1280.9	1273.1
20°	1243.9	1242.0	1247.8	1242.0	1243.9	1245.9	1245.9	1242.0	1259.5	1238.1
22.5°	1210.9	1216.7	1209.0	1205.1	1209.0	1212.8	1212.8	1214.7	1210.9	1207.0
25°	1177.9	1181.8	1183.7	1172.0	1177.9	1172.0	1185.6	1187.5	1179.8	1183.7
27.5°	1148.7	1142.9	1140.9	1133.1	1137.0	1135.1	1137.0	1137.0	1148.7	1133.1
30°	1104.0	1098.2	1100.1	1094.3	1096.2	1094.3	1096.2	1096.2	1104.0	1102.1
32.5°	1061.2	1055.4	1057.3	1051.5	1051.5	1053.4	1049.6	1049.6	1055.4	1051.5
35°	1020.4	1006.8	1008.7	1006.8	1008.7	1000.9	1000.9	999.0	1002.9	993.2
37.5°	962.1	956.3	954.3	952.4	954.3	950.4	954.3	948.5	954.3	946.5
40°	909.6	905.7	907.7	896.0	896.0	897.9	894.0	892.1	894.0	901.8
42.5°	857.2	849.4	845.5	841.6	843.5	837.7	835.8	831.9	835.8	828.0
45°	794.9	794.9	793.0	783.3	785.2	785.2	777.5	769.7	771.6	771.6
47.5°	738.6	734.7	732.7	723.1	721.1	719.2	711.3	705.5	705.5	699.7
50°	676.4	672.5	666.7	656.9	653.0	641.4	635.6	627.8	620.1	620.1
52.5°	618.1	604.4	596.7	581.1	575.3	569.5	553.9	548.1	542.3	536.5
55°	548.1	536.5	520.9	503.4	495.6	485.9	470.3	458.7	450.9	452.9
57.5°	480.1	460.7	445.1	421.8	412.1	406.2	390.6	375.1	367.3	367.3
60°	396.5	381.0	361.5	340.1	332.4	322.7	303.2	293.5	287.6	281.8
62.5°	316.8	305.2	287.6	260.4	254.6	244.9	231.3	219.7	213.8	213.8
65°	237.1	225.5	209.9	190.5	182.7	174.9	163.3	151.6	145.8	143.9
67.5°	167.2	153.5	140.0	124.4	118.6	114.7	103.0	95.2	91.4	89.4
70°	101.0	93.3	83.6	71.9	66.1	62.2	54.4	48.6	46.6	44.7
72.5°	52.5	46.6	38.9	31.1	27.2	23.3	19.4	15.5	13.6	13.6
75°	19.4	15.5	9.8	5.9	3.9	3.9	3.9	3.9	3.9	3.9
77.5°	3.9	2.0	2.0	2.0	2.0	2.0	2.0	2.0	2.0	2.0
80°	2.0	2.0	2.0	2.0	2.0	2.0	2.0	2.0	2.0	2.0
82.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)