

LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P#

Luminaire Tested: **FLDSQ4C30D010 FEU4C309040 F4LC-CSSQ-MW**

Issue Date: 12/13/2022

Tested By:

Approved By:



Cooper Lighting Solutions laboratories have been accredited by National Voluntary Laboratory Accreditation Program (NVLAP) that it adheres to the requirements of ISO/IEC 17025:2005 and appropriate IESNA test methods. This report must not be used to claim product certification, approval or endorsement by NVLAP, NIST or any agency of the Federal Government. Results contained in this report are valid for luminaire sample tested, as supplied by requestor. Information related to the luminaire tested has been supplied by requestor and can affect the validity of the test results. Report shall not be reproduced except in full without approval of Cooper Lighting Solutions Lighting Laboratory. Test performed at address noted above.

Test Information

Test Method: LM-79-08
 Report Number: P#
 Test Lab: INNOVATION CENTER
 Issue Date: 12/13/2022
 Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
 Product Line: FAIL-SAFE
 Catalog Number: FLDSQ4C30D010 FEU4C309040 F4LC-CSSQ-MW
 Description: 4 INCH 3000 LUMEN FAIL-SAFE LED DOWNLIGHT WITH, 4000K, 90CRI LEDS AND F4LC-CSSQ TRIM WITH MW FINISH
 Light Source: -
 Ballast/Driver: -

Summary


Lumens per Lamp: N/A
 Luminaire Lumens: 2927.0 lumens
 Efficiency: N/A
 Efficacy: 92.6 lumens/watt
 Spacing Criteria (0/90/45): 1.19 / 1.2 / 1.29
 Luminous Opening: Rectangular (W 0.33' x L: 0.33' x H: 0')
 CIE Type: Direct

Input Watts (W): 31.6
 Input Voltage (V):
 Input Current (Ain): NR
 Voltage Rise (V): NR
 Power Factor: NR
 Total Harmonic Distortion (THDi): NR
 Frequency (hertz): 60
 Stabilization Time: NR
 Operation Time: NR
 Ambient Temperature (°C): NR
 Test Distance: 25 FT

Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	GONIO 1 IN0055	4/22/2021	10/22/2021
Power Meter	XITRON 2801 IN0197	12/1/2020	12/1/2021
AC Power Source	CHROMA 61505 IN0196	12/1/2020	12/1/2021
DC Power Supply	AGILENT E3634A IN0198	11/30/2020	11/30/2021
Room Thermometer	ONSET IN0143	12/1/2020	12/1/2021

TEST NUMBER: P#
CATALOG NUMBER: FLDSQ4C30D010 FEU4C309040 F4LC-CSSQ-MW

Luminous Intensity Polar Plot



TEST NUMBER: P#

CATALOG NUMBER: FLDSQ4C30D010 FEU4C309040 F4LC-CSSQ-MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	111	108	104	101	109	105	102	100	101	99	96	97	95	94	94	92	91	89				89
2	103	96	91	86	100	94	89	85	91	87	83	88	84	81	85	82	79	77				77
3	95	86	79	74	93	85	78	73	82	76	72	79	74	71	77	73	69	67				67
4	88	77	70	64	86	76	69	63	74	67	63	71	66	62	69	65	61	59				59
5	81	70	62	56	79	69	61	56	67	60	55	65	59	54	63	58	54	52				52
6	75	63	55	49	73	62	55	49	61	54	49	59	53	48	57	52	48	46				46
7	70	58	50	44	68	57	49	44	55	49	44	54	48	43	53	47	43	41				41
8	65	53	45	40	64	52	45	39	51	44	39	50	44	39	49	43	39	37				37
9	61	49	41	36	60	48	41	36	47	40	36	46	40	35	45	39	35	33				33
10	57	45	38	33	56	44	37	33	44	37	32	43	37	32	42	36	32	31				31

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	132209	132209	132209
5°	130080	131775	132143
10°	131202	130819	131388
15°	128901	129091	129481
20°	125908	127900	127304
25°	125361	125361	126191
30°	121867	122736	122958
35°	118062	119216	117143
40°	112530	114722	113752
45°	106490	108892	105439
50°	93789	101970	93203
55°	75953	93313	76289
60°	55578	77365	54458
65°	33767	55092	32877
70°	13175	29650	12639
75°	1454	7978	1454
80°	1111	1111	1111
85°	0	0	0

TEST NUMBER: P#
 CATALOG NUMBER: FLDSQ4C30D010 FEU4C309040 F4LC-CSSQ-MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	129.3	4.4
10°-20°	366.0	12.5
20°-30°	543.1	18.6
30°-40°	629.2	21.5
40°-50°	603.3	20.6
50°-60°	443.6	15.2
60°-70°	191.6	6.5
70°-80°	20.7	0.7
80°-90°	0.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1038.4	35.5
0°-40°	1667.6	57.0
0°-60°	2714.5	92.7
0°-90°	2927.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2927.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1370	1370	1370	1370	1370	
5°	1343	1357	1360	1362	1364	128
15°	1290	1298	1292	1294	1296	364
25°	1178	1176	1178	1180	1185	539
35°	1002	1008	1012	1010	994	627
45°	780	782	798	786	773	593
55°	452	498	555	496	454	406
65°	148	185	241	183	144	152
75°	4	6	21	4	4	12
85°	0	0	0	0	0	0
90°	0	0	0	0	0	

TEST NUMBER: P#
 CATALOG NUMBER: FLDSQ4C30D010 FEU4C309040 F4LC-CSSQ-MW

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1370.2	1370.2	1370.2	1370.2	1370.2	1370.2	1370.2	1370.2	1370.2	1370.2	1370.2
2.5°	1360.5	1376.0	1378.0	1368.2	1364.3	1358.5	1372.1	1362.4	1366.3	1362.4	1360.5
5°	1343.0	1360.5	1362.4	1362.4	1358.5	1356.6	1362.4	1360.5	1358.5	1354.7	1360.5
7.5°	1335.2	1344.9	1354.7	1343.0	1348.8	1346.9	1360.5	1354.7	1352.7	1352.7	1348.8
10°	1339.1	1337.1	1344.9	1333.2	1337.1	1333.2	1344.9	1344.9	1341.0	1337.1	1335.2
12.5°	1307.9	1323.4	1323.4	1321.5	1317.7	1311.8	1323.4	1331.3	1319.6	1319.6	1317.7
15°	1290.4	1294.3	1296.2	1296.2	1294.3	1298.2	1304.0	1296.2	1298.2	1288.4	1292.3
17.5°	1271.0	1263.2	1269.0	1265.1	1267.1	1271.0	1278.7	1278.7	1267.1	1265.1	1269.0
20°	1226.2	1249.5	1251.5	1239.8	1241.7	1241.7	1255.4	1243.7	1251.5	1241.7	1245.6
22.5°	1204.7	1220.3	1222.3	1206.7	1216.4	1204.7	1218.4	1200.8	1220.3	1206.7	1212.5
25°	1177.5	1175.6	1181.4	1173.6	1175.6	1175.6	1185.3	1177.5	1183.4	1175.6	1177.5
27.5°	1132.8	1148.3	1146.4	1138.6	1142.5	1140.6	1160.0	1138.6	1150.3	1140.6	1144.5
30°	1093.8	1107.5	1103.6	1095.8	1095.8	1089.9	1111.3	1105.5	1103.6	1103.6	1101.6
32.5°	1054.9	1056.9	1053.0	1054.9	1056.9	1049.1	1066.6	1058.8	1056.9	1058.8	1060.8
35°	1002.3	1002.3	1006.2	1000.4	1008.2	1008.2	1023.8	1014.0	1012.1	1006.2	1012.1
37.5°	955.6	949.8	951.7	951.7	955.6	959.5	967.3	963.4	963.4	957.6	961.5
40°	893.4	889.5	895.3	895.3	901.1	901.1	908.9	905.0	910.8	910.8	910.8
42.5°	838.9	838.9	835.0	840.8	842.8	840.8	854.5	852.5	854.5	850.6	852.5
45°	780.4	780.4	776.6	774.6	784.3	782.4	798.0	792.1	799.9	796.0	798.0
47.5°	700.6	710.4	704.5	710.4	722.1	724.1	733.7	729.9	737.6	731.8	739.6
50°	624.8	624.8	630.6	638.4	650.1	652.0	663.7	671.5	675.4	677.3	679.3
52.5°	545.0	543.0	548.9	558.6	568.3	576.1	587.8	599.5	607.2	618.9	613.0
55°	451.5	455.4	461.3	473.0	488.5	498.2	508.0	523.6	537.2	543.0	554.7
57.5°	371.7	367.8	371.7	387.3	404.8	412.6	426.3	441.8	461.3	473.0	476.9
60°	288.0	290.0	293.9	307.6	321.1	332.8	338.7	363.9	381.5	393.2	400.9
62.5°	212.2	216.1	220.0	231.6	245.2	255.0	264.7	286.1	301.7	313.4	321.1
65°	147.9	149.8	155.7	161.5	175.2	184.9	192.7	210.2	225.8	235.5	241.3
67.5°	91.5	93.4	97.3	105.1	114.8	122.6	130.4	142.1	155.7	165.4	167.4
70°	46.7	48.7	50.6	56.5	64.2	68.1	73.9	83.7	93.4	101.2	105.1
72.5°	15.6	15.6	17.5	21.4	25.3	29.2	31.1	40.9	48.7	52.6	54.5
75°	3.9	3.9	3.9	3.9	3.9	5.9	5.9	11.7	15.6	19.5	21.4
77.5°	2.0	2.0	2.0	2.0	2.0	2.0	2.0	2.0	2.0	3.9	3.9
80°	2.0	2.0	2.0	2.0	2.0	2.0	2.0	2.0	2.0	2.0	2.0
82.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P#
 CATALOG NUMBER: FLDSQ4C30D010 FEU4C309040 F4LC-CSSQ-MW

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°
0°	1370.2	1370.2	1370.2	1370.2	1370.2	1370.2	1370.2	1370.2	1370.2	1370.2
2.5°	1370.2	1366.3	1364.3	1366.3	1366.3	1364.3	1370.2	1378.0	1387.7	1362.4
5°	1368.2	1364.3	1368.2	1356.6	1362.4	1358.5	1366.3	1364.3	1372.1	1364.3
7.5°	1362.4	1354.7	1356.6	1350.8	1358.5	1348.8	1354.7	1366.3	1358.5	1346.9
10°	1343.0	1339.1	1352.7	1333.2	1329.3	1337.1	1352.7	1341.0	1337.1	1341.0
12.5°	1323.4	1323.4	1329.3	1313.8	1315.7	1319.6	1327.3	1319.6	1323.4	1333.2
15°	1302.1	1298.2	1307.9	1296.2	1294.3	1290.4	1298.2	1298.2	1302.1	1296.2
17.5°	1276.8	1271.0	1271.0	1267.1	1265.1	1274.8	1278.7	1280.6	1282.6	1274.8
20°	1245.6	1243.7	1249.5	1243.7	1245.6	1247.6	1247.6	1243.7	1261.2	1239.8
22.5°	1212.5	1218.4	1210.6	1206.7	1210.6	1214.5	1214.5	1216.4	1212.5	1208.6
25°	1179.5	1183.4	1185.3	1173.6	1179.5	1173.6	1187.3	1189.2	1181.4	1185.3
27.5°	1150.3	1144.5	1142.5	1134.7	1138.6	1136.7	1138.6	1138.6	1150.3	1134.7
30°	1105.5	1099.7	1101.6	1095.8	1097.7	1095.8	1097.7	1097.7	1105.5	1103.6
32.5°	1062.7	1056.9	1058.8	1053.0	1053.0	1054.9	1051.0	1051.0	1056.9	1053.0
35°	1021.8	1008.2	1010.1	1008.2	1010.1	1002.3	1002.3	1000.4	1004.3	994.5
37.5°	963.4	957.6	955.6	953.7	955.6	951.7	955.6	949.8	955.6	947.8
40°	910.8	906.9	908.9	897.3	897.3	899.2	895.3	893.4	895.3	903.1
42.5°	858.3	850.6	846.7	842.8	844.7	838.9	836.9	833.0	836.9	829.1
45°	796.0	796.0	794.1	784.3	786.3	786.3	778.5	770.8	772.7	772.7
47.5°	739.6	735.7	733.7	724.1	722.1	720.2	712.3	706.5	706.5	700.6
50°	677.3	673.4	667.6	657.8	653.9	642.3	636.5	628.7	620.9	620.9
52.5°	618.9	605.3	597.5	581.9	576.1	570.2	554.7	548.9	543.0	537.2
55°	548.9	537.2	521.6	504.1	496.3	486.5	471.0	459.3	451.5	453.5
57.5°	480.7	461.3	445.7	422.4	412.6	406.7	391.2	375.6	367.8	367.8
60°	397.0	381.5	362.0	340.6	332.8	323.1	303.6	293.9	288.0	282.2
62.5°	317.2	305.6	288.0	260.8	255.0	245.2	231.6	220.0	214.1	214.1
65°	237.4	225.8	210.2	190.7	183.0	175.2	163.5	151.8	146.0	144.0
67.5°	167.4	153.7	140.2	124.6	118.7	114.8	103.2	95.4	91.5	89.5
70°	101.2	93.4	83.7	72.0	66.1	62.3	54.5	48.7	46.7	44.8
72.5°	52.6	46.7	38.9	31.1	27.2	23.3	19.5	15.6	13.7	13.7
75°	19.5	15.6	9.8	5.9	3.9	3.9	3.9	3.9	3.9	3.9
77.5°	3.9	2.0	2.0	2.0	2.0	2.0	2.0	2.0	2.0	2.0
80°	2.0	2.0	2.0	2.0	2.0	2.0	2.0	2.0	2.0	2.0
82.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)