

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P574678

Luminaire Tested: **FLD6C-08-D010 FEU6C-X-90-50 F6X-N-X-LI**

Issue Date: 3/1/2023



**Test Information**

Test Method: LM-79-08  
Report Number: P574678  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P205310)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/1/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: FAIL-SAFE  
Catalog Number: FLD6C-08-D010 FEU6C-X-90-50 F6X-N-X-LI  
Description: 6 INCH FAIL-SAFE LED DOWNLIGHT WITH 5000K, 90 CRI LEDS, 6LBNLI TRIM

Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 741.1 lumens  
Efficiency: N/A  
Efficacy: 75.1 lumens/watt  
Spacing Criteria (0/90/45): 0.53 / 0.53 / 0.58  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct

Input Watts (W): 9.87  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P574678

CATALOG NUMBER: FLD6C-08-D010 FEU6C-X-90-50 F6X-N-X-LI

### Luminous Intensity Polar Plot





TEST NUMBER: P574678

CATALOG NUMBER: FLD6C-08-D010 FEU6C-X-90-50 F6X-N-X-LI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	114	112	109	107	112	109	107	106	105	104	102	102	101	99	98	97	96	95		
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	93	91	89		
3	105	99	94	91	103	97	93	90	95	91	89	93	90	87	90	88	86	85		
4	100	93	88	85	98	92	88	84	90	86	83	88	85	82	86	84	81	80		
5	96	88	83	79	94	87	83	79	86	82	78	84	81	78	83	80	77	76		
6	92	84	79	75	90	83	78	75	82	77	74	80	76	74	79	76	73	72		
7	88	80	74	71	87	79	74	71	78	73	70	77	73	70	76	72	69	68		
8	84	76	71	67	83	75	70	67	74	70	67	73	69	66	73	69	66	65		
9	81	73	67	64	80	72	67	64	71	67	63	70	66	63	70	66	63	62		
10	78	69	64	61	77	69	64	61	68	64	61	67	63	60	67	63	60	59		

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	92487
5°	86490
10°	70540
15°	51907
20°	35779
25°	26560
30°	19952
35°	12441
40°	6040
45°	2070
50°	273
55°	210
60°	121
65°	143
70°	176
75°	0
80°	0
85°	0



TEST NUMBER: P574678

CATALOG NUMBER: FLD6C-08-D010 FEU6C-X-90-50 F6X-N-X-LI

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	140.3	18.9
10°-20°	251.8	34.0
20°-30°	203.6	27.5
30°-40°	117.3	15.8
40°-50°	24.8	3.3
50°-60°	2.2	0.3
60°-70°	1.1	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	595.6	80.4
0°-40°	712.9	96.2
0°-60°	739.8	99.8
0°-90°	741.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	741.1	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1687	
5°	1572	140
15°	915	252
25°	439	204
35°	186	117
45°	27	25
55°	2	2
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P574678

CATALOG NUMBER: FLD6C-08-D010 FEU6C-X-90-50 F6X-N-X-LI

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	1687.1
2.5°	1666.8
5°	1571.7
7.5°	1434.9
10°	1267.2
12.5°	1095.2
15°	914.6
17.5°	740.4
20°	613.3
22.5°	516.1
25°	439.1
27.5°	374.0
30°	315.2
32.5°	250.0
35°	185.9
37.5°	129.3
40°	84.4
42.5°	51.3
45°	26.7
47.5°	10.7
50°	3.2
52.5°	3.2
55°	2.2
57.5°	2.2
60°	1.1
62.5°	1.1
65°	1.1
67.5°	1.1
70°	1.1
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-MV3F9LC







— 0°-180°







(END OF REPORT)