

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P579628

Luminaire Tested: **FLD6C-80-D010 FEU6C-X-90-35 F6X-M-X-H**

Issue Date: 3/1/2023



**Test Information**

Test Method: LM-79-08  
Report Number: P579628  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P203254)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/1/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: FAIL-SAFE  
Catalog Number: FLD6C-80-D010 FEU6C-X-90-35 F6X-M-X-H  
Description: 6 INCH FAIL-SAFE LED DOWNLIGHT WITH 3500K, 90 CRI LEDS, 6LBMH TRIM

Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 6742.0 lumens  
Efficiency: N/A  
Efficacy: 75.3 lumens/watt  
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.93  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct

Input Watts (W): 89.5  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P579628

CATALOG NUMBER: FLD6C-80-D010 FEU6C-X-90-35 F6X-M-X-H

### Luminous Intensity Polar Plot





TEST NUMBER: P579628

CATALOG NUMBER: FLD6C-80-D010 FEU6C-X-90-35 F6X-M-X-H

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	92				92
2	107	102	97	93	105	100	96	92	97	93	90	94	91	88	91	89	87	85				85
3	101	94	88	84	99	92	87	84	90	86	82	87	84	81	85	82	80	78				78
4	95	87	81	76	93	86	80	76	84	79	75	82	78	74	80	76	73	72				72
5	90	81	75	70	88	80	74	70	78	73	69	76	72	68	75	71	68	66				66
6	85	75	69	64	83	75	69	64	73	68	64	72	67	63	70	66	63	61				61
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57				57
8	76	66	60	55	75	65	59	55	64	59	55	63	58	55	62	58	54	53				53
9	72	62	56	51	71	61	55	51	60	55	51	60	55	51	59	54	51	49				49
10	69	58	52	48	68	58	52	48	57	52	48	56	51	48	55	51	48	46				46

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	365777
5°	359222
10°	340870
15°	319650
20°	297689
25°	274292
30°	228548
35°	161084
40°	102657
45°	61223
50°	36135
55°	22986
60°	15832
65°	11233
70°	7742
75°	6121
80°	2999
85°	0



TEST NUMBER: P579628

CATALOG NUMBER: FLD6C-80-D010 FEU6C-X-90-35 F6X-M-X-H

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	610.1	9.0
10°-20°	1578.2	23.4
20°-30°	2044.9	30.3
30°-40°	1518.2	22.5
40°-50°	640.9	9.5
50°-60°	227.5	3.4
60°-70°	87.8	1.3
70°-80°	30.4	0.5
80°-90°	3.9	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4233.2	62.8
0°-40°	5751.4	85.3
0°-60°	6619.9	98.2
0°-90°	6742.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6742.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	6672	
5°	6528	610
15°	5632	1578
25°	4535	2045
35°	2407	1518
45°	790	641
55°	240	228
65°	87	88
75°	29	30
85°	0	4
90°	0	



TEST NUMBER: P579628

CATALOG NUMBER: FLD6C-80-D010 FEU6C-X-90-35 F6X-M-X-H

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	6672.3
2.5°	6652.9
5°	6527.8
7.5°	6344.7
10°	6123.5
12.5°	5882.6
15°	5632.2
17.5°	5353.2
20°	5102.8
22.5°	4842.9
25°	4534.7
27.5°	4111.0
30°	3610.5
32.5°	3023.0
35°	2407.0
37.5°	1887.1
40°	1434.5
42.5°	1068.6
45°	789.7
47.5°	577.6
50°	423.7
52.5°	317.7
55°	240.5
57.5°	182.8
60°	144.4
62.5°	106.0
65°	86.6
67.5°	67.3
70°	48.3
72.5°	38.4
75°	28.9
77.5°	19.4
80°	9.5
82.5°	9.5
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-MV3F9LC







— 0°-180°







(END OF REPORT)