

LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P#

Luminaire Tested: **FLDSQ4C40D010 FEU4C409050 F4LC-CSSQ-MW**

Issue Date: 12/13/2022

Tested By:

Approved By:



Cooper Lighting Solutions laboratories have been accredited by National Voluntary Laboratory Accreditation Program (NVLAP) that it adheres to the requirements of ISO/IEC 17025:2005 and appropriate IESNA test methods. This report must not be used to claim product certification, approval or endorsement by NVLAP, NIST or any agency of the Federal Government. Results contained in this report are valid for luminaire sample tested, as supplied by requestor. Information related to the luminaire tested has been supplied by requestor and can affect the validity of the test results. Report shall not be reproduced except in full without approval of Cooper Lighting Solutions Lighting Laboratory. Test performed at address noted above.

Test Information

Test Method: LM-79-08
 Report Number: P#
 Test Lab: INNOVATION CENTER
 Issue Date: 12/13/2022
 Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
 Product Line: FAIL-SAFE
 Catalog Number: FLDSQ4C40D010 FEU4C409050 F4LC-CSSQ-MW
 Description: 4 INCH 4000 LUMEN FAIL-SAFE LED DOWNLIGHT WITH, 5000K, 90CRI LEDS AND F4LC-CSSQ TRIM WITH MW FINISH
 Light Source: -
 Ballast/Driver: -

Summary


Lumens per Lamp: N/A
 Luminaire Lumens: 4093.0 lumens
 Efficiency: N/A
 Efficacy: 87.1 lumens/watt
 Spacing Criteria (0/90/45): 1.19 / 1.2 / 1.29
 Luminous Opening: Rectangular (W 0.33' x L: 0.33' x H: 0')
 CIE Type: Direct

Input Watts (W): 47
 Input Voltage (V):
 Input Current (Ain): NR
 Voltage Rise (V): NR
 Power Factor: NR
 Total Harmonic Distortion (THDi): NR
 Frequency (hertz): 60
 Stabilization Time: NR
 Operation Time: NR
 Ambient Temperature (°C): NR
 Test Distance: 25 FT

Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	GONIO 1 IN0055	4/22/2021	10/22/2021
Power Meter	XITRON 2801 IN0197	12/1/2020	12/1/2021
AC Power Source	CHROMA 61505 IN0196	12/1/2020	12/1/2021
DC Power Supply	AGILENT E3634A IN0198	11/30/2020	11/30/2021
Room Thermometer	ONSET IN0143	12/1/2020	12/1/2021

TEST NUMBER: P#
CATALOG NUMBER: FLDSQ4C40D010 FEU4C409050 F4LC-CSSQ-MW

Luminous Intensity Polar Plot



TEST NUMBER: P#

CATALOG NUMBER: FLDSQ4C40D010 FEU4C409050 F4LC-CSSQ-MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	111	108	104	101	109	105	102	100	101	99	96		97	95	94		94	92	91	89
2	103	96	91	86	100	94	89	85	91	87	83		88	84	81		85	82	79	77
3	95	86	79	74	93	85	78	73	82	76	72		79	74	71		77	73	69	67
4	88	77	70	64	86	76	69	63	74	67	63		71	66	62		69	65	61	59
5	81	70	62	56	79	69	61	56	67	60	55		65	59	54		63	58	54	52
6	75	63	55	49	73	62	55	49	61	54	49		59	53	48		57	52	48	46
7	70	58	50	44	68	57	49	44	55	49	44		54	48	43		53	47	43	41
8	65	53	45	40	64	52	45	39	51	44	39		50	44	39		49	43	39	37
9	61	49	41	36	60	48	41	36	47	40	36		46	40	35		45	39	35	33
10	57	45	38	33	56	44	37	33	44	37	32		43	37	32		42	36	32	31

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	184882	184882	184882
5°	181898	184262	184785
10°	183463	182934	183727
15°	180256	180516	181065
20°	176057	178850	178019
25°	175303	175303	176453
30°	170410	171625	171937
35°	165096	166710	163812
40°	157346	160432	159059
45°	148914	152271	147441
50°	131151	142590	130326
55°	106216	130474	106687
60°	77731	108203	76149
65°	47238	77055	45982
70°	18422	41471	17660
75°	2013	11184	2013
80°	1556	1556	1556
85°	0	0	0

TEST NUMBER: P#
 CATALOG NUMBER: FLDSQ4C40D010 FEU4C409050 F4LC-CSSQ-MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	180.9	4.4
10°-20°	511.8	12.5
20°-30°	759.4	18.6
30°-40°	879.9	21.5
40°-50°	843.6	20.6
50°-60°	620.3	15.2
60°-70°	267.9	6.5
70°-80°	28.9	0.7
80°-90°	0.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1452.0	35.5
0°-40°	2331.9	57.0
0°-60°	3795.8	92.7
0°-90°	4093.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4093.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1916	1916	1916	1916	1916	
5°	1878	1897	1902	1905	1908	179
15°	1804	1815	1807	1810	1813	509
25°	1647	1644	1647	1649	1657	754
35°	1402	1410	1415	1412	1391	876
45°	1091	1094	1116	1100	1080	830
55°	631	697	776	694	634	568
65°	207	258	338	256	201	213
75°	5	8	30	5	5	17
85°	0	0	0	0	0	0
90°	0	0	0	0	0	

TEST NUMBER: P#
 CATALOG NUMBER: FLDSQ4C40D010 FEU4C409050 F4LC-CSSQ-MW

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1916.1	1916.1	1916.1	1916.1	1916.1	1916.1	1916.1	1916.1	1916.1	1916.1	1916.1
2.5°	1902.4	1924.2	1926.9	1913.3	1907.8	1899.7	1918.7	1905.2	1910.6	1905.2	1902.4
5°	1878.0	1902.4	1905.2	1905.2	1899.7	1897.0	1905.2	1902.4	1899.7	1894.3	1902.4
7.5°	1867.1	1880.6	1894.3	1878.0	1886.1	1883.4	1902.4	1894.3	1891.5	1891.5	1886.1
10°	1872.5	1869.8	1880.6	1864.3	1869.8	1864.3	1880.6	1880.6	1875.2	1869.8	1867.1
12.5°	1828.9	1850.7	1850.7	1848.0	1842.5	1834.3	1850.7	1861.6	1845.2	1845.2	1842.5
15°	1804.5	1809.9	1812.6	1812.6	1809.9	1815.3	1823.5	1812.6	1815.3	1801.7	1807.1
17.5°	1777.3	1766.4	1774.5	1769.0	1771.8	1777.3	1788.1	1788.1	1771.8	1769.0	1774.5
20°	1714.6	1747.3	1750.0	1733.7	1736.4	1736.4	1755.5	1739.2	1750.0	1736.4	1741.8
22.5°	1684.6	1706.4	1709.2	1687.4	1701.0	1684.6	1703.7	1679.2	1706.4	1687.4	1695.5
25°	1646.6	1643.9	1652.0	1641.1	1643.9	1643.9	1657.4	1646.6	1654.8	1643.9	1646.6
27.5°	1584.0	1605.8	1603.0	1592.1	1597.6	1594.9	1622.1	1592.1	1608.5	1594.9	1600.4
30°	1529.5	1548.6	1543.2	1532.3	1532.3	1524.1	1554.1	1545.8	1543.2	1543.2	1540.4
32.5°	1475.1	1477.9	1472.4	1475.1	1477.9	1467.0	1491.4	1480.5	1477.9	1480.5	1483.3
35°	1401.6	1401.6	1407.0	1398.9	1409.8	1409.8	1431.6	1417.9	1415.3	1407.0	1415.3
37.5°	1336.3	1328.2	1330.9	1330.9	1336.3	1341.7	1352.6	1347.2	1347.2	1339.1	1344.5
40°	1249.2	1243.8	1251.9	1251.9	1260.1	1260.1	1271.0	1265.6	1273.7	1273.7	1273.7
42.5°	1173.1	1173.1	1167.6	1175.7	1178.5	1175.7	1194.8	1192.1	1194.8	1189.4	1192.1
45°	1091.3	1091.3	1085.9	1083.2	1096.8	1094.1	1115.9	1107.7	1118.5	1113.1	1115.9
47.5°	979.7	993.4	985.2	993.4	1009.7	1012.5	1026.0	1020.6	1031.5	1023.4	1034.3
50°	873.7	873.7	881.8	892.7	909.0	911.8	928.1	939.0	944.4	947.1	949.9
52.5°	762.1	759.3	767.5	781.1	794.7	805.6	821.9	838.3	849.2	865.5	857.3
55°	631.4	636.8	645.1	661.4	683.1	696.7	710.3	732.1	751.2	759.3	775.6
57.5°	519.8	514.4	519.8	541.6	566.1	577.0	596.1	617.8	645.1	661.4	666.8
60°	402.8	405.5	411.0	430.1	449.1	465.4	473.6	508.9	533.5	549.8	560.7
62.5°	296.7	302.1	307.6	323.9	342.9	356.6	370.1	400.1	421.9	438.2	449.1
65°	206.9	209.5	217.8	225.9	245.0	258.5	269.4	293.9	315.7	329.4	337.5
67.5°	127.9	130.6	136.0	147.0	160.6	171.5	182.3	198.7	217.8	231.3	234.1
70°	65.3	68.1	70.7	79.0	89.8	95.3	103.4	117.0	130.6	141.5	147.0
72.5°	21.8	21.8	24.5	30.0	35.4	40.9	43.5	57.2	68.1	73.5	76.2
75°	5.4	5.4	5.4	5.4	5.4	8.2	8.2	16.3	21.8	27.2	30.0
77.5°	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.8	5.4	5.4
80°	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.8
82.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P#
 CATALOG NUMBER: FLDSQ4C40D010 FEU4C409050 F4LC-CSSQ-MW

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°
0°	1916.1	1916.1	1916.1	1916.1	1916.1	1916.1	1916.1	1916.1	1916.1	1916.1
2.5°	1916.1	1910.6	1907.8	1910.6	1910.6	1907.8	1916.1	1926.9	1940.5	1905.2
5°	1913.3	1907.8	1913.3	1897.0	1905.2	1899.7	1910.6	1907.8	1918.7	1907.8
7.5°	1905.2	1894.3	1897.0	1888.9	1899.7	1886.1	1894.3	1910.6	1899.7	1883.4
10°	1878.0	1872.5	1891.5	1864.3	1858.9	1869.8	1891.5	1875.2	1869.8	1875.2
12.5°	1850.7	1850.7	1858.9	1837.1	1839.8	1845.2	1856.1	1845.2	1850.7	1864.3
15°	1820.8	1815.3	1828.9	1812.6	1809.9	1804.5	1815.3	1815.3	1820.8	1812.6
17.5°	1785.4	1777.3	1777.3	1771.8	1769.0	1782.7	1788.1	1790.8	1793.6	1782.7
20°	1741.8	1739.2	1747.3	1739.2	1741.8	1744.6	1744.6	1739.2	1763.6	1733.7
22.5°	1695.5	1703.7	1692.9	1687.4	1692.9	1698.3	1698.3	1701.0	1695.5	1690.1
25°	1649.3	1654.8	1657.4	1641.1	1649.3	1641.1	1660.2	1662.9	1652.0	1657.4
27.5°	1608.5	1600.4	1597.6	1586.7	1592.1	1589.5	1592.1	1592.1	1608.5	1586.7
30°	1545.8	1537.7	1540.4	1532.3	1535.0	1532.3	1535.0	1535.0	1545.8	1543.2
32.5°	1486.0	1477.9	1480.5	1472.4	1472.4	1475.1	1469.7	1469.7	1477.9	1472.4
35°	1428.8	1409.8	1412.5	1409.8	1412.5	1401.6	1401.6	1398.9	1404.4	1390.7
37.5°	1347.2	1339.1	1336.3	1333.6	1336.3	1330.9	1336.3	1328.2	1336.3	1325.4
40°	1273.7	1268.2	1271.0	1254.7	1254.7	1257.4	1251.9	1249.2	1251.9	1262.8
42.5°	1200.3	1189.4	1183.9	1178.5	1181.2	1173.1	1170.3	1164.8	1170.3	1159.4
45°	1113.1	1113.1	1110.4	1096.8	1099.6	1099.6	1088.7	1077.8	1080.5	1080.5
47.5°	1034.3	1028.8	1026.0	1012.5	1009.7	1007.1	996.1	988.0	988.0	979.7
50°	947.1	941.7	933.5	919.9	914.4	898.1	890.0	879.1	868.2	868.2
52.5°	865.5	846.4	835.5	813.7	805.6	797.4	775.6	767.5	759.3	751.2
55°	767.5	751.2	729.4	704.9	694.0	680.4	658.6	642.3	631.4	634.2
57.5°	672.3	645.1	623.3	590.6	577.0	568.8	547.0	525.2	514.4	514.4
60°	555.2	533.5	506.2	476.3	465.4	451.8	424.5	411.0	402.8	394.6
62.5°	443.6	427.3	402.8	364.7	356.6	342.9	323.9	307.6	299.4	299.4
65°	332.0	315.7	293.9	266.7	255.8	245.0	228.6	212.3	204.1	201.4
67.5°	234.1	215.0	196.0	174.2	166.0	160.6	144.2	133.4	127.9	125.1
70°	141.5	130.6	117.0	100.7	92.5	87.1	76.2	68.1	65.3	62.6
72.5°	73.5	65.3	54.4	43.5	38.1	32.6	27.2	21.8	19.1	19.1
75°	27.2	21.8	13.7	8.2	5.4	5.4	5.4	5.4	5.4	5.4
77.5°	5.4	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.8
80°	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.8
82.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)