

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P579788

Luminaire Tested: **FLD6C-80-D010 FEU6C-X-90-50 F6X-W-X-H**

Issue Date: 3/1/2023



**Test Information**

Test Method: LM-79-08  
Report Number: P579788  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P202739)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/1/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: FAIL-SAFE  
Catalog Number: FLD6C-80-D010 FEU6C-X-90-50 F6X-W-X-H  
Description: 6 INCH FAIL-SAFE LED DOWNLIGHT WITH 5000K, 90 CRI LEDS, 6LBWH TRIM

Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 8338.9 lumens  
Efficiency: N/A  
Efficacy: 93.2 lumens/watt  
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.16  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct

Input Watts (W): 89.5  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P579788

CATALOG NUMBER: FLD6C-80-D010 FEU6C-X-90-50 F6X-W-X-H

### Luminous Intensity Polar Plot





TEST NUMBER: P579788

CATALOG NUMBER: FLD6C-80-D010 FEU6C-X-90-50 F6X-W-X-H

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	112	109	106	103	110	107	104	101	103	100	98	99	97	95	95	94	93	91			
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	85	83	81			
3	98	90	84	79	96	89	83	78	86	81	77	83	79	76	81	78	75	73			
4	92	82	75	70	90	81	75	70	79	73	69	77	72	68	75	71	67	65			
5	86	75	68	63	84	74	68	63	72	66	62	71	65	61	69	64	61	59			
6	80	69	62	57	78	68	61	56	67	61	56	65	60	56	64	59	55	53			
7	75	64	56	51	73	63	56	51	62	55	51	60	55	51	59	54	50	49			
8	70	59	52	47	69	58	51	47	57	51	46	56	50	46	55	50	46	44			
9	66	55	48	43	65	54	47	43	53	47	43	52	47	42	51	46	42	41			
10	62	51	44	40	61	50	44	39	50	43	39	49	43	39	48	43	39	38			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	281951
5°	281850
10°	279682
15°	277811
20°	273578
25°	267324
30°	251703
35°	227793
40°	190214
45°	145752
50°	103220
55°	65078
60°	36708
65°	23829
70°	15564
75°	11438
80°	6882
85°	6856



TEST NUMBER: P579788

CATALOG NUMBER: FLD6C-80-D010 FEU6C-X-90-50 F6X-W-X-H

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	485.8	5.8
10°-20°	1378.4	16.5
20°-30°	2021.0	24.2
30°-40°	2103.4	25.2
40°-50°	1455.2	17.5
50°-60°	633.6	7.6
60°-70°	194.3	2.3
70°-80°	58.2	0.7
80°-90°	8.9	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3885.2	46.6
0°-40°	5988.6	71.8
0°-60°	8077.5	96.9
0°-90°	8338.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	8338.9	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	5143	
5°	5122	486
15°	4895	1378
25°	4420	2021
35°	3404	2103
45°	1880	1455
55°	681	634
65°	184	194
75°	54	58
85°	11	9
90°	0	



TEST NUMBER: P579788

CATALOG NUMBER: FLD6C-80-D010 FEU6C-X-90-50 F6X-W-X-H

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	5143.2
2.5°	5154.1
5°	5121.8
7.5°	5078.7
10°	5024.3
12.5°	4970.3
15°	4895.0
17.5°	4797.5
20°	4689.5
22.5°	4570.6
25°	4419.5
27.5°	4224.9
30°	3976.3
32.5°	3716.9
35°	3403.8
37.5°	3058.1
40°	2658.0
42.5°	2258.3
45°	1880.0
47.5°	1523.4
50°	1210.3
52.5°	918.6
55°	680.9
57.5°	486.3
60°	334.8
62.5°	248.6
65°	183.7
67.5°	140.6
70°	97.1
72.5°	75.7
75°	54.0
77.5°	32.2
80°	21.8
82.5°	10.9
85°	10.9
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-MV3F9LC







— 0°-180°







(END OF REPORT)