

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P579808

Luminaire Tested: **FLD6C-90-D010 FEU6C-X-90-27 F6X-M-X-H**

Issue Date: 3/1/2023



Test Information

Test Method: LM-79-08
Report Number: P579808
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P203254)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/1/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD6C-90-D010 FEU6C-X-90-27 F6X-M-X-H
Description: 6 INCH FAIL-SAFE LED DOWNLIGHT WITH 2700K, 90 CRI LEDS, 6LBMH TRIM

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6811.0 lumens
Efficiency: N/A
Efficacy: 70.1 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.93
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 97.1
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P579808

CATALOG NUMBER: FLD6C-90-D010 FEU6C-X-90-27 F6X-M-X-H

Luminous Intensity Polar Plot





TEST NUMBER: P579808

CATALOG NUMBER: FLD6C-90-D010 FEU6C-X-90-27 F6X-M-X-H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	92																			
2	107	102	97	93	105	100	96	92	97	93	90	94	91	88	91	89	87	85																			
3	101	94	88	84	99	92	87	84	90	86	82	87	84	81	85	82	80	78																			
4	95	87	81	76	93	86	80	76	84	79	75	82	78	74	80	76	73	72																			
5	90	81	75	70	88	80	74	70	78	73	69	76	72	68	75	71	68	66																			
6	85	75	69	64	83	75	69	64	73	68	64	72	67	63	70	66	63	61																			
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57																			
8	76	66	60	55	75	65	59	55	64	59	55	63	58	55	62	58	54	53																			
9	72	62	56	51	71	61	55	51	60	55	51	60	55	51	59	54	51	49																			
10	69	58	52	48	68	58	52	48	57	52	48	56	51	48	55	51	48	46																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	369515
5°	362904
10°	344360
15°	322919
20°	300734
25°	277099
30°	230884
35°	162730
40°	103709
45°	61844
50°	36511
55°	23225
60°	15997
65°	11350
70°	7822
75°	6185
80°	3031
85°	0



TEST NUMBER: P579808

CATALOG NUMBER: FLD6C-90-D010 FEU6C-X-90-27 F6X-M-X-H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	616.3	9.0
10°-20°	1594.4	23.4
20°-30°	2065.9	30.3
30°-40°	1533.7	22.5
40°-50°	647.5	9.5
50°-60°	229.9	3.4
60°-70°	88.8	1.3
70°-80°	30.7	0.5
80°-90°	3.9	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4276.5	62.8
0°-40°	5810.3	85.3
0°-60°	6687.6	98.2
0°-90°	6811.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6811.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	6740	
5°	6595	616
15°	5690	1594
25°	4581	2066
35°	2432	1534
45°	798	647
55°	243	230
65°	88	89
75°	29	31
85°	0	4
90°	0	



TEST NUMBER: P579808

CATALOG NUMBER: FLD6C-90-D010 FEU6C-X-90-27 F6X-M-X-H

CANDELA DISTRIBUTION (FULL):

	0°
0°	6740.5
2.5°	6721.0
5°	6594.7
7.5°	6409.6
10°	6186.2
12.5°	5942.8
15°	5689.8
17.5°	5408.0
20°	5155.0
22.5°	4892.4
25°	4581.1
27.5°	4153.0
30°	3647.4
32.5°	3053.9
35°	2431.6
37.5°	1906.5
40°	1449.2
42.5°	1079.5
45°	797.7
47.5°	583.5
50°	428.1
52.5°	320.9
55°	243.0
57.5°	184.7
60°	145.9
62.5°	107.1
65°	87.5
67.5°	68.0
70°	48.8
72.5°	38.8
75°	29.2
77.5°	19.6
80°	9.6
82.5°	9.6
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-MV3F9LC





— 0°-180°







(END OF REPORT)