

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P579818

Luminaire Tested: **FLD6C-90-D010 FEU6C-X-90-27 F6X-M-X-LI**

Issue Date: 3/1/2023



Test Information

Test Method: LM-79-08
Report Number: P579818
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P205108)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/1/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD6C-90-D010 FEU6C-X-90-27 F6X-M-X-LI
Description: 6 INCH FAIL-SAFE LED DOWNLIGHT WITH 2700K, 90 CRI LEDS, 6LBMLI TRIM

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8336.0 lumens
Efficiency: N/A
Efficacy: 85.8 lumens/watt
Spacing Criteria (0/90/45): 0.85 / 0.85 / 0.85
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 97.1
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P579818

CATALOG NUMBER: FLD6C-90-D010 FEU6C-X-90-27 F6X-M-X-LI

Luminous Intensity Polar Plot





TEST NUMBER: P579818

CATALOG NUMBER: FLD6C-90-D010 FEU6C-X-90-27 F6X-M-X-LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	111	109	106	111	109	107	105	105	103	101	101	100	98	98	97	96	94
2	108	103	100	96	106	102	98	95	99	96	93	96	93	91	93	91	89	88
3	103	97	92	88	101	95	91	87	93	89	86	90	87	85	88	85	83	82
4	98	91	85	81	96	89	84	81	87	83	80	85	82	79	83	80	78	76
5	93	85	79	75	91	84	79	75	82	78	74	81	77	73	79	76	73	71
6	89	80	74	70	87	79	74	70	78	73	69	76	72	69	75	71	68	67
7	84	75	69	65	83	75	69	65	73	68	65	72	68	64	71	67	64	63
8	80	71	65	61	79	70	65	61	69	64	61	68	64	60	67	63	60	59
9	77	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55
10	73	64	58	54	72	63	58	54	62	57	54	62	57	54	61	57	54	52

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	571889
5°	566447
10°	536764
15°	487330
20°	430625
25°	372294
30°	291013
35°	178464
40°	91600
45°	36391
50°	11821
55°	4072
60°	3498
65°	2789
70°	1715
75°	2266
80°	0
85°	0



TEST NUMBER: P579818

CATALOG NUMBER: FLD6C-90-D010 FEU6C-X-90-27 F6X-M-X-LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	961.0	11.5
10°-20°	2392.6	28.7
20°-30°	2781.3	33.4
30°-40°	1703.2	20.4
40°-50°	422.9	5.1
50°-60°	49.4	0.6
60°-70°	18.5	0.2
70°-80°	7.0	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	6134.9	73.6
0°-40°	7838.1	94.0
0°-60°	8310.5	99.7
0°-90°	8336.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	8336.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	10432	
5°	10294	961
15°	8587	2393
25°	6155	2781
35°	2667	1703
45°	469	423
55°	43	49
65°	22	18
75°	11	7
85°	0	0
90°	0	



TEST NUMBER: P579818

CATALOG NUMBER: FLD6C-90-D010 FEU6C-X-90-27 F6X-M-X-LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	10432.1
2.5°	10421.4
5°	10293.5
7.5°	10016.0
10°	9642.6
12.5°	9152.1
15°	8586.7
17.5°	7978.8
20°	7381.5
22.5°	6783.9
25°	6154.9
27.5°	5429.5
30°	4597.3
32.5°	3626.7
35°	2666.7
37.5°	1877.2
40°	1280.0
42.5°	799.9
45°	469.4
47.5°	266.8
50°	138.6
52.5°	64.1
55°	42.6
57.5°	31.9
60°	31.9
62.5°	21.5
65°	21.5
67.5°	10.7
70°	10.7
72.5°	10.7
75°	10.7
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-MV3F9LC





— 0°-180°







(END OF REPORT)