

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P579888

Luminaire Tested: **FLD6C-90-D010 FEU6C-X-90-30 F6X-N-X-H**

Issue Date: 3/1/2023



**Test Information**

Test Method: LM-79-08  
Report Number: P579888  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P203666)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/1/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: FAIL-SAFE  
Catalog Number: FLD6C-90-D010 FEU6C-X-90-30 F6X-N-X-H  
Description: 6 INCH FAIL-SAFE LED DOWNLIGHT WITH 3000K, 90 CRI LEDS, 6LBNH TRIM

Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 6092.0 lumens  
Efficiency: N/A  
Efficacy: 62.7 lumens/watt  
Spacing Criteria (0/90/45): 0.78 / 0.78 / 0.84  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct

Input Watts (W): 97.1  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P579888

CATALOG NUMBER: FLD6C-90-D010 FEU6C-X-90-30 F6X-N-X-H

### Luminous Intensity Polar Plot





TEST NUMBER: P579888

CATALOG NUMBER: FLD6C-90-D010 FEU6C-X-90-30 F6X-N-X-H

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	111	108	106	111	109	106	104	104	103	101	101	99	98	97	96	95	93			
2	108	103	99	96	106	101	98	94	98	95	92	95	93	90	92	90	89	87			
3	102	96	91	87	100	95	90	86	92	88	85	90	86	84	87	85	82	81			
4	97	90	84	80	95	89	83	79	86	82	78	84	81	78	83	79	77	75			
5	92	84	78	74	91	83	78	73	81	76	73	80	75	72	78	74	72	70			
6	88	79	73	69	86	78	72	68	77	72	68	75	71	67	74	70	67	65			
7	83	74	68	64	82	73	68	64	72	67	63	71	66	63	70	66	63	61			
8	79	70	64	60	78	69	64	60	68	63	59	67	63	59	66	62	59	58			
9	76	66	60	56	75	66	60	56	65	59	56	64	59	56	63	59	55	54			
10	72	62	57	53	71	62	57	53	61	56	53	60	56	52	60	55	52	51			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	428107
5°	417515
10°	385247
15°	341075
20°	296149
25°	253309
30°	208836
35°	137527
40°	73931
45°	32732
50°	13270
55°	9577
60°	6085
65°	4345
70°	3574
75°	2372
80°	3536
85°	0



TEST NUMBER: P579888

CATALOG NUMBER: FLD6C-90-D010 FEU6C-X-90-30 F6X-N-X-H

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	702.3	11.5
10°-20°	1674.7	27.5
20°-30°	1918.5	31.5
30°-40°	1289.0	21.2
40°-50°	368.3	6.0
50°-60°	90.2	1.5
60°-70°	34.3	0.6
70°-80°	13.3	0.2
80°-90°	1.5	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4295.5	70.5
0°-40°	5584.5	91.7
0°-60°	6043.0	99.2
0°-90°	6092.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6092.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	7809	
5°	7587	702
15°	6010	1675
25°	4188	1919
35°	2055	1289
45°	422	368
55°	100	90
65°	34	34
75°	11	13
85°	0	2
90°	0	



TEST NUMBER: P579888

CATALOG NUMBER: FLD6C-90-D010 FEU6C-X-90-30 F6X-N-X-H

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	7809.3
2.5°	7753.9
5°	7587.1
7.5°	7287.0
10°	6920.7
12.5°	6453.8
15°	6009.7
17.5°	5543.3
20°	5076.4
22.5°	4632.3
25°	4187.8
27.5°	3776.8
30°	3299.1
32.5°	2665.9
35°	2055.0
37.5°	1499.5
40°	1033.1
42.5°	677.5
45°	422.2
47.5°	255.4
50°	155.6
52.5°	122.1
55°	100.2
57.5°	77.8
60°	55.5
62.5°	44.3
65°	33.5
67.5°	22.3
70°	22.3
72.5°	11.2
75°	11.2
77.5°	11.2
80°	11.2
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-MV3F9LC







— 0°-180°







(END OF REPORT)